



LOC	Q1ST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14					RELEASED PER 0720-0008-93	2-2-93	18 DAP



AMP WIRE RANGE	UL E13268 Listed
26-22 AWG STRANDED	NOT LISTED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION
1-800-722-1111

FOR ORDER ENTRY
1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.1-0.41mm² [202-810] CIR MILS
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONSULTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLG DEC ±
3 PLG DEC ±
ANGLES

DR 2-2-93
TA BRINKMAN
CHK 2-2-93
DA PATTERSON
APPD 2-2-93
DE MILLER
APPD 2-2-93
JL MECKLEY
PRODUCT SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING
TONGUE, BUDGET

FINISH
TIN PLATE
0.00254 [0.00100] MIN
THK PER MIL-T-10727

APPLICATION SPEC
WEIGHT

SIZE
CAGE CODE
00779
DRAWING NO
322771

SHEET
1 OF 1