





LOGO(SEE NOTE 3)





DETAIL X



DETAIL X
BACK SHIELD TAB
(OPTIONAL)





PRINT P/N & DATE CODE
(SEE NOTE 4)







mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family GANGED MJACK			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
A		WL	11/04/11	angles	line of	X.X±0.25			CAT 3 MULTI-PORTS TAB DOWN				
						X.XX±0.13			1x4 WITH SHIELD, W/O LED				
						X.XXX±0.05							
				dr	WENDY CHEN	05/03/11			dwg no		sheet 1 of 4 size		
				enr	WENDY CHEN	05/03/11			10118062		A4		
				chr	WENDY CHEN	05/03/11							
				appd	GARY HSIEH	05/03/11			type CUSTOMER Drawing				
sheet index	revision sheet	A	A	A	A								
		1	2	3	4								



LOGO(SEE NOTE 3)



DETAIL X

PRINT P/N & DATE CODE
(SEE NOTE 4)


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family GANGED MJACK	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title
A				angles	X.X±0.25	MM [INCH]	CAT 3 MULTI-PORTS TAB DOWN 1x4 WITH SHIELD, W/O LED	
				X*±1°	X.XXX±0.05	scale	dwg no 10118062	
		dr	WENDY CHEN	05/03/11			sheet 2 of 4	size
		enr	WENDY CHEN	05/03/11				A4
		chr	WENDY CHEN	05/03/11				
		appd	GARY HSIEH	05/03/11			type	CUSTOMER Drawing
sheet index	revision	sheet						




mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family GANGED MJACK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title CAT 3 MULTI-PORTS TAB DOWN 1x4 WITH SHIELD, W/O LED			
A				angles	$X.X \pm 0.25$	 MM [INCH]	dwg no 10118062			
				$X^\circ \pm 1'$	$X.XXX \pm 0.05$					
				dr	WENDY CHEN 05/03/11		sheet 3 of 4 size A4			
				enr	WENDY CHEN 05/03/11					
				chr	WENDY CHEN 05/03/11					
				appd	GARY HSIEH 05/03/11					
sheet index	revision	sheet					type CUSTOMER Drawing			

NOTE:

- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC , UL94V-0
COLOR: BLACK.
CONTACTS: COPPER ALLOY.
SHIELD: COPPER ALLOY.
- FINISH:
CONTACTS: 50u" MIN. NICKEL UNDER PLATED OVER ALL.
SELECTIVE GOLD PLATED ON CONTACT AREA,
1u" GOLD PLATED ON SOLDER TAIL.
SHIELD: 20u" MIN. NICKEL OVER ALL.
- LASER MARK FCI LOGO ON THE TOP OF SHIELD.
- "DATE CODE" DESCRIPTION:
XX XX
WEEK
YEAR (EX. : 10--2010)
- PRODUCT PERFORMANCE PER SPEC. : GS-12-0990.
- PACKING SPEC. : GS-14-2170.
- THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED
IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.




10118062-XXXX3XXLF
WITH 3 BACK SHIELD TABS



10118062-XXXX0XXLF
WITHOUT BACK SHIELD TAB

9. PART NUMBER DESCRIPTION:

- 10118062-X X X X X X X LF
- LEAD FREE
 - 0 : RESERVED (NOT USED)
 - PACKAGING
1 : TRAY
 - OPTIONAL BACK SHIELD TAB
0 : WITHOUT BACK SHIELD TAB
3 : WITH 3 BACK SHIELD TABS
 - OPTIONAL RIGHT / LEFT SHIELD TAB
1 : DIM.A=4.57
5 : DIM.B=3.05
 - OPTIONAL PANEL GROUND
0 : WITHOUT PANEL GROUND
 - LED COLOR
0 : WITHOUT LED
 - CONTACT AREA PLATING
1 : 15u" GOLD PLATING
2 : 30u" GOLD PLATING
5 : 1u" GOLD FLASH PLATING



mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family GANGED MJACK									
ltr		ecn no		dr		date		tolerances unless otherwise specified		title									
A								angles linear		X.X±0.25		MM [INCH]		CAT 3 MULTI-PORTS TAB DOWN					
								X*±1°		X.XX±0.13				1x4 WITH SHIELD, W/O LED					
								X.XXX±0.05		scale									
								dr		WENDY CHEN		05/03/11		dwg no					
								engr		WENDY CHEN		05/03/11		sheet 4 of 4		size			
								chr		WENDY CHEN		05/03/11		10118062		A4			
								appd		GARY HSIEH		05/03/11		type		CUSTOMER Drawing			
sheet index		revision sheet																	