

2014



Professional HEX Tools





Inch & Metric



Complete Hex Program




Wiha Hex Tools Index

	DESCRIPTION	Page
	T-handles	13
	PocketStar Fold Outs	17
	L-keys - Long/Short Nickel & Black Finish	18-20
	Insulated T-handle	21
	Insulated Hex Drivers	21
	Insulated L-keys	22
	Insulated Sockets	22
	Drive-Loc VI Blades	23
	ESD Safe Precision	26
	Precision	28
	PicoFinish	27
	SYSTEM 4 Blades	29
	SYSTEM 4 Micro Bits	31
	Insert/Power Bit Sets	32
	XSelectors	34
	Bit Insert & Power Bits	35-37
	Sockets	38-40



Wiha Security Hex Index

	DESCRIPTION	Page
	SYSTEM 4 Micro Bits	31
	Insert Bits	35
	Sockets	39-40

Wiha Ball End Hex Tools Index

	DESCRIPTION	Page
	Ball End L-keys & Sets Chrome Finish	6
	Colored Coded L-keys Chrome Finish	5
	Ball End L-keys & Sets Long, Mid-Length & Short Black Finish	7-9
	Stainless Steel L-keys & Set	7
	Soft Grip T-handles Chrome & Black Finish	11-12
	3K Series Screwdrivers	16
	Drive-Loc VI Blades	23
	Precision	29
	PicoFinish Soft Grip	27
	SYSTEM 4 Blades	29
	Stubby Bit Holder Sets	32
	Ball End Hex Insert Bit	36
	Ball End Hex Socket	39


MagicRing Screw Holding Hex Tools Index

	DESCRIPTION	Page
	L-keys Screw Holding	4
	T-handles Screw Holding	10
	SoftFinish Screw Holding Cushion Grip	14-15
	PocketStars Screw Holding	17
	Insert Bits Screw Holding	33
	Power Bits Screw Holding	33
	Bit-Selectors Screw Holding Insert & Power Bits	33,34


Wiha Drive-Loc VI Index

DESCRIPTION	Page
 Drive-Loc VI Handle SoftFinish® Cushion Grip	23
 Drive-Loc VI Handle ESD Safe Cushion Grip	23
 Drive-Loc VI Handle MicroFinish Non-Slip Grip	23
 Drive-Loc VI Blades Ball End Hex & Hex Inch/Metric	23
 Drive-Loc VI Blade Set	23




Wiha Power & Insert Bits Index

DESCRIPTION	Page
 MagicRing Hex Inch & Metric Insert/Power Bits	33
 Hex Inch & Metric Insert/Power Bits	35-37
 Security Bits Inch & Metric Insert/Power Bits	35
 Ball End Hex Inch & Metric	36
 Stainless Steel Metric	36



Wiha TorqueControl Tools Index

DESCRIPTION	Page
 TorqueFix Handle	24
 TorqueVario Handle	24
 Hex Inch/Metric Blades	24
 T-handle Torque Tools	25
 Hex Inch/Metric Blades	25

Wiha Sockets & Sets Index

DESCRIPTION	Page
 Insulated Sockets	22
 Hex Bit Sockets 1/4" Drive	38-39
 Hex Bit Sockets 3/8" Drive	39
 Ball End Sockets	39
 6" Bit Sockets 1/4" & 3/8" Drive	38
 Socket Sets	40

Wiha Bit Sets Index

DESCRIPTION	Page
 MicroBit Sets	31
 Stubby Bit Holder Sets	32
 Topra Bit Sets	32
 Bit Selector Sets	33
 Power Bit Belt Packs	34
 XSelectors	34
 PokitPaks	34

MagicRing Ball End Hex Keys



669 MagicRing Ball End Metric Hex L-key Long blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	mm	mm	mm	lbs.	pkg.	
66904*	1.5	90	14	.01	10	No Ring
66908*	2.0	99	16	.01	10	No Ring
66912*	2.5	111	18	.01	10	No Ring
MagicRing						
66916	3.0	125	20	.02	10	
66920	4.0	138	25	.04	10	
66924	5.0	158	28	.07	10	
66928	6.0	178	32	.12	10	
66936	8.0	198	36	.23	10	
66944	10.0	221	40	.40	10	

* Standard Ball - No Ring




66990 9 Pc. MagicRing Long Metric Ball End Hex L-key Set, In ErgoStar Holder Blade Chrome-V-Moly, hardened, hard chrome finish.

Item							
No.		mm	mm		mm	mm	lbs.
66990	66904*	1.5	90	66924	5.0	158	.94
	66908*	2.0	99	66928	6.0	178	
	66912*	2.5	111	66936	8.0	197	
	66916	3.0	125	66944	10.0	221	
	66920	4.0	138				

* Standard Ball - No Ring

Screw Holding Hex Tools!



669 MagicRing Ball End Inch Hex L-key, Long blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.	
66945*	.050	2.8	.5	.01	10	No Ring
66946*	1/16	3.1	.6	.01	10	No Ring
66947*	5/64	3.5	.7	.01	10	No Ring
66950*	3/32	3.9	.7	.01	10	No Ring
66952*	7/64	4.3	.7	.02	10	No Ring
MagicRing						
66953	1/8	4.6	.8	.02	10	
66955	9/64	5.2	.9	.03	10	
66956	5/32	5.7	1.0	.04	10	
66959	3/16	6.2	1.1	.06	10	
66962	7/32	6.7	1.2	.09	10	
66965	1/4	7.3	1.2	.13	10	
66968	5/16	8.0	1.4	.22	10	
66971	3/8	8.8	1.6	.36	10	

* Standard Ball - No Ring



66991 13 Piece MagicRing Long Inch Ball End Hex L-key Set, In ErgoStar Holder Chrome-V-Moly, hardened, hard chrome finish.

Item							
No.		Inch	Inch		Inch	Inch	lbs.
66991	66945*	.050	2.8	66956	5/32	5.7	1.08
	66946*	1/16	3.1	66959	3/16	6.2	
	66947*	5/64	3.5	66962	7/32	6.7	
	66950*	3/32	3.9	66965	1/4	7.3	
	66952*	7/64	4.3	66968	5/16	8.0	
	66953	1/8	4.6	66971	3/8	8.8	
	66955	9/64	5.2				

* Standard Ball - No Ring



66992 22 Piece Combination MagicRing L-key Set, In ErgoStar Holder Blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	lbs.
66992	Set includes Inch & Metric: 2.02
	66990 Set - 1.5*, 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
	66991 Set - .050*, 1/16*, 5/64*, 3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"


* Standard Ball - No Ring

Inch & Metric Ball End Hex Keys Color Coded



Wiha exclusive Chrome-V-Moly super tool steel, through hardened


Wiha standard extra long for extended reach



Color coding for immediate identification of L-keys

Corrosion resistant nickel chrome base finish

25° Working Angles



25° Angle
For angle entry



569 Ball End Inch Hex Long Arm L-key, Set With Color Coded Keys Blade Chrome-V-Moly, hardened.

Item No.	Color Key	Inch
56901	Brown	.050
56902	Green	1/16
56903	Chrome	5/64
56904	Blue	3/32
56905	Purple	7/64
56906	Red	1/8
56907	Copper	9/64
56908	Gold	5/32
56909	Grey	3/16
56910	Black	7/32
56911	Chrome	1/4
56912	Green	5/16
56913	Brown	3/8




569 Ball End Metric Hex Long Arm L-key, Set With Color Coded Keys Blade Chrome-V-Moly, hardened.

Item No.	Color Key	mm	mm	mm	lbs.
56914	brown	1.5	91	15	.005
56915	green	2.0	101	18	.009
56916	chrome	2.5	113	20	.017
56917	blue	3.0	128	23	.019
56918	purple	4.0	142	29	.04
56919	red	5.0	163	33	.06
56920	Copper	6.0	184	38	.10
56921	gold	8.0	206	44	.20
56922	grey	10.0	231	50	.38



36986 13 Piece Inch Ball End Hex Long L-key Set With Color Coded Keys Chrome-V-Moly, hardened


Item No.	Inch:	lbs.
36986	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	.90



36987 9 Piece Metric Ball End Hex Long L-key Set With Color Coded Keys Chrome-V-Moly, hardened

Item No.	Metric:	lbs.
36987	1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	.90

Metric Ball End Hex Keys Chrome Finish



669 Ball End Metric Hex L-key, Long Arm

Blade Chrome-V-Moly, hardened, hard chrome finish.




Item No.	mm	mm	mm	lbs.	pkg.
66904	1.5	90	14	.004	10
66908	2.0	99	16	.007	10
66912	2.5	111	18	.012	10
66918	3.0	125	20	.019	10
66922	4.0	138	25	.042	10
66926	5.0	158	28	.072	10
66930	6.0	178	32	.12	10
66937	8.0	198	36	.23	10
66938	10.0	221	40	.40	10



66994 9 Piece Metric Ball End Hex Long L-key Set

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0,	
66994	5.0, 6.0, 8.0, 10.0mm	lbs. .98



66995 6 Piece Metric Ball End Hex Long L-key Set

Item No.		
66995	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm	lbs. .21



66998 11 Piece Metric Ball End Hex Long L-key Set

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0,	
66998	5.0, 6.0, 7.0, 8.0, 9.0, 10.0mm	lbs. 1.36

Inch Ball End Hex Keys Chrome Finish



369 Ball End Inch Hex L-key, Long Arm

Blade Chrome-V-Moly, hardened, hard chrome finish.



Item No.	Inch	Inch	Inch	lbs.	pkg.
36940	.050	2.8	.5	.002	10
36941	1/16	3.1	.6	.004	10
36942	5/64	3.5	.7	.007	10
36943	3/32	3.9	.7	.010	10
36948	7/64	4.3	.7	.016	10
36949	1/8	4.6	.8	.021	10
36951	9/64	5.2	.9	.029	10
36954	5/32	5.7	1.0	.035	10
36957	3/16	6.2	1.1	.059	10
36958	7/32	6.7	1.2	.092	10
36960	1/4	7.3	1.2	.13	10
36961	5/16	8.0	1.4	.22	10
36963	3/8	8.8	1.6	.36	10



36998 13 Piece Inch Ball End Hex Long L-key Set, In Plastic Holder

Blade Chrome-V-Moly, hardened, hard chrome finish.

Item No.	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8,	
36998	9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 1.0



66993 2 Pack Inch & Metric Ball End Hex L-key Sets

High alloy Chrome-V-Moly, hardened, hard chrome finish. In molded Holders

Item No		
66993	2 Sets with 22 L-keys include:	lbs.
	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	2.0
	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	

ErgoStar Ball End Hex Keys Chrome Finish

Fast Auto Open Key Holder




66996 9 Piece ErgoStar Metric Ball End Hex Long L-key Set

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	lbs. 1.02
----------	--	-----------

[SHOP](#)

Fast Auto Open Key Holder




66988 13 Piece ErgoStar Inch Ball End Hex Long L-key Set

Item No.	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 1.08
----------	--	-----------

[SHOP](#)

Fast Auto Open Key Holder




66982 22 Piece ErgoStar Inch/Metric Ball End Hex Long L-key Set

Item No.	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 2.10
	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	


[SHOP](#)



ErgoStar Inch Ball End L-key Set

- Patented ErgoStar auto open key holder
- Keys of chrome-vanadium-molybdenum steel
- 60HRC through hardened durability
- Hard chrome finish for best wear resistance

Stainless Steel Metric Ball End Hex Key



369 Stainless Steel Ball End Metric Hex L-key, Long Arm

Blade hardened, hard chrome finish.

Item No.	mm	mm	mm	lbs.	pkg.
36911	1.5	91	14	.004	10
36913	2.0	101	18	.007	10
36914	2.5	113	20	.012	10
36915	3.0	128	23	.020	10
36917	4.0	142	29	.050	10
36918	5.0	163	33	.074	10
36919	6.0	184	38	.13	10
36921	8.0	206	44	.25	10
36922	10.0	231	50	.44	10



36988 9 Pc. Stainless Steel Ball End L-key Set

In molded ergo holder

Item No.	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm	lbs. .88
36988	6.0, 8.0, 10.0mm	

L-keys Black Finish Sets



36995 2 Pack Inch & Metric Ball End Hex L-key Sets

High alloy Chrome-V-Moly, hardened, black finish.

Item No	lbs. 2.21
36995	2 Sets with 22 L-keys include:
	Sizes: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"




36696 3 Pack Inch & Metric Mid-Length Ball End Hex & TORX L-key Sets

Blade Chrome-V-Moly, hardened, black finish.

Item No	lbs. 2.58
36696	3 Sets with Hex & TORX L-keys include:
	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"
	TORX: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

Metric Ball End Inch & Metric Hex Keys Black Finish



369 Ball End Hex Metric L-key, Long Arm

Blade Chrome-V-Moly, hardened, black finish.


Item No.	mm	mm	mm	lbs.	pkg.
36904	1.5	90	14	.004	10
36908	2.0	99	16	.007	10
36912	2.5	111	18	.012	10
36916	3.0	125	20	.019	10
36920	4.0	138	25	.042	10
36924	5.0	158	28	.072	10
36928	6.0	178	32	.12	10
36936	8.0	198	36	.23	10
36944	10.0	221	40	.40	10



36990 9 Piece Metric Ball End Hex Long L-key Set

Blade Chrome-V-Moly, hardened, black finish.


Blade Chrome-V-Moly, hardened, black finish.							
Item							
No.		mm	mm		mm	mm	lbs.
36990	36904	1.5	90	36924	5.0	158	.98
	36908	2.0	99	36928	6.0	178	
	36912	2.5	111	36936	8.0	198	
	36916	3.0	125	36944	10.0	221	
	36920	4.0	138				



36992 6 Piece Metric Ball End Long Hex L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Blade Chrome-V-Moly, hardened, black finish.						
Item						
No.		mm	mm	mm	mm	lbs.
36992	36904	1.5	90	36916	3.0	125
	36908	2.0	99	36920	4.0	138
	36912	2.5	111	36924	5.0	158



369 Ball End Hex Inch L-key, Long Arm

Blade Chrome-V-Moly, hardened, black finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.
36945	.050	2.8	.5	.002	10
36946	1/16	3.1	.6	.004	10
36947	5/64	3.5	.7	.007	10
36950	3/32	3.9	.7	.010	10
36952	7/64	4.3	.7	.016	10
36953	1/8	4.6	.8	.021	10
36955	9/64	5.2	.9	.029	10
36956	5/32	5.7	1.0	.035	10
36959	3/16	6.2	1.1	.059	10
36962	7/32	6.7	1.2	.092	10
36965	1/4	7.3	1.2	.13	10
36968	5/16	8.0	1.4	.22	10
36971	3/8	8.8	1.6	.36	10



36991 13 Piece Inch Ball End Hex Long L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Blade Chrome-V-Moly, hardened, black finish.	
Item No.	
36991 13 pc. set includes: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 1.0



36993 8 Piece Inch Ball End Hex Long L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Blade Chrome-V-Moly, hardened, black finish.	
Item No.	
36993 8 pc. set includes: 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16"	lbs. .62

Mid-Length Ball End Hex Keys Black Finish



Ball End Hex L-keys
Working angle up to 25°

Ball End Hex Keys
Chamfered ends for easy insertion



369 Ball End Hex Inch Mid-Length L-keys

Blade Chrome-V-Moly, hardened, black finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.	10 Pack Item No.	pkg.
36901	.050	2.82	.45	.002	1	46701	10
36902	1/16	3.05	.53	.004	1	46703	10
36903	5/64	3.27	.63	.007	1	46705	10
36905	3/32	3.43	.68	.010	1	46707	10
36906	7/64	3.62	.76	.016	1	46709	10
36907	1/8	3.84	.76	.021	1	46711	10
36909	9/64	4.08	.87	.029	1	46713	10
36910	5/32	4.36	.96	.035	1	46717	10
36923	3/16	4.67	1.08	.059	1	46719	10
36925	7/32	5.05	1.18	.092	1	46721	10
36926	1/4	5.73	1.25	.13	1	46723	10
36927	5/16	6.75	1.36	.22	1	46727	10
36929	3/8	7.0	1.50	.36	1	46731	10



36937 13 Piece Inch Mid-Length Ball End Hex L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Item No.		lbs.
36937	13 pc. set includes: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	.82



369 Ball End Hex Metric Mid-Length L-keys

Blade Chrome-V-Moly, hardened, black finish.

Item No.	mm	mm	mm	lbs.	pkg.	10 Pack Item No.	pkg.
36930	1.5	79	13	.010	1	46732	10
36931	2.0	84	15	.016	1	46733	10
36932	2.5	90	17	.029	1	46734	10
36933	3.0	100	19	.035	1	46735	10
36934	4.0	113	24	.059	1	46736	10
36935	5.0	123	26	.092	1	46737	10
36938	6.0	144	31	.13	1	46738	10
36939	8.0	159	35	.22	1	46739	10
36966	10.0	181	37	.36	1	46741	10



36999 9 Piece Metric Mid-Length Ball End Hex L-key Set

Blade Chrome-V-Moly, hardened, black finish.

Item No.		lbs.
36999	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	.72



Inch & Metric




36900 2 Pack Inch & Metric Mid-Length Ball End Hex L-key Sets

Chrome-V-Moly, hardened, black finish.

Item No.		lbs.
36900	2 Sets with 22 L-keys include: Sizes: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1.54

Ball End Hex Keys Black Finish Short Arm



36989 9 Pc. Short Arm Metric Ball End Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

lbs. .59	pkg. 1
----------	--------

Wiha MagicRing Screw Holding T-handle

Hole for hanging

Proportioned ergonomic handle designed for high torque

Blade Wiha exclusive Chrome-V-Moly super tool steel, hardened, hard chrome finish

Screw Holding Hex Tools

Handle is molded directly onto blade

Smooth edges prevent injuries & eliminate pressure marks




540 MagicRing Hex **Metric** Ball End, With Wiha T-handle [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Ball end for easy insertion. Wiha T-handle high quality plastic, impact resistant.

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
54040	4.0	150	80	176	6.9	.08	10
54050	5.0	150	100	182	7.1	.14	10
54060	6.0	150	100	182	7.1	.17	10
54080	8.0	200	100	232	9.1	.29	10
54086	10.0	200	120	238	9.3	.49	10

540 MagicRing Hex **Inch** Ball End, With Wiha T-handle [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Ball end for easy insertion. Wiha T-handle high quality plastic, impact resistant.

Item No.	Inch	Inch	Inch	Inch	lbs.	pkg.
54012	5/32	5.8	2.8	6.9	.08	10
54014	3/16	5.8	4.0	7.2	.14	10
54016	7/32	5.8	4.0	7.2	.16	10
54018	1/4	5.8	4.0	7.2	.19	10
54022	5/16	7.8	4.0	7.2	.29	10
54024	3/8	7.8	4.7	7.5	.45	10



54090 5 Piece MagicRing Ball End T-handle Set, **Metric** Sizes [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Wiha T-handle high quality plastic, impact resistant.

Item		 		 			
No.		mm	mm		mm	mm	lbs.
54090	54040	4.0	150	54080	8.0	200	1.49
	54050	5.0	150	54086	10.0	200	
	54060	6.0	150				

54091 6 Piece MagicRing Ball End T-handle Set, **Inch** Sizes [SHOP](#)

Blade Chrome-V-Moly, hardened, hard chromed. Wiha T-handle high quality plastic, impact resistant.

Item											
No.		Inch		Inch		Inch		Inch		lbs.	
54091	54012	5/32	5.8			54018	1/4	5.8			1.59
	54014	3/16	5.8			54022	5/16	7.8			
	54016	7/32	5.8			54024	3/8	7.8			

Wiha Soft Grip Dual Drive T-handle



Two Tools In One!

Through the handle side torque drive

Ball & Standard Hex In One Powerful Tool

Two component soft grip handle

Wiha exclusive Chrome-V-Moly super tool steel, through hardened durability, hard chrome finish

Maximum Comfort & Maximum Power



Hard Chrome Finish

For angle entry

- Chrome-V-Moly, hardened, hard chrome finish
- Ball tip for speed & easy insertion
- Wiha soft grip are molded on and include through the handle side torque drive.

SHOP

540 Soft Grip Ball End Hex Metric Dual Drive T-handle

Item No.	mm	mm	Tip	lbs.	pkg.
54020	2.0	150	Ball	.06	10
54025	2.5	150	Ball	.06	10
54030	3.0	150	Ball	.07	10
54042	4.0	150	Ball	.09	10
54052	5.0	150	Ball	.18	10
54062	6.0	150	Ball	.21	10
54082	8.0	200	Ball	.35	10
54088	10.0	200	Ball	.55	10

54095 8 Pc. Ball End Hex Metric Soft Grip T-handle Set- No stand

Item						
No.		mm	mm	mm	mm	lbs.
54095	54020	2.0	150	54052	5.0	150
	54025	2.5	150	54062	6.0	150
	54030	3.0	150	54082	8.0	200
	54042	4.0	150	54088	10.0	200



54092 8 Piece Ball End Hex Metric Soft Grip T-handle Set


Blade Chrome-V-Moly, hardened, chrome finish. Wiha soft grips are molded on with through the handle side torque drive.



In metal stand

Item No.	mm	mm	lbs.	
54092	54020	2.0	150	3.34
	54025	2.5	150	
	54030	3.0	150	
	54042	4.0	150	
	54052	5.0	150	
	54062	6.0	150	
	54082	8.0	200	
	54088	10.0	200	

SHOP



540 Soft Grip Ball End Hex Inch Dual Drive T-handle Chrome-V-Moly, hardened, hard chrome finish. Ball tip for speed & easy insertion. Wiha soft grips are molded on with through the handle side torque drive.

Item No.	Inch	Inch	Tip	lbs.	pkg.
54007	3/32	5.9	Ball	.06	10
54008	7/64	5.9	Ball	.07	10
54009	1/8	5.9	Ball	.08	10
54010	9/64	5.9	Ball	.08	10
54001	5/32	5.9	Ball	.09	10
54002	3/16	5.9	Ball	.17	10
54003	7/32	5.9	Ball	.20	10
54004	1/4	5.9	Ball	.23	10
54005	5/16	7.9	Ball	.35	10
54006	3/8	7.9	Ball	.51	10

54097 10 Pc. Ball End Hex Inch Soft Grip T-handle Set- No stand

Item											
No.		Inch	Inch		Inch	Inch		Inch	Inch		lbs.
54097	54007	3/32	5.9		54002	3/16	5.9				2.15
	54008	7/64	5.9		54003	7/32	5.9				
	54009	1/8	5.9		54004	1/4	5.9				
	54010	9/64	5.9		54005	5/16	7.9				
	54001	5/32	5.9		54006	3/8	7.9				




54094 8 Piece Ball End Hex Inch Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, chrome finish. Wiha soft grips are molded on with through the handle side torque drive.

Item							
No.		Inch	Inch	Inch	Inch		lbs.
54094	54009	1/8	5.9	54003	7/32	5.9	3.37
	54010	9/64	5.9	54004	1/4	5.9	
	54001	5/32	5.9	54005	5/16	5.9	
	54002	3/16	5.9	54006	3/8	7.9	

Soft Grip Dual Drive T-handle - Black Finish



334 Soft Grip Ball End Hex **Metric** Dual Drive T-handle Chrome-V-Moly, hardened, black finish. Ball tip for speed & easy insertion. Wiha soft grip are molded on with through the handle side torque drive.

Item No.				
	mm	mm	lbs.	pkg.
33442*	2.0	150	.06	10
33444*	2.5	150	.06	10
33446*	3.0	150	.07	10
33448	4.0	150	.09	10
33450	5.0	150	.18	10
33452	6.0	150	.21	10
33454	8.0	200	.35	10
33458	10.0	200	.55	10

*No Ball - Standard Hex



33496 8 Pc. Ball End Hex **Metric** Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, black finish. Wiha soft grip are molded on with through the handle side torque drive.

Item							
No.		mm	mm		mm	mm	lbs.
33496	33442*	2.0	150	33450	5.0	150	2.04
	33444*	2.5	150	33452	6.0	150	
	33446*	3.0	150	33454	8.0	200	
	33448	4.0	150	33458	10.0	200	

*No Ball - Standard Hex

33489 8 Piece Hex & Ball End Hex **Metric** Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, black finish. Wiha soft grips are molded on with through the handle side torque drive.





Item No.			
	mm	mm	lbs.
33489	33442*	2.0	150
	33444*	2.5	150
	33446*	3.0	150
	33448	4.0	150
	33450	5.0	150
	33452	6.0	150
	33454	8.0	200
	33458	10.0	200



*No Ball - Standard Hex

In metal stand



334 Soft Grip Ball End Hex Inch Dual Drive T-handle Chrome-V-Moly, hardened, black finish. Ball tip for speed & easy insertion. Wiha soft grips are molded on with through the handle side torque drive.

Item No.				
	Inch	Inch	lbs.	pkg.
33418*	5/64	5.9	.06	10
33420*	3/32	5.9	.06	10
33422*	7/64	5.9	.07	10
33424*	1/8	5.9	.08	10
33426*	9/64	5.9	.08	10
33428	5/32	5.9	.09	10
33430	3/16	5.9	.17	10
33432	7/32	5.9	.20	10
33433	1/4	5.9	.23	10
33439	5/16	7.9	.35	10
33440	3/8	7.9	.51	10

*No Ball - Standard Hex

33494 11 Pc. Ball End Hex Inch Soft Grip Dual Drive T-handle Set

Item													
No.		Inch	Inch			Inch	Inch			Inch	Inch		lbs.
33494	33418*	5/64	5.9			33430	3/16	5.9					2.39
	33420*	3/32	5.9			33432	7/32	5.9					
	33422*	7/64	5.9			33433	1/4	5.9					
	33424*	1/8	5.9			33439	5/16	7.9					
	33426*	9/64	5.9			33440	3/8	7.9					
	33428	5/32	5.9										

*No Ball - Standard Hex

33498 8 Piece Ball End Hex Inch Soft Grip T-handle Set

Item		 		 			
No.		Inch	Inch	Inch	Inch	lbs.	
33498	33424*	1/8	5.9	33432	7/32	5.9	2.15
	33426*	9/64	5.9	33433	1/4	5.9	
	33428	5/32	5.9	33439	5/16	7.9	
	33430	3/16	5.9	33440	3/8	7.9	

*No Ball - Standard Hex

33499 8 Piece Hex & Ball End Hex Inch Soft Grip T-handle Set

Blade Chrome-V-Moly, hardened, black finish. Wiha soft grips are molded on with through the handle side torque drive.



Item No.			
	Inch	Inch	lbs.
33499	33424*	1/8	5.9
	33426*	9/64	5.9
	33428	5/32	5.9
	33430	3/16	5.9
	33432	7/32	5.9
	33433	1/4	5.9
	33439	5/16	7.9
	33440	3/8	7.9



*No Ball - Standard Hex

In metal stand

Wiha T-handle Hex Tools

Ergonomic handle design for high torque

Hole for hanging

Handle is molded directly onto blade

Smooth edges prevent injuries & eliminate pressure marks

Blade Wiha exclusive Chrome-V-Moly super tool steel hardened, nickel-plated



Yellow = Inch
Red = Metric

334 Hex Inch & Metric Drivers, With Wiha T-handle Chamfered tip for easy insertion. Wiha-T-handle high quality plastic, impact resistant.

Item No.	Inch	Inch	Inch	Inch	lbs.	pkg.	
33453	3/32	6.0	2.8	7.0	.05	10	
33456	7/64	6.0	2.8	7.0	.05	10	
33459	1/8	6.0	2.8	7.0	.06	10	
33462	9/64	6.0	2.8	7.0	.07	10	
33465	5/32	6.0	2.8	7.0	.08	10	
33468	3/16	6.0	3.5	7.0	.13	10	
33471	7/32	6.0	3.5	7.0	.16	10	
33474	1/4	6.0	3.5	7.0	.18	10	
33477	5/16	6.0	3.5	7.0	.25	10	
33480	3/8	6.0	4.1	7.0	.39	10	
Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
33401	2.0	100	80	126	4.9	.05	10
33436	2.0	200	80	226	8.9	.05	10
33402	2.5	100	80	126	4.9	.05	10
33437	2.5	200	80	226	8.9	.08	10
33403	3.0	100	80	126	4.9	.05	10
33404	3.0	150	80	176	6.9	.08	10
33405	3.0	200	80	226	8.9	.09	10
33435	3.0	350	100	382	15.0	.22	10
33406	4.0	100	80	126	4.9	.07	10
33407	4.0	150	80	176	6.9	.10	10
33408	4.0	200	80	226	8.9	.09	10
33438	4.0	350	100	382	15.0	.26	10
33409	5.0	100	100	132	5.2	.13	10
33410	5.0	150	100	182	7.1	.17	10
33411	5.0	200	100	232	9.1	.16	10
33412	5.0	350	100	382	15.0	.26	10
33413	5.0	450	120	488	19.1	.53	10
33414	6.0	100	100	132	5.2	.14	10
33415	6.0	150	100	182	7.1	.18	10
33416	6.0	200	100	232	9.1	.20	10
33417	6.0	350	100	382	15.0	.32	10
33419	7.0	200	100	232	9.1	.22	10
33421	8.0	100	100	132	5.2	.20	10
33423	8.0	200	100	232	9.1	.29	10
33434	8.0	350	100	372	14.6	.48	10
33425	10.0	100	120	138	5.4	.34	10
33427	10.0	200	120	238	9.3	.49	10
33429	12.0	200	120	238	9.3	.58	10



SHOP

33492 10 Piece Hex Driver T-handle Set, Inch Sizes

 				  			
Item No.		Inch	Inch	Inch		Inch	lbs.
33492	33453	3/32	6.0	33468	3/16	6.0	1.74
	33456	7/64	6.0	33471	7/32	6.0	
	33459	1/8	6.0	33474	1/4	6.0	
	33462	9/64	6.0	33477	5/16	6.0	
	33465	5/32	6.0	33480	3/8	6.0	



SHOP

33493 8 Piece Hex Driver T-handle Set, Metric Sizes

Item							
No.		mm	mm		mm	mm	lbs.
33493	33401	2.0	100	33409	5.0	100	1.64
	33402	2.5	100	33416	6.0	200	
	33403	3.0	100	33423	8.0	200	
	33406	4.0	100	33427	10.0	200	



SHOP

33484 8 Pc. Hex Driver T-handle Set, Inch Sizes - In metal stand

Item											
No.		Inch		Inch		Inch		Inch		lbs.	
33484	33459	1/8	6.0	33471	7/32	6.0	3.07				
	33462	9/64	6.0	33474	1/4	6.0					
	33465	5/32	6.0	33477	5/16	6.0					
	33468	3/16	6.0	33480	3/8	6.0					

33488 8 Pc. Hex Driver T-handle Set, Metric Sizes - In metal stand

Item											
No.		mm	mm		mm	mm		mm	mm		lbs.
33488	33401	2.0	100		33410	5.0	150				3.07
	33402	2.5	100		33415	6.0	150				
	33403	3.0	100		33423	8.0	200				
	33406	4.0	100		33427	10.0	200				

SHOP

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools




367 MagicRing Ball End Hex-Driver Inch, With Wiha-SoftFinish®

Handle Hex blade, Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item						
No.	Inch	Inch	mm	mm	lbs.	pkg.
36710*	.050	3.1	80	179	.06	10
36713*	1/16	3.1	80	204	.06	10
36716*	5/64	3.9	100	204	.07	10
36719*	3/32	3.9	100	204	.07	10
36723*	7/64	3.9	100	211	.07	10
With MagicRing						
36726	1/8	3.9	100	243	.12	10
36728	9/64	3.9	100	243	.12	10
36732	5/32	5.0	125	271	.12	10
36734	3/16	6.0	150	271	.16	10
36736	7/32	6.0	150	271	.23	10
36738	1/4	6.0	150	271	.25	10
36742	5/16	8.0	200	271	.37	10
36744	3/8	8.0	200	271	.54	10

* Standard Ball - No Ring



36793 8 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
36793	36726	1/8	4.0	36736	7/32	6.0	2.25
	36728	9/64	4.0	36738	1/4	6.0	
	36732	5/32	5.0	36742	5/16	8.0	
	36734	3/16	6.0	36744	3/8	8.0	

Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!



36791 13 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
36791	36710*	.050	3.0	36732	5/32	5.0	2.58
	36713*	1/16	3.0	36734	3/16	6.0	
	36716*	5/64	4.0	36736	7/32	6.0	
	36719*	3/32	4.0	36738	1/4	6.0	
	36723*	7/64	4.0	36742	5/16	8.0	
	36726	1/8	4.0	36744	3/8	8.0	
	36728	9/64	4.0				

* Standard Ball - No Ring



36794 6 Piece MagicRing Inch Ball End Screwdriver Set

Hex blade Chrome-V-Moly, hardened, hard chromed.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
36794	36726	1/8	4.0	36734	3/16	6.0	1.34
	36728	9/64	4.0	36736	7/32	6.0	
	36732	5/32	5.0	36738	1/4	6.0	

Wiha MagicRing SoftFinish® Hex Drivers

Screw Holding Hex Tools



Don't Drop That Screw!
Save Valuable Time!
Improve Productivity!
Make The Job Easy!



367 MagicRing Ball End Hex Driver Metric, With Wiha-SoftFinish®
Handle Hex blade, Chrome-V-Moly, hardened, hard chromed.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	lbs.	pkg.
36715*	1.5	75	179	.06	10
36720*	2.0	100	204	.07	10
36725*	2.5	100	204	.07	10
With MagicRing					
36730	3.0	100	204	.07	10
36740	4.0	125	211	.12	10
36750	5.0	150	243	.16	10
36760	6.0	150	243	.23	10
36780	8.0	200	268	.37	10
36786	10.0	200	271	.54	10

* Standard Ball - No Ring

Hardened spring steel retaining ring holds screws on

Hard chrome super durable corrosion resistant finish

Precision machined for exact fit

Made from Wiha exclusive Chrome-V-Moly hardened tool steel

36790 9 Piece MagicRing Metric Ball End Hex Screwdriver Set
Hex blade Chrome-V-Moly, hardened, hard chromed.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	mm	lbs.
36790	36715*	1.5	75	36750	5.0 150
	36720*	2.0	100	36760	6.0 150
	36725*	2.5	100	36780	8.0 200
	36730	3.0	100	36786	10.0 200
	36740	4.0	125		

* Standard Ball - No Ring



36792 6 Piece MagicRing Metric Ball End Hex Screwdriver Set
Hex blade Chrome-V-Moly, hardened, hard chromed.
Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	mm	mm	mm	mm	lbs.
36792	36730	3.0	100	36760	6.0 150
	36740	4.0	125	36780	8.0 200
	36750	5.0	150	36786	10.0 200

Wiha Ball End 3K Series Drivers & Sets



467 Ball End Hex Inch Drivers, With 3K Ergo Soft Grip Handles
Blades Chrome-V-Moly, hardened, black finish. Ergo soft grip handles.

Item No.	Inch	Inch	Inch	lbs.	pkg.
46702	.050	2.9	6.3	.07	10
46704	1/16	2.9	6.3	.07	10
46706	5/64	3.9	7.3	.07	10
46708	3/32	3.9	7.3	.07	10
46710	7/64	3.9	7.3	.07	10
46712	1/8	3.9	7.7	.09	10
46714	9/64	3.9	7.7	.10	10
46716	5/32	3.9	7.7	.11	10
46718	3/16	3.9	7.7	.12	10
46722	7/32	5.9	10.0	.19	10
46724	1/4	5.9	10.0	.22	10
46726	5/16	7.9	12.0	.34	10
46728	3/8	7.9	12.5	.48	10




46794 6 Piece 3K Ergo Inch Ball End Hex Screwdriver set

Item No.		
46794	Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .97



46793 8 Piece 3K Ergo Inch Ball End Hex Screwdriver Set

Item No.		
46793	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	lbs. 1.19



46797 13 Piece 3K Ergo Inch Ball End Hex Screwdriver Set

Item No.		
46797	Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	lbs. 2.40

Yellow = Inch
Red = Metric



- Soft panel grip
- Fast angle entry
- Convenient hang hole
- Exact fit precision machined tips
- Wiha exclusive Chrome-V-Moly super tool steel



467 Ball End Hex Metric Screwdriver, With Wiha-3K Ergo Handle

Blades Chrome-V-Moly, hardened, black finish. Molded on Wiha-3K Ergo soft grip handles.


Item No.	mm	mm	mm	lbs.	pkg.
46715	1.5	75	161	.07	10
46720	2.0	100	186	.07	10
46725	2.5	100	186	.07	10
46730	3.0	100	186	.07	10
46740	4.0	100	197	.11	10
46750	5.0	100	197	.13	10
46760	6.0	150	257	.21	10
46780	8.0	200	307	.34	10
46786	10.0	200	319	.52	10



46796 7 Piece Metric Ball End Hex Screwdriver Set

Blades Chrome-V-Moly, hardened, black finish. Molded on Wiha-3k Ergo soft grip handles.

Item No.		
46796	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	lbs. 1.15



46799 9 Piece Metric Ball End Hex Screwdriver Set

Item No.		
46799	Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	lbs. 1.93

Wiha PocketStar Fold-Ups



Push button key release

36997 9 Piece MagicRing Inch PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 36997	
Inch PocketStar: 5/64*, 3/32*, 7/64*	lbs. .46
1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	

* Standard Ball - No Ring



Push button key release

36996 7 Piece MagicRing Metric PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 36996	
PocketStar	lbs. .50
Metric: 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0mm	

* Standard Ball - No Ring



Push button key release

66997 2 Pack MagicRing PocketStar Fold Outs Inch & Metric

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 66997	
Fold Outs Inch/Metric Includes:	lbs. .98
36996 - 2.0*, 2.5*, 3.0, 4.0, 5.0, 6.0, 8.0mm	
36997 - 5/64*, 3/32*, 7/64*, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	

* Standard Ball - No Ring



#35195

#35196

SHOP

35195 7 Piece Metric Hex PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35195	
PocketStar	lbs. .51
Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	

35196 7 Piece Metric Hex PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35196	
PocketStar	lbs. .31
Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	

SHOP



Push button key release

35197 9 Piece Inch Hex PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35197	
Inch PocketStar:	lbs. .47
5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	



Push button key release

35198 6 Pc. Slotted, Phillips & Hex Metric PocketStar Fold Outs

High alloy CVM steel, hardened, molded ergonomic handle.

Item No. 35198	
PocketStar	lbs. .35
Slotted: 5.5mm Phillips: #2	
Metric: 3.0, 4.0, 5.0, 6.0mm	

SHOP



Nickel-Plated Long Arm Hex L-keys



Nickel-Plated

• Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.

352 Inch							
Inch & Metric Hex L-keys, Long Arm							
Item No.	Inch	mm	Inch	mm	lbs.	pkg.	
35231	.050	75	3.0	.01	.01	10	
35233	1/16	78	3.1	.01	.01	10	
35235	5/64	82	3.2	.01	.01	10	
35237	3/32	85	3.3	.01	.01	10	
35239	7/64	92	3.6	.01	.01	10	
35241	1/8	95	3.7	.02	.02	10	
35243	9/64	100	3.9	.03	.03	10	
35251	5/32	105	4.1	.03	.03	10	
35252	3/16	113	4.4	.05	.05	10	
35253	7/32	122	4.8	.07	.07	10	
35254	1/4	135	5.3	.10	.10	10	
35255	5/16	152	6.0	.18	.18	10	
35256	3/8	173	6.8	.30	.30	10	
35257	1/2	209	8.2	.77	.77	1	
35258	9/16	230	9.1	1.04	1.04	1	
35259	5/8	245	9.6	1.27	1.27	1	
35261	3/4	286	11.3	2.01	2.01	1	
352 Metric							
Item No.	mm	mm	Inch	mm	mm	lbs.	pkg.
35201	1.5	89	3.5	14	.6	.01	10
35202	2.0	99	3.9	16	.6	.01	10
35204	2.5	110	4.3	18	.7	.02	10
35206	3.0	124	4.9	20	.8	.02	10
35208	4.0	138	5.4	25	1.0	.04	10
35210	5.0	158	6.2	28	1.1	.07	10
35211	6.0	178	7.0	32	1.3	.12	10
35212	7.0	187	7.4	34	1.3	.17	10
35214	8.0	196	7.7	36	1.4	.23	10
35217	10.0	219	8.6	40	1.6	.40	10
35219	12.0	245	9.6	45	1.8	.77	1
35221	14.0	277	10.9	56	2.2	1.12	1
35223	17.0	316	12.4	63	2.5	1.80	1
35227	19.0	355	14.0	70	2.8	2.46	1



SHOP

35295 13 Piece Inch Hex L-key Set, In Plastic Holder

Equipped with .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Item No.	lbs.	pkg.
35295	.90	1



SHOP

35297 9 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Item No.	lbs.	pkg.
35297	1.00	1

Black Finish Long Arm Hex L-keys



Black Finish

High alloy CVM steel, hardened, black finish. Precision machined, burr free chamfered ends.

352 Inch							
L-key Hex, Long Arm							
Item No.	Inch	mm	Inch	mm	lbs.	pkg.	
35200	.028	67	2.6	.01	.01	10	
35203	.035	69	2.7	.01	.01	10	
35213	.050	75	3.0	.01	.01	10	
35216	1/16	78	3.1	.01	.01	10	
35218	5/64	82	3.2	.01	.01	10	
35222	3/32	85	3.3	.01	.01	10	
35224	7/64	92	3.6	.02	.02	10	
35226	1/8	95	3.7	.02	.02	10	
35228	9/64	100	3.9	.03	.03	10	
35232	5/32	105	4.1	.04	.04	10	
35234	3/16	113	4.4	.05	.05	10	
35236	7/32	122	4.8	.07	.07	10	
35238	1/4	135	5.3	.10	.10	10	
35242	5/16	152	6.0	.18	.18	10	
35244	3/8	173	6.8	.30	.30	10	
35245	1/2	209	8.2	.75	.75	1	
35246	9/16	230	9.1	.99	.99	1	
35247	5/8	245	9.6	1.26	1.26	1	
35248	3/4	286	11.3	2.02	2.02	1	
35249	1"	359	14.1	4.38	4.38	1	
352 Metric							
Item No.	mm	mm	Inch	mm	mm	lbs.	pkg.
35200	0.7	66	2.6	5	.2	.01	10
35203	0.9	68	2.7	8	.3	.01	10
35205	1.3	72	2.8	12	.5	.01	10
35215	1.5	76	3.5	14	.6	.01	10
35220	2.0	99	3.9	16	.6	.01	10
35225	2.5	110	4.3	18	.7	.02	10
35230	3.0	124	4.9	20	.8	.02	10
35240	4.0	138	5.4	25	1.0	.04	10
35250	5.0	158	6.2	28	1.1	.07	10
35260	6.0	178	7.0	32	1.3	.12	10
35270	7.0	187	7.4	34	1.3	.18	10
35280	8.0	196	7.7	36	1.4	.24	10
35282	10.0	219	8.6	40	1.6	.40	10
35284	12.0	245	9.6	45	1.8	.77	1
35285	14.0	277	10.9	56	2.2	1.13	1
35286	17.0	316	12.4	63	2.5	1.80	1
35288	19.0	355	14.0	70	2.8	2.45	1



#35291



#35290

Black Finish

35291 13 Piece Inch Hex L-key Set, In Plastic Holder

.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Item No.	lbs.	pkg.
35291	.98	1

35290 9 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

Item No.	lbs.	pkg.
35290	.97	1

SHOP

Short Arm Hex L-keys Nickel Finish

- Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.

Nickel-Plated

[SHOP](#)

351 Metric L-key Hex Metric, Short Arm high alloy CVM steel, hardened, nickel plated. Precision machined, burr free chamfered ends.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
35104	1.5	45	1.8	14	.6	.01	10
35108	2.0	49	1.9	16	.6	.01	10
35112	2.5	55	2.2	18	.7	.01	10
35116	3.0	61	2.4	20	.8	.02	10
35120	4.0	68	2.7	25	1.0	.03	10
35124	5.0	78	3.1	28	1.1	.04	10
35128	6.0	88	3.5	32	1.3	.07	10
35132	7.0	92	3.6	34	1.3	.10	10
35136	8.0	97	3.8	36	1.4	.13	10
35140	9.0	103	4.1	38	1.5	.18	10
35144	10.0	109	4.3	40	1.6	.23	10
35145	12.0	122	4.8	45	1.8	.40	1
35175	14.0	137	5.4	56	2.2	.61	1
35177	17.0	156	6.1	63	2.5	1.02	1
35179	19.0	176	6.9	70	2.8	1.40	1

- Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.

Nickel-Plated

[SHOP](#)

351 Inch L-key Hex, Short Arm Nickel-plated

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
35143	.050	40	1.6	10	.39	.01	10
35146	1/16	46	1.8	14	.55	.01	10
35147	5/64	50	2.0	16	.63	.01	10
35150	3/32	52	2.1	19	.75	.01	10
35152	7/64	54	2.1	19	.75	.01	10
35153	1/8	58	2.3	21	.83	.02	10
35155	9/64	62	2.4	23	.91	.02	10
35156	5/32	68	2.7	25	.99	.02	10
35159	3/16	70	2.8	26	1.0	.04	10
35162	7/32	77	3.1	29	1.2	.05	10
35165	1/4	88	3.5	31	1.2	.08	10
35168	5/16	98	3.9	36	1.4	.13	10
35171	3/8	107	4.2	38	1.5	.20	10
35174	1/2	133	5.2	44	1.7	.46	1
35176	9/16	158	6.2	64	2.5	.64	1
35178	5/8	175	6.9	71	2.8	.85	1
35180	3/4	198	7.8	89	3.5	1.40	1



[SHOP](#)

35191 9 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

 lbs. .59  pkg. 1



[SHOP](#)

35193 6 Piece Metric Hex L-key Set, In Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm

 lbs. .20  pkg. 1



[SHOP](#)

35192 8 Piece Inch Hex L-key Set, In Plastic Holder

Equipped with 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16"

 lbs. .41  pkg. 1



[SHOP](#)

35194 13 Piece Inch Hex L-key Set, In Plastic Holder

Equipped with .050 - 3/8"

 lbs. .72  pkg. 1

Short Arm Hex L-keys Black Finish


 Black Finish



353 Metric L-key Hex Metric, Short Arm high alloy CVM steel, hardened, black finish. Precision machined, burr free chamfered ends.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
35301	0.7	31	1.2	-	-	.01	10
35302	0.9	31	1.2	-	-	.01	10
35303	1.3	40	1.6	12	.5	.01	10
35304	1.5	45	1.8	14	.6	.01	10
35305	2.0	49	1.9	16	.6	.01	10
35306	2.5	55	2.2	18	.7	.01	10
35307	3.0	61	2.4	20	.8	.02	10
35308	4.0	68	2.7	25	1.0	.03	10
35309	5.0	78	3.1	28	1.1	.04	10
35310	6.0	88	3.5	32	1.3	.07	10
35311	7.0	92	3.6	34	1.3	.10	10
35312	8.0	97	3.8	36	1.4	.13	10
35313	9.0	103	4.1	38	1.5	.17	10
35314	10.0	109	4.3	40	1.6	.23	10
35316	11.0	115	4.5	42	1.7	.29	10
35317	12.0	122	4.8	45	1.8	.40	1
35318	14.0	137	5.4	56	2.2	.61	1
35319	17.0	156	6.1	63	2.5	1.03	1
35320	19.0	176	6.9	70	2.8	1.40	1
35321	22.0	195	7.7	80	3.1	2.17	1


 Black Finish




353 Inch L-key Hex Inch, Short Arm black finish

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
35301	.028	31	1.2	-	-	.01	10
35302	.035	31	1.2	-	-	.01	10
35330	.050	40	1.6	10	.4	.01	10
35331	1/16	46	1.8	14	.6	.01	10
35332	5/64	50	2.0	16	.6	.01	10
35333	3/32	52	2.1	19	.8	.01	10
35334	7/64	54	2.1	19	.8	.01	10
35335	1/8	58	2.3	21	.8	.02	10
35336	9/64	62	2.4	23	.9	.02	10
35337	5/32	68	2.7	25	1.0	.02	10
35338	3/16	70	2.8	26	1.0	.05	10
35339	7/32	77	3.1	29	1.2	.07	10
35340	1/4	88	3.5	31	1.2	.07	10
35341	5/16	98	3.9	36	1.4	.13	10
35342	3/8	107	4.2	38	1.5	.20	10
35343	1/2	133	5.2	44	1.7	.49	1
35345	9/16	158	6.2	64	2.5	.66	1
35346	5/8	175	6.9	71	2.8	.86	1
35347	3/4	198	7.8	89	3.5	1.45	1
35348	1"	220	8.7	91	3.6	3.14	1





35390 9 Piece Metric Hex L-key Set, In Plastic Holder
 Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm
 lbs. .59  pkg. 1




35392 5 Piece Mini Metric Hex L-key Set, In Plastic Holder
 Equipped with 0.7, 0.9, 1.3, 1.5, 2.0mm
 lbs. .03  pkg. 1




35391 13 Piece Inch Hex L-key Set, In Plastic Holder
 Equipped with .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"
 lbs. .64  pkg. 1




35393 5 Piece Mini Inch Hex L-key Set, In Plastic Holder
 Equipped with .028, .035, .050, 1/16, 5/64"
 lbs. .03  pkg. 1

Wiha Insulated T-handles

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E, CSA

Responds to OSHA's use specification 29 CFR1910


Insulation

Molded directly onto blade for permanent bonding

Each tool individually tested to 10,000 volts and certified to 1000 Volt ac or 1500 Volt dc

Blade CVM tool steel, hardened to average 58/60RC

1000V



1000Volt

SHOP

334 **Metric** T-handle, With Wiha-Molded Handle. Insulation According to ASTM, VDE, EN/IEC, NFPA70E and CSA, **1000 Volt. Individually Tested.**

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
33441	4.0	150	5.9	176	6.9	.09	10
33443	5.0	150	5.9	176	6.9	.15	10
33445	6.0	150	5.9	176	6.9	.18	10
33447	8.0	150	5.9	176	6.9	.26	10
33449	10.0	150	5.9	176	6.9	.46	10



1000Volt

SHOP

33478 5 Piece Hex **Metric** T-handle Set

Item	Hex	lbs.
No.	Hex Metric :	lbs.
33478	4.0, 5.0, 6.0, 8.0, 10.0mm	1.20

Wiha Insulated Hex Metric Screwdrivers




1000Volt

SHOP

323 Hex **Metric** Screwdriver, With Wiha-SoftFinish® Handle Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA, **1000 Volt. Individually Tested.** Blade high alloy CVM steel, hardened, black finish. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
32302	2.5	75	3.0	179	7.0	.06	10
32303	3.0	75	3.0	179	7.0	.08	10
32304	4.0	75	3.0	186	7.3	.12	10
32305	5.0	75	3.0	186	7.3	.15	10
32306	6.0	100	3.9	218	8.6	.21	10
32308	8.0	100	3.9	218	8.6	.34	10




1000Volt

SHOP

32366 6 Piece Insulated Hex **Metric** Screwdriver Set

Item No.	Hex	lbs.
No.	Hex Metric :	lbs.
32366	2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	1.06



1000Volt

SHOP

334 Inch T-handle, With Wiha-Molded Handle Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201, EN/IEC 60900, NFPA70E and CSA, **1000 Volt. Individually Tested.**

Blade CVM steel, hardened. Insulation molded directly onto blade. Wiha-SoftFinish® handle, multi-component.

Item	Hex	Inch	Inch	mm	lbs.	pkg.
No.	Inch	Inch	Inch	mm	lbs.	pkg.
33481	5/32	5.9	6.9	176	.09	10
33482	3/16	5.9	6.9	176	.15	10
33483	7/32	5.9	6.9	176	.19	10
33485	1/4	6.9	6.9	176	.20	10
33486	5/16	6.9	6.9	176	.26	10
33487	3/8	6.9	6.9	176	.44	10



1000Volt

SHOP

33490 6 Piece Hex Inch T-handle Set

Item	Hex	lbs.
No.	Hex Inch:	lbs.
33490	5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1.66

Wiha Insulated Hex L-keys

Insulation Test Standards:

Insulation according to ASTM,
F-1505-01, EN/IEC 60900
and CSA



Insulation
Applied directly
onto blade for
permanent
bonding

**Each tool individually
tested to 10,000 volts
and certified to 1000
Volt ac or 1500 Volt dc**

1000V



1000V

SHOP

136 Inch Insulated Hex L-keys, With Insulated Handle

Insulation According to IEC 60900 specification, up to 1000 Volt.
Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	ØMM	OAL	OAL	lbs.	pkg.
No.	Inch	mm	Inch		
13670	1/16	79	3.1	.05	1
13671	5/64	84	3.3	.05	1
13672	3/32	89	3.5	.05	1
13673	7/64	94	3.7	.06	1
13663	1/8	104	4.1	.06	1
13665	5/32	104	4.1	.06	1
13666	3/16	134	5.3	.10	1
13667	7/32	134	5.3	.12	1
13668	1/4	134	5.3	.16	1
13669	5/16	144	5.7	.24	1
13662	3/8	234	9.2	.51	1
13664	1/2	234	9.2	.77	1




1000V

SHOP

136 Metric Insulated Hex L-keys, With Insulated Handle

Insulation According to IEC 60900 specification, up to 1000 Volt.
Individually Tested. Blade chrome-vanadium steel, hardened.

Item No.	ØMM	OAL	OAL	lbs.	pkg.
No.	mm	mm	Inch		
13650	1.5	100	3.9	.09	1
13651	2.0	105	4.1	.09	1
13652	2.5	115	4.5	.09	1
13653	3.0	130	5.1	.10	1
13654	4.0	120	4.7	.10	1
13655	5.0	140	5.5	.10	1
13656	6.0	140	5.5	.13	1
13658	8.0	150	5.9	.24	1
13659	10.0	220	8.7	.51	1
13657	12.0	260	10.2	.77	1



#13691

#13690

1000V

SHOP

13690 8 Piece Insulated Hex L-key Set - Inch

Item No.		lbs.
13690	1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2"	2.17

13691 7 Piece Insulated Hex L-key Set - Metric

Item No.		lbs.
13691	3.0, 4.0, 5.0, 6.0, 8.0, 10.0, 12.0mm	2.07



1000V

SHOP

13693 10 Piece Insulated Hex L-key Set - Metric

Item No.		lbs.
13693	1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0, 12.0mm	2.26

13694 12 Piece Insulated Hex L-key Set - Inch

Item No.		lbs.
13694	1/16, 5/64, 3/32, 7/64, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8, 1/2"	2.40

Wiha Insulated 3/8" Bit Sockets & Set



1000V

SHOP

318 Insulated 3/8" Drive Sockets - Insulation according to

EN/IEC 60900, DIN 7448 specification, up to 1000 Volt.

Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	Inch	OAL	lbs.	pkg.
31805	3/16	3.1"	.13	1
31807	7/32	3.1"	.14	1
31809	1/4	3.1"	.14	1
31811	5/16	3.1"	.16	1
31813	3/8	3.1"	.18	1
31815	7/16	3.1"	.20	1
31817	1/2	3.1"	.22	1

*Sockets must be used with insulated ratchets & extensions



1000V

SHOP

31890 7 Piece Insulated 3/8" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No.	Set includes the following:	lbs.
31890	3/16, 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"	1.7

Wiha Drive-Loc VI Handles



Allows adjustable blade lengths 1.7" to 4.7" in 1/8" increments



28488 Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28488	6.0	115	4.5	36.0	1.41	.26



Allows adjustable blade lengths 1.7" to 4.7" in 1/8" increments



28486 ESD Safe Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange. Static Dissipative.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28486	6.0	115	4.5	36.0	1.41	.21



Allows adjustable blade lengths 1.7" to 4.7" in 1/8" increments



28487 Drive-Loc VI MicroFinish Non-Slip Grip Handle

Wiha-MicroFinish handle, won't peel, crack or deteriorate when exposed to petroleum solvents. Ideal for Hex, TORX® & Nut Drivers.

Advantages:

Ergonomic handle shape for maximum comfort, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28487	6.0	115	4.5	36.0	1.41	.20



Wiha Drive-Loc VI Blades



281 Ball End Hex & Hex Metric Drive-Loc VI Interchangeable Blade

Blade High alloy CVM steel, through hardened, hard chrome finish. Ball end enables the user to work at angles up to 25°. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.				
No.	mm + mm	lbs.	pkg.	
28116	2.5 2.5	.10	1	
28117	3 3	.10	1	
28118	4 4	.10	1	
28119	5 5	.10	1	
28120	6 6	.10	1	



281 Hex Metric Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.				
No.	mm + mm	lbs.	pkg.	
28149	2.0 2.5	.09	1	
28150	3.0 4.0	.10	1	
28151	5.0 6.0	.10	1	



281 Hex Inch Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish. Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item No.				
No.	Inch + Inch	lbs.	pkg.	
28122	3/32 7/64	.10	1	
28123	1/8 9/64	.10	1	
28124	5/32 3/16	.10	1	



28189 15 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch

Set includes Drive-Loc VI handle & 14 interchangeable blades.
Item No. 28189 lbs. 1.28
Slotted: 3.5+4.5, 5.5+6.5 **Phillips:** 1+2 **Security TORX®:** T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s **Hex Inch:** 3/32+7/64, 1/8+9/64, 5/32+3/16 **Hex Metric:** 2.0+2.5, 3.0+4.0, 5.0+6.0mm
 Wiha SoftFinish® Cushion Grip Blade Lock Handle

TorqueControl Tools



+/-6% accuracy
tolerance
Certificate of
calibration



+/-6% accuracy tolerance
Certificate of calibration



285 TorqueFix, With Wiha-SoftFinish® Handle

Fixed Torque value pre-set. Tested in accordance with EN ISO 6798, BS EN 26789, ASME B107.14M, tolerance +/- 6%. Audible and perceptible click when pre-set torque has been attained.

Automatically resets for next torque cycle; 50% greater reverse torque.

Item No.	Pre-Sets						
	oz.	lbs.	Nm	mm	Inch	lbs.	pkg.
28503	80	5	0.56	112	4.4	.16	1
28505	120	7.5	0.84	112	4.4	.15	1
28507	160	10	1.12	119	4.7	.28	1
28509	200	12.5	1.41	119	4.7	.27	1
28511	240	15	1.69	119	4.7	.27	1
28513	320	20	2.25	119	4.7	.28	1
28515	400	25	2.82	126	4.9	.37	1
28517	480	30	3.39	126	4.9	.37	1
28518	560	35	3.95	126	4.9	.37	1
28519	640	40	4.52	126	4.9	.37	1
28521	800	50	5.65	132	5.2	.52	1
28523	960	60	6.78	132	5.2	.52	1
28525	1120	70	7.91	132	5.2	.52	1

Direct Reading Scale



+/-6% accuracy
tolerance
Certificate of
calibration



285 Adjustable TorqueVario With Direct Reading Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Range				
	Inch	lbs.	Increments	mm	lbs.
28501*	15 - 80	(in/oz)	2.5 Inch oz	122 - 127	.22
28502	5 - 10		.5 Inch lbs	122 - 127	.41
28504	7.5 - 20		.5 Inch lbs	126 - 131	.50
28506	10 - 50		2 Inch lbs	133 - 138	.59
28508	20 - 70		2 Inch lbs	137 - 142	.74

Above includes Micro Bit Holder 28583

See 4mm Micro Bits on Page 30

* +/- 10% (This unit only)

* (1 Nm = 8.8507)

285 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale	Increments			
			mm	lbs.	pkg.
28550*	0.1 - 0.6Nm	.02 Nm	122 - 127	.35	1
28551	0.4 - 1.0Nm	.05 Nm	122 - 127	.35	1
28552	0.8 - 2.0Nm	.05 Nm	126 - 131	.45	1
28553	1.0 - 5.0Nm	.20 Nm	133 - 138	.55	1
28554	2.0 - 8.0Nm	.25 Nm	137 - 142	.70	1

* +/- 10% (This unit only)

* (1 Nm 8.8507)



285 Hex Metric Interchangeable Blades For TorqueFix & TorqueVario

Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.				Max. Torque	
	mm	mm	lbs.	Nm	pkg.
28545	1.5	175	.07	0.9	1
28546	2.0	175	.07	1.8	1
28547	2.5	175	.07	3.8	1
28548	3.0	175	.07	8.0	1
28549	4.0	175	.07	8.0	1



285 Hex Inch Interchangeable Blades For TorqueFix & TorqueVario

Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.				Max. Torque	
	Inch	mm	lbs.	Nm	pkg.
28555	.050	175	.07	.4	1
28556	1/16	175	.07	.9	1
28557	5/64	175	.07	1.8	1
28558	3/32	175	.07	1.8	1
28559	7/64	175	.07	3.8	1
28560	1/8	175	.07	3.8	1
28587	9/64	175	.07	8.0	1
28588	5/32	175	.07	8.0	1

T-handle TorqueControl Tools



Includes Calibration Certificate



289 TorqueFix T-handle

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy
Ergonomic multi-component handle, light and compact.
With Certificate of calibration.

Item No.	Torque In-lbs.	Torque Nm	 mm x mm	 lbs.	 pkg.
28931	53.1	6	56 x 120	.81	1
28933	70.8	8	56 x 120	.82	1
28935	88.5	10	56 x 120	.79	1
28937	106.2	12	56 x 120	.79	1
28938	110.6	12.5	56 x 120	.80	1
28939	123.9	14	56 x 120	.80	1

Each TorqueFix T-handle has unique serial number and certificate of calibration



Includes Calibration Certificate



28940 Adjustable TorqueVario STplus T-handle

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy
Ergonomic multi-component handle, light and compact.

Item No.	Torque In-lbs.	Torque Nm	 mm x mm	 lbs.	 pkg.
28940	44.3-123.9	5-14	56 x 120	.81	1

* (1 Nm 8.8507)



289 Hex Metric Interchangeable Blades For TorqueFix T-handle

Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	 mm	 mm	 Inch	 lbs.	 pkg.
28916	3.0	130	5.1	.11	1
28917	4.0	130	5.1	.11	1
28918	5.0	130	5.1	.11	1
28919	6.0	130	5.1	.11	1



289 Hex Inch Interchangeable Blades For TorqueFix T-handle

Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	 Inch	 mm	 Inch	 lbs.	 pkg.
28920	1/8	130	5.1	.11	1
28921	9/64	130	5.1	.11	1
28922	5/32	130	5.1	.11	1
28923	3/16	130	5.1	.11	1
28924	7/32	130	5.1	.11	1



Adjustable from
Nm 5-14 or
In-lbs. 44.3-123.9

Wiha Precision ESD Safe Hex Drivers

Wiha Precision ESD Static Dissipative Screwdrivers meet the requirements for tools used in static sensitive areas.



Rotating cap for precise turning & control with fingertip

Molded Precision handle of impact resistant dissipative material

Tapered handle allows rapid rotation

Blade, CVM steel, hardened, hard chrome finish

Tip, precision ground for exact fit, Wiha Chromtop finish

ESD Standard IEC 61340-5-1

Surface resistance of handles is $10^6 - 10^9$ Ohms


[SHOP](#)

275 Inch Hex Driver, With Precision ESD Safe Dissipative

Handle Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
No.							
27505	0.028	40	1.6	120	4.7	.02	10
27510	0.035	40	1.6	120	4.7	.02	10
27513	0.05	40	1.6	120	4.7	.02	10
27537	1/16	50	2.0	145	5.7	.03	10
27539	5/64	50	2.0	145	5.7	.03	10
27541	3/32	60	2.4	170	6.7	.04	10
27543	7/64	60	2.4	170	6.7	.04	10
27545	1/8	60	2.4	170	6.7	.04	10
27547	9/64	60	2.4	170	6.7	.05	10
27549	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate


[SHOP](#)

275 Metric Hex Metric Driver, With Precision ESD Safe

Dissipative Handle Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item	Hex	mm	Inch	mm	Inch	lbs.	pkg.
No.							
27507	0.7	40	1.6	120	4.7	.02	10
27509	0.9	40	1.6	120	4.7	.02	10
27513	1.3	40	1.6	120	4.7	.03	10
27515	1.5	50	2.0	145	5.7	.03	10
27520	2.0	50	2.0	145	5.7	.04	10
27525	2.5	60	2.4	170	6.7	.05	10
27530	3.0	60	2.4	170	6.7	.05	10
27535	4.0	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



ESD standard
IEC 61340-5-1

[SHOP](#)

27590 Set 8 Pcs. Hex Metric Precision ESD Safe Dissipative

Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. In storage pouch

Item							
No.		mm	mm		mm	mm	lbs.
27590	27507	.71	40	27520	2.0	50	.53
	27509	.89	40	27525	2.5	60	
	27513	1.3	40	27530	3.0	60	
	27515	1.5	50	27535	4.0	60	



ESD standard
IEC 61340-5-1

[SHOP](#)

27591 8 Piece Hex Inch Precision Set, ESD Safe Dissipative

Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. In storage pouch

Item	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
No.							
27591	27513	0.05	1.6	27543	7/64	2.4	.57
	27537	1/16	2.0	27545	1/8	2.4	
	27539	5/64	2.0	27547	9/64	2.4	
	27541	3/32	2.4	27549	5/32	2.4	


[SHOP](#)

91118 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item	Size	lbs.	pkg.
No.			
91118	14 1/2" W x 7 3/4" L	.13	1

Pico Soft Grip Ball End Inch & Metric



SHOP

264 Ball End Hex Inch Screwdriver, With Precision Soft

PicoFinish Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item						
No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10
26457	5/64	2.0	50	5.9	150	10
26459	3/32	2.0	50	5.9	150	10
26461	7/64	2.4	60	6.3	160	10
26463	1/8	2.4	60	6.3	160	10
26465	9/64	2.4	60	6.3	160	10
26467	5/32	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26493 7 Piece Inch Ball End Hex Precision Driver Set, With

Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item	No.	Inch	Inch	Inch	Inch	lbs.
26493	26455	1/16	2.0	26463	1/8	2.4
	26457	5/64	2.0	26465	9/64	2.4
	26459	3/32	2.0	26467	5/32	2.4
	26461	7/64	2.4			



SHOP

264 Ball End Hex Metric Screwdriver, With Precision Soft

PicoFinish Handle. Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item							
No.	mm	mm	Inch	mm	Inch	pkg.	
26441	1.3	40	1.6	134	5.3	10	
26443	1.5	50	2.0	150	5.9	10	
26445	2.0	50	2.0	150	5.9	10	
26447	2.5	60	2.4	160	6.3	10	
26449	3.0	60	2.4	160	6.3	10	

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Hex Inch & Metric



SHOP

263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	Inch	mm	Inch	mm	Inch	pkg.
26341	0.028(0.7)	40	1.6	134	5.3	10
26343	0.035(0.9)	40	1.6	134	5.3	10
26345	0.05(1.3)	40	1.6	134	5.3	10
26349	5/64(2.0)	50	2.0	150	5.9	10
26363	1/16	50	2.0	144	5.7	10
26367	3/32	60	2.4	160	6.3	10
26369	7/64	60	2.4	160	6.3	10
26371	1/8	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26392 8 Piece Hex Inch Precision Driver Set

Item	No.	Inch	Inch	Inch	Inch	lbs.
26392	26341	0.028	1.6	26363	1/16	2.0
	26343	0.035	1.6	26367	3/32	2.4
	26345	0.05	1.6	26369	7/64	2.4
	26349	5/64	2.0	26371	1/8	2.4



SHOP

263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item						
No.	mm	mm	Inch	mm	Inch	pkg.
26341	0.7(0.028)	40	1.6	134	5.3	10
26343	0.9(0.035)	40	1.6	134	5.3	10
26345	1.3(0.05)	40	1.6	134	5.3	10
26347	1.5	50	2.0	144	5.7	10
26349	2.0(5/64)	50	2.0	150	5.9	10
26351	2.5	60	2.4	160	6.3	10
26353	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26393 7 Pc. Hex Metric Precision Driver Set

Item	No.	mm	mm	mm	mm	lbs.
26393	26341	0.7	40	26349	2.0	50
	26343	0.9	40	26351	2.5	60
	26345	1.3	40	26353	3.0	60
	26347	1.5	50			

Wiha Hex Precision Series



263 Metric Metric Hex Driver, With Precision Handle

Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26307	0.7	0.028	40	1.6	120	4.7	.02	10	
26309	0.9	0.035	40	1.6	120	4.7	.02	10	
26313	1.3	0.05	40	1.6	120	4.7	.02	10	
26315	1.5	-	50	2.0	145	5.7	.03	10	
26320	2.0	5/64	50	2.0	145	5.7	.03	10	
26325	2.5	-	60	2.4	170	6.7	.04	10	
26330	3.0	-	60	2.4	170	6.7	.04	10	
26340	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26390 7 Pc. Precision Hex Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	Inch	lbs.
26390	26307	0.7	1.6	.28
	26309	0.9	1.6	
	26313	1.3	1.6	
	26315	1.5	2.0	
	26320	2.0	2.0	
	26325	2.5	2.4	
	26330	3.0	2.4	



26399 8 Piece Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item	No.	Inch	Inch	Inch	Inch	lbs.
26399	26307	0.028	1.6	26320	5/64	.55
	26309	0.035	1.6	26323	3/32	2.4
	26313	0.05	1.6	26327	7/64	2.4
	26316	1/16	2.0	26331	1/8	2.4



263 Inch Inch Hex Driver, With Precision Handle

Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.
26307	.028	0.7	40	1.6	120	4.7	.02	10	
26309	.035	0.9	40	1.6	120	4.7	.02	10	
26313	0.05	1.3	40	1.6	120	4.7	.02	10	
26316	1/16	-	50	2.0	145	5.7	.03	10	
26320	5/64	2.0	50	2.0	145	5.7	.03	10	
26323	3/32	-	60	2.4	170	6.7	.04	10	
26327	7/64	-	60	2.4	170	6.7	.04	10	
26331	1/8	-	60	2.4	170	6.7	.04	10	
26333	9/64	-	60	2.4	170	6.7	.05	10	
26336	5/32	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26391 8 Pc. Precision Hex Driver Set - Inch

Blade high alloy CVM steel.

Item	No.	Inch	Inch	lbs.
26391	26307	0.028	1.6	.32
	26309	0.035	1.6	
	26313	0.05	1.6	
	26316	1/16	2.0	
	26320	5/64	2.0	
	26323	3/32	2.4	
	26327	7/64	2.4	
	26331	1/8	2.4	



Wiha Ball End Precision Series



264 Metric Ball End Hex Metric Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy CVM steel.

Item	No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	1.3	0.05	40	1.6	120	4.7	.02	10	
26415	1.5	-	50	2.0	145	5.7	.03	10	
26420	2.0	-	50	2.0	145	5.7	.03	10	
26425	2.5	-	60	2.4	170	6.7	.04	10	
26430	3.0	-	60	2.4	170	6.7	.05	10	
26440	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26491 5 Piece Ball End Hex Driver Set - Metric

Angle entry up to 30°.

Blade high alloy CVM steel.

Item	No.	mm	mm	lbs.
26491	26413	1.3	40	.31
	26415	1.5	50	
	26420	2.0	50	
	26425	2.5	60	
	26430	3.0	60	

Wiha Ball End Precision Series



264 Inch Ball End Hex Inch Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item	No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	0.05	40	1.6	120	4.7	.02	10	
26416	1/16	50	2.0	145	5.7	.03	10	
26419	5/64	50	2.0	145	5.7	.03	10	
26423	3/32	50	2.0	145	5.7	.03	10	
26427	7/64	60	2.4	170	6.7	.03	10	
26431	1/8	60	2.4	170	6.7	.05	10	
26436	9/64	60	2.4	170	6.7	.05	10	
26439	5/32	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



26490 8 Piece Ball End Hex Driver Set - Inch

Angle entry up to 30°.

Blade high alloy chrome-vanadium-molybdenum steel.

Item	No.	Inch	Inch	lbs.
26490	26413	0.05	1.6	.40
	26416	1/16	2.0	
	26419	5/64	2.0	
	26423	3/32	2.0	
	26427	7/64	2.4	
	26431	1/8	2.4	
	26436	9/64	2.4	
	26439	5/32	2.4	




26499 8 Piece Ball End Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In canvas storage pouch

Item	No.	Inch	Inch	lbs.
26499	26413	0.05	1.6	.62
	26416	1/16	2.0	
	26419	5/64	2.0	
	26423	3/32	2.0	
	26427	7/64	2.4	
	26431	1/8	2.4	
	26436	9/64	2.4	
	26439	5/32	2.4	

Wiha Ball End Precision Series



62995 22 Piece Slotted/Phillips/TORX®/Ball End Hex Inch & Metric Tech Pack

Wiha Proturm precision ball retainer handle & 21 Wiha interchangeable blades. Set in canvas storage pouch

62995 Set includes the following blades:

Slotted: 1.5, 2.0, 3.0, 4.0 Phillips: #000, #00, #0, #1

TORX®: T6, T7, T8, T9, T10, T15, T20

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .87

62994 14 Piece Inch/Metric Ball End Hex Work Tech Pack

Proturm precision ball retainer handle & 13 Wiha interchangeable blades.

62994 Set includes the following blades:

Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm

lbs. .66 Set in canvas storage pouch

SYS 4 Drive-Loc Precision Locking Tools



26961 ESD Safe Dissipative Precision Drive-Loc Handle

Surface resistant 10⁶-10⁹ Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item	No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08	



280 SYSTEM 4 Metric Hex Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item	No.	mm	mm	lbs.
28003	1.3	+	1.3	.02
28004	1.5	+	1.5	.02
28005	2.0	+	2.0	.02
28006	2.5	+	2.5	.02
28007	3.0	+	3.0	.02
28008	4.0	+	4.0	.02



Rotating Cap
for precise
turning and
control

**Precision
Handle**
high quality
plastic,
cadmium
free. ESD
Safe or
Standard
styles

Tapered Handle
allows rapid
rotation,
requires less
clearance

Tips
exact fit,
precision
machined

Blades
CVM steel, hardened, hard chromed

15mm

Collet Lock Handle
adjustable blade
length from
15 to 95mm/
.6" to 3.75"

95mm



26900 SYS 4 Standard Precision Handle,
with rotating control cap. Accepts all
SYSTEM 4 interchangeable blades. Wiha
Precision handle, tapered, impact resistant.
Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26900	4.0	.1574	14.0	.55	.04



26901 SYSTEM 4 Standard Precision

Adjustable handle with rotating control cap.

- Allows adjustable blade from 15 to 95mm.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
26901	4.0	.1574	14.0	.55	.06



269 SYSTEM 4 Metric Ball End & Standard Hex, Reversible Blade

Wiha vapor Chrome-Top finish on tips.

One side hex, other side ball end hex.

Item					
No.	mm	mm	mm	Inch	lbs.
26932	1.27 + 1.27	120	4.7	.05	
26933	1.5 + 1.5	120	4.7	.05	
26934	2.0 + 2.0	120	4.7	.06	
26935	2.5 + 2.5	120	4.7	.06	
26936	3.0 + 3.0	120	4.7	.06	
26937	4.0 + 4.0	120	4.7	.06	



28000 ESD Safe Dissipative Precision

Handle with rotating control cap. Surface
resistant 10^6 - 10^9 Ohms. 4 mm hex retainer
for all SYSTEM 4 interchangeable blades.
Tapered handle, high quality plastic, impact
resistant. Ball retainer hold. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28000	4.0	.1574	14.0	.55	.04



28001 ESD Safe Dissipative Precision

Adjustable Handle with rotating control cap.

Advantages:

- Use in ESD sensitive applications. Surface resistant 10^6 - 10^9 Ohms.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
28001	4.0	.1574	14.0	.55	.04



280 SYSTEM 4 Metric Ball End Hex

Interchangeable Blade Ball end works at 30°
angle entry for easy access to fasteners.

Item					
No.	mm	mm	Inch	lbs.	pkg.
28033	1.5	120	4.7	.06	1
28034	2.0	120	4.7	.06	1
28035	2.5	120	4.7	.06	1
28036	3.0	120	4.7	.06	1
28037	4.0	120	4.7	.06	1



280 SYSTEM 4 Inch Ball End Hex

Interchangeable Blade Ball end works at 30°
angle entry for easy access to fasteners.

Item					
No.	Inch	mm	Inch	lbs.	
28021	.050	120	4.7	.06	
28023	1/16	120	4.7	.06	
28024	5/64	120	4.7	.06	
28025	3/32	120	4.7	.06	
28026	7/64	120	4.7	.06	
28027	1/8	120	4.7	.06	
28028	9/64	120	4.7	.06	
28029	5/32	120	4.7	.06	



269 SYSTEM 4 Metric Hex,

Interchangeable Blade High alloy CVM steel,
hardened, corrosion protected.

Item					
No.	mm	mm	Inch	lbs.	
26913	0.7	120	4.7	.06	
26914	0.9	120	4.7	.06	
26915	1.3	120	4.7	.06	
26916	1.5	120	4.7	.06	
26917	2.0	120	4.7	.06	
26918	2.5	120	4.7	.06	
26919	3.0	120	4.7	.06	
26920	4.0	120	4.7	.06	



269 SYSTEM 4 Inch Hex,

Interchangeable Blade High alloy CVM steel,
hardened, corrosion protected.

Item					
No.	Inch	mm	Inch	lbs.	
26921	0.05	120	4.7	.06	
26923	1/16	120	4.7	.06	
26924	5/64	120	4.7	.06	
26925	3/32	120	4.7	.06	
26926	7/64	120	4.7	.06	
26927	1/8	120	4.7	.06	
26928	9/64	120	4.7	.06	
26929	5/32	120	4.7	.06	



26999 9 Pc. Hex Metric Precision Blade Set

Set includes the following blades:

Hex Metric:	0.7, 0.9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
lbs.	.66



26989 9 Pc. Hex Inch Precision Blade Set

Set includes the following blades:

Hex Inch:	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
lbs.	.64

Wiha ESD Safe
Precision Collet
Lock handle
and 8 Wiha
interchangeable
blades

Wiha ESD Safe
Precision Collet
Lock handle
and 8 Wiha
interchangeable
blades

SYSTEM 4 Handles & Micro Bits

Tips
exact fit,
precision
machined

Rotating Cap
for precise
turning and
control

Tapered Handle
allows rapid rotation,
requires less clearance

Bits CVM steel,
hardened

Use bits directly in handle or with 4" bit extension



110mm/4.3" OAL

75800 SYSTEM 4 Standard Precision Bit

Handle with rotating control cap. Tapered, high quality plastic, impact resistant, ball retainer. Accepts all SYSTEM 4 Series bits.

Item	No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06	



110mm/4.3" OAL

75801 SYSTEM 4 ESD Safe Dissipative

Precision Bit Handle with rotating control cap. Tapered, high quality plastic, impact resistant. **Advantages:**

- For working in ESD sensitive applications Surface resistant 10^6 - 10^9 Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item	No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06	



75901 Magnetic Bit Extension Blade For SYSTEM 4 Micro Bits Shaft CVM steel, hardened. Magnetic bit holder.

Item	No.	Size	mm	mm	lbs.
75901	4.0	100	4.0	.04	



75900 Extension Blade For SYSTEM 4 Micro Bits Shaft CVM steel, hardened, corrosion protected. Ball retainer bit extension for 4 mm bits.

Item	No.	Size	mm	mm	lbs.
75900	4.0	100	4.0	.07	



753 SYSTEM 4 Hex Metric Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item	No.	mm	mm	Inch	lbs.
75307	.71	28	1.1	.01	
75309	.89	28	1.1	.01	
75313	1.3	28	1.1	.01	
75315	1.5	28	1.1	.01	
75320	2.0	28	1.1	.01	
75325	2.5	28	1.1	.01	
75330	3.0	28	1.1	.01	
75340	4.0	28	1.1	.01	



753 SYSTEM 4 Hex Inch Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item	No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01	
75309	.035	28	1.1	.01	
75313	.050	28	1.1	.01	
75350	1/16	28	1.1	.01	
75352	5/64	28	1.1	.01	
75354	3/32	28	1.1	.01	
75356	7/64	28	1.1	.01	
75358	1/8	28	1.1	.01	
75360	9/64	28	1.1	.01	
75340	5/32	28	1.1	.01	



753 SYSTEM 4 Metric Security Hex Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item	No.	mm	mm	Inch	lbs.
75322	2.0	28	1.1	.01	
75327	2.5	28	1.1	.01	
75332	3.0	28	1.1	.01	
75342	4.0	28	1.1	.01	



753 SYSTEM 4 Security Hex Inch Bits

High alloy CVM steel, hardened, on 4 mm hex stock.

Item	No.	Inch	mm	Inch	lbs.
75362	5/64	28	1.1	.01	
75364	3/32	28	1.1	.01	
75366	7/64	28	1.1	.01	
75368	1/8	28	1.1	.01	
75370	9/64	28	1.1	.01	
75372	5/32	28	1.1	.01	

Wiha SYSTEM 4 Micro Bits & Compact Bit Sets



75395 18 Piece SYSTEM 4 Hex Inch & Metric Precision Interchangeable Bit Set, In Compact Fold Out Box

Wiha precision handle, bit extension & 16 Wiha interchangeable bits.

Item No. Combination Bit Set

75395 Set with Standard Precision Handle

Set includes the following bits:

- **Hex Metric:** .71, .89, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

• **100mm Bit Extension**

• **lbs.** .58



75096 16 Piece Precision Micro Bit Hex Inch & Metric Sets

ESD Safe precision handle, Bit Extension and 14 CVM steel Micro Bits.

Set includes the following Micro Bits:

- **Inch:** 0.89/0.35", 1.3/.050", 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- **Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

• **lbs.** .14



75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs. Wiha precision storage handle & 6 interchangeable bits.

Item No. Precision Storage Handle Set

75983 • **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8"

• **lbs.** .08

Wiha Cushion Grip Stubby Bit Holder

Stubby 6 in 1 Multi-Bit Driver Sets



[SHOP](#)

38056 Ball End Hex SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

● Ball End Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .21
--	----------



[SHOP](#)

38057 Hex Metric SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

● Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	lbs. .18
--	----------



[SHOP](#)

38058 Hex Inch SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

● Hex Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	lbs. .18
--	----------

Wiha Torque Ratchet Bit Sets

Smooth, high torque, silent ratchet handle

Pistol Grip Handle ergonomic design with free running mechanism. Instant clutch engagement allows constant turning pressure on the fastener.

Hex Retainer for bit holder blades



No release of handle is needed, change of direction can be made with index finger and thumb. **Allows** for quick adjustment to right, left or fixed turning.

Opens a new generation of easier torque transmission



[SHOP](#)

28298 12 Piece Hex Inch Topra Ratchet Bit Set

Set includes Topra Handle, Magnetic bit holder and the following bits:

● Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	lbs. .65
---	----------



[SHOP](#)

28299 10 Piece Hex Metric Topra Ratchet Bit Set

Set includes Topra Handle, Magnetic bit holder and the following bits:

● Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	lbs. .65
--	----------

Wiha Bit Selectors

Compact size and easy bit selection make the Bit Selector an ideal maintenance tool



Plastic storage box is compact, durable and light weight

Slide out drawer allows quick bit access and secure storage



Molded hex cavity in box end Magnetic adapter fits into opening so tool case can be used as a handle on quick fastening jobs

1/4" Magnetic Adapter fits all standard 1/4" bits

792 Sets Bit-Selector Sets

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" magnetic bit holder can be used in power tools. Plastic storage box is compact, durable and light weight. Molded hex cavity turns box into handle for quick fastening jobs. Quick bit access with slide out drawer. Packaged in clear blister pack.



[SHOP](#)

79276 Bit-Selector With Ball End Hex Inch Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:

● Ball End Hex Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	⚖ lbs. .30
--	-----------------------



Item #79246

[SHOP](#)

79246 Bit-Selector With Hex Metric Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

● Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	⚖ lbs. .32
---	-----------------------

79256 Bit-Selector With Hex Metric Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:

● Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	⚖ lbs. .30
--	-----------------------



[SHOP](#)

79266 Bit-Selector With Security Hex Inch Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 9 Bits:

● Hex Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	⚖ lbs. .31
---	-----------------------

Screw Holding



MagicRing



[SHOP](#)

71399 Bit-Selector With Metric & Inch MagicRing Insert 1/4" Bits

Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

● No Ball End	⚖ lbs. .46
Hex Metric: 3.0, 4.0, 5.0, 6.0mm	
Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	

Wiha MagicRing Insert Bits

Screw Holding Hex Bits



[SHOP](#)

713 MagicRing Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
71304	3.0	25	1	.01
71307	4.0	25	1	.01
71310	5.0	25	1	.01
71311	6.0	25	1	.01

713 MagicRing Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71343	1/8	25	1	.01
71346	9/64	25	1	.01
71349	5/32	25	1	.01
71352	3/16	25	1	.01
71354	7/32	25	1	.01
71358	1/4	25	1	.01

[SHOP](#)

Wiha MagicRing Power Bits

Screw Holding Hex Bits



[SHOP](#)

743 MagicRing Metric Power Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
74301	3.0	50	1	.02
74305	4.0	50	1	.02
74307	5.0	50	1	.03
74319	6.0	50	1	.03

743 MagicRing Inch Power Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
74369	1/8	50	1	.02
74371	9/64	50	1	.02
74373	5/32	50	1	.02
74375	3/16	50	1	.03
74377	7/32	50	1	.03
74379	1/4	50	1	.03

[SHOP](#)

Wiha XSelector Bit Sets

Compact size and easy bit selection make the Wiha XSelector an ideal maintenance tool

Easy bit access
with hinged
cover



XSelector Pocket Sized
3-1/8" x 2-1/8" x 1/2"

Sets include Clicfix quick
release holder

794 Sets XSelector Bit Sets

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" Quick Release holder can be used in power tools. Quick bit access through integrated bit-clamp.


[SHOP](#)

79446 XSelector Bit Set With Hex Inch Bits

Set Includes Quick Release Holder
and the following 10 bits:

lbs.
.27

Hex Inch: 1/16, 5/64, 3/32, 7/64,
1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Wiha Security Hex Inch & Metric PokitPaks


[SHOP](#)

71998 PokitPak - Security Hex Inch Insert Bits In Molded Case - Set includes 6 - 1/4" Insert Bits

Inch Security Hex:
3/32, 7/64, 1/8, 9/64, 5/32, 3/16"

lbs.
.12


[SHOP](#)

71995 PokitPak - Security Hex Insert Bits In Molded Case - Set includes 6 - 1/4" Insert Bits

Metric Security Hex:
2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

lbs.
.31

Wiha Power Bit Belt Packs


[SHOP](#)


74986 Power Bit Belt Pack With Inch & Metric Hex Bits

Set includes the following 10 bits:

Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

lbs.
.34

Metric: 3.0, 4.0, 5.0, 6.0mm



Screw Holding
Hex Bits


[SHOP](#)


74989 Power Bit Belt Pack With Screw Holding Hex MagicRing Bits

Set includes the following 10 bits:


Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

lbs.
.34

Metric: 3.0, 4.0, 5.0, 6.0mm



Screw Holding
Hex Bits

[SHOP](#)


74999 Power Bit Belt Pack With Screw Holding Inch & Metric Ball End Hex MagicRing Bits

Set includes the following 10 bits:

Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

lbs.
.37

Metric: 3.0, 4.0, 5.0, 6.0mm

Wiha Security Hex Inch Multi Bit Set


[SHOP](#)

38014 Security Hex Inch Multi-Bit Screwdriver, 6 Pc. Set

With Wiha Powerhandle & CVM steel, hardened shaft.

Set includes the following 1/4" bits:

Security Hex: 3/32, 1/8, 5/32, 3/16, 7/32"

lbs.
.39

Hex Bits

The ideal multi-purpose bits for all around quality & performance

Made in Germany - Production Quality

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual & machine Hardness HRC 59-61



713 Hex Inch Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
71329	.050	25	10	.12	
71326	1/16	25	10	.12	
71328	5/64	25	10	.12	
71330	3/32	25	10	.12	
71333	7/64	25	10	.12	
71336	1/8	25	10	.12	
71339	9/64	25	10	.12	
71342	5/32	25	10	.12	
71345	3/16	25	10	.13	
71348	7/32	25	10	.13	
71351	1/4	25	10	.13	
71353	5/16	25	10	.20	
71356	3/8	25	10	.25	



713 Hex Metric Insert Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
71303	1.5	25	10	.12	
71306	2.0	25	10	.12	
71308	2.5	25	10	.12	
71309	3.0	25	10	.12	
71312	4.0	25	10	.12	
71315	5.0	25	10	.14	
71318	6.0	25	10	.14	
71321	8.0	25	10	.20	
71324	10.0	25	10	.27	

725 Hex Metric Insert Contractor Grade, 1/4"

Item	No.	Size	mm	pkg.	lbs.
72582	2.0	25	30 pc	.85	
72583	2.5	25	30 pc	.85	
72584	3.0	25	30 pc	.85	
72585	4.0	25	30 pc	.85	
72586	5.0	25	30 pc	.85	
72587	6.0	25	30 pc	.85	

Wiha Hex Inch & Metric Insert Bit Packs



713 Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	Inch	mm	lbs.
71359	.050	25	.03	
71360	1/16	25	.03	
71361	5/64	25	.03	
71362	3/32	25	.03	
71363	7/64	25	.03	
71364	1/8	25	.03	
71365	9/64	25	.03	
71366	5/32	25	.04	
71367	3/16	25	.04	
71368	7/32	25	.04	
71369	1/4	25	.04	
71373	5/16	25	.05	
71387	3/8	25	.06	

733 Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	mm	mm	lbs.
73301	1.5	25	.03	
73302	2.0	25	.03	
73303	2.5	25	.03	
73304	3.0	25	.03	
73305	4.0	25	.03	
73306	5.0	25	.03	
73307	6.0	25	.04	
73308	8.0	25	.05	
73309	10.0	25	.06	



71396 Hex Inch Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71396 Set includes the following bits:

Hex Inch:	1/16, 3/32, 1/8, 5/32
wt. .13	3/16, 1/4" x 1" (25mm)

71397 Hex Metric Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71397 Set includes the following bits:

Hex Metric:	2.0, 2.5, 3.0, 4.0, 5.0, 6.0
wt. .21	

Wiha Security Hex Insert Bits



719 Security Hex In Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
71930	5/64	25	10	.12	
71932	3/32	25	10	.12	
71934	7/64	25	10	.12	
71936	1/8	25	10	.12	
71938	9/64	25	10	.12	
71940	5/32	25	10	.12	
71955	3/16	25	10	.13	
71956	7/32	25	10	.14	
71960	1/4	25	10	.15	



719 Security Hex Metric Insert Bits, 1/4"

Item	No.	mm	mm	pkg.	lbs.
71939	2.0	25	10	.12	
71941	2.5	25	10	.12	
71942	3.0	25	10	.12	
71943	4.0	25	10	.12	
71944	5.0	25	10	.15	
71945	6.0	25	10	.15	
71946	8.0	25	10	.20	



719 Security Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	Inch	mm	lbs.
71970	5/64	25	.03	
71971	3/32	25	.03	
71972	7/64	25	.03	
71973	1/8	25	.03	
71974	9/64	25	.03	
71975	5/32	25	.03	
71976	3/16	25	.04	
71977	7/32	25	.04	
71978	1/4	25	.04	

719 Security Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	mm	mm	lbs.
71979	2.0	25	.03	
71980	2.5	25	.03	
71981	3.0	25	.03	
71982	4.0	25	.03	
71983	5.0	25	.04	
71984	6.0	25	.04	
71985	8.0	25	.05	

Wiha Hex Inch & Metric Power Bits



SHOP

743 Hex Inch Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Inch	mm	pkg.	lbs.
74311	3/32	50	10	.30	
74312	7/64	50	10	.30	
74313	1/8	50	10	.30	
74314	9/64	50	10	.30	
74315	5/32	50	10	.30	
74316	3/16	50	10	.30	
74317	7/32	50	10	.30	
74318	1/4	50	10	.30	



SHOP

743 Hex Inch Power Bits

1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Inch	mm	pkg.	lbs.
74341	5/64	70	1	.36	
74342	3/32	70	1	.36	
74343	7/64	70	1	.36	
74344	1/8	70	1	.36	
74345	9/64	70	1	.36	
74346	5/32	70	1	.36	
74347	3/16	70	1	.36	
74348	7/32	70	1	.36	
74349	1/4	70	1	.36	



SHOP

743 Hex Metric Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item	No.	mm	mm	pkg.	lbs.
74325	2.5	50	10	.25	
74330	3.0	50	10	.25	
74340	4.0	50	10	.25	
74350	5.0	50	10	.25	
74360	6.0	50	10	.25	
74380	8.0	50	10	.38	



SHOP

743 Hex Metric Power Bits

1/4" Hex Drive, Length 2.75"/70mm

Item	No.	mm	mm	pkg.	lbs.
74351	2.0	70	1	.36	
74352	2.5	70	1	.36	
74353	3.0	70	1	.36	
74354	4.0	70	1	.36	
74355	5.0	70	1	.36	
74356	6.0	70	1	.36	
74357	8.0	70	1	.36	



SHOP

2 bit pack

743 Hex Inch Power Bit Packs, 2"

Item	No.	Inch	mm	lbs.
74381	3/32	50	.07	
74382	7/64	50	.07	
74383	1/8	50	.07	
74384	9/64	50	.07	
74385	5/32	50	.07	
74386	3/16	50	.07	
74387	7/32	50	.07	
74388	1/4	50	.07	

743 Hex Metric Power Bit Packs, 2"

Item	No.	mm	mm	lbs.
74361	2.5	50	.07	
74362	3.0	50	.07	
74363	4.0	50	.07	
74364	5.0	50	.07	
74365	6.0	50	.07	
74366	8.0	50	.09	

SHOP

Hex Metric Long Insert Bit On 5/16"



SHOP

72388 Hex Metric Bit On 5/16" Stock

Item	No.	mm	mm	pkg.	lbs.
72388	12.0	75	10	.14	

Stainless Steel Hex Metric Bits



SHOP

701 Stainless Steel Hex Metric Insert Bits

Item	No.	mm	mm	pkg.
70170	1.5	25	10	
70171	2.0	25	10	
70172	2.5	25	10	
70173	3.0	25	10	
70174	4.0	25	10	
70175	5.0	25	10	
70176	6.0	25	10	

Wiha Ball End Hex Inch Insert Bits



SHOP

717 Ball End Hex Inch Insert Bits, 1/4"

Item	No.	Inch	mm	pkg.	lbs.
71701	3/32	25	10	.12	
71702	7/64	25	10	.12	
71703	1/8	25	10	.12	
71704	9/64	25	10	.12	
71705	5/32	25	10	.12	
71706	3/16	25	10	.13	
71707	7/32	25	10	.13	
71708	1/4	25	10	.13	



SHOP

2 bit pack

717 Ball End Hex Inch Insert Bit Packs, 1"

Item	No.	Inch	mm	lbs.
71711	3/32	25	.03	
71712	7/64	25	.03	
71713	1/8	25	.03	
71714	9/64	25	.03	
71715	5/32	25	.04	
71716	3/16	25	.04	
71717	7/32	25	.04	
71718	1/4	25	.04	

Ball End Hex Metric Power Bits



SHOP

2 pc. bit pack!

717 Ball End Hex Metric Power Bits

1/4" Hex Drive, Length 1.5"/38mm

Item	No.	mm	mm	pkg.
71719	1.5	38	1	
71720	2.0	38	1	
71721	2.5	38	1	
71722	3.0	38	1	
71723	4.0	38	1	
71724	5.0	38	1	
71725	6.0	38	1	

Wiha Terminator Hex Inch & Metric Impact Bits - Insert & Power

**Up To 30X
Performance Over
Standard
Screwdriver Bits**



Dual material
impact absorbing
torsion zone

Impact rated bits for long life in impact applications

Provide up to 30 times impact performance over standard bits

Standard 1/4" drive - No special adaptor required

Wiha enhanced bi-material torsion zone

Precision machined exact fit tips

Wiha exclusive CVM tool steel

Guaranteed to out perform impact imposters



765 Hex Inch Terminator Impact Bits, 1/4" Insert - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76530	1/8	29	10	
76531	9/64	29	10	
76532	5/32	29	10	
76533	3/16	29	10	
76534	7/32	29	10	
76535	1/4	29	10	

768 Hex Inch Terminator Impact Bits, 1/4" Insert - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76830	1/8	29	2	
76831	9/64	29	2	
76832	5/32	29	2	
76833	3/16	29	2	
76834	7/32	29	2	
76835	1/4	29	2	



765 Hex Metric Terminator Impact Bits, 1/4" Insert - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76523	3.0	29	10	
76524	4.0	29	10	
76525	5.0	29	10	
76526	6.0	29	10	

768 Hex Metric Terminator Impact Bits, 1/4" Insert - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76823	3.0	29	2	
76824	4.0	29	2	
76825	5.0	29	2	
76826	6.0	29	2	



765 Hex Inch Terminator Impact Bits, 1/4" Power - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76570	1/8	49	10	
76571	9/64	49	10	
76572	5/32	49	10	
76573	3/16	49	10	
76574	7/32	49	10	
76575	1/4	49	10	



768 Hex Inch Terminator Impact Bits, 1/4" Power - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76870	1/8	49	2	
76871	9/64	49	2	
76872	5/32	49	2	
76873	3/16	49	2	
76874	7/32	49	2	
76875	1/4	49	2	



765 Hex Metric Terminator Impact Bits, 1/4" Power - 10 bit pack

Item No.	Inch	mm	pkg.	SHOP
76563	3.0	49	10	
76564	4.0	49	10	
76565	5.0	49	10	
76566	6.0	49	10	



768 Hex Metric Terminator Impact Bits, 1/4" Power - 2 bit pack

Item No.	Inch	mm	pkg.	SHOP
76863	3.0	49	2	
76864	4.0	49	2	
76865	5.0	49	2	
76866	6.0	49	2	



76894 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm


76894 Set includes the following bits:

- Hex Inch: 5/32, 3/16, 7/32, 1/4"
- Hex Metric: 4, 5, 6mm



91313 Empty Bit Buddy Case Holds
Terminator Impact Power Bits
91313 Holds 7 Impact Bits

1/4" Drive Insert & Power Bits



**Up To 30X Performance
Over Standard Screwdriver Bits**



76893 7 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76893 Set includes the following bits:

- Hex Inch: 5/32, 3/16, 7/32, 1/4"
- Hex Metric: 4, 5, 6mm



91247 Empty Bit Buddy Case Holds
Terminator Impact Insert Bits
91247 Holds 7 Impact Bits

Wiha Bit Holders

Quick Release



714 ClicFix Bit Holder, Magnetic, For Insert Bits

Item				
No.	Size	Size	mm	Inch
71490	1/4"	1/4"	60	2.4
71491	1/4"	1/4"	75	2.9

Quick Release



714 CentroFix Bit Holder For Power Bits

Item				
No.	Size	Size	mm	Inch
71480	1/4"	1/4"	60	2.3

Wiha Impact Bit Holding Sockets



720 Impact Bit Holding Socket With Retaining Ring

For 1/4" drive bits.

Item				
No.	Bit	mm	Drive	lbs.
72001	1/4	25	1/4"	.05
72002	1/4	30	3/8"	.10
72003	1/4	35	1/2"	.21

72090 3 Piece Bit Holding Socket Set

for use with 1/4" Insert bits

Drive:		lbs.
1/4", 3/8", 1/2"		.40

Long Blade Sockets & Sets



771 Hex Metric Sockets

1/4" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	mm	lbs.
77140	2.5	6.0	.13	
77142	3.0	6.0	.13	
77144	4.0	6.0	.13	
77146	5.0	6.0	.13	
77148	6.0	6.0	.13	

77192 5 Pc. Hex Metric Socket Blade Set

Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm

	lbs. .70
--	----------



Long Blade Sockets & Sets



771 Hex Inch Sockets 1/4" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77128	3/32	6.0	.12	
77130	7/64	6.0	.12	
77132	1/8	6.0	.12	
77134	9/64	6.0	.12	
77136	5/32	6.0	.12	
77138	3/16	6.0	.12	
77139	7/32	6.0	.12	
77141	1/4	6.0	.12	

77191 8 Piece Hex Inch Socket Blade Set

Inch: 3/32, 7/64, 1/8, 9/64, 5/32,

3/16, 7/32, 1/4"  wt. .97



771 Hex Inch Sockets 3/8" Drive 6" Long Bit Socket

Item				
No.	Size	Inch	lbs.	
77165	3/32	6.0	.18	
77167	7/64	6.0	.18	
77169	1/8	6.0	.18	
77171	9/64	6.0	.18	
77173	5/32	6.0	.18	
77175	3/16	6.0	.18	
77177	7/32	6.0	.18	
77179	1/4	6.0	.18	



77198 22 Piece Hex & TORX® Long Blade Socket Set, 1/4" Drive

Inch Hex: 3/32, 7/64, 1/8, 9/64, 5/32,

3/16, 7/32, 1/4"

Metric Hex: 2.5, 3.0, 4.0, 5.0, 6.0mm

TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40

	lbs. 2.82
---	-----------

Wiha Sockets



713 Hex Sockets 1/4" Square drive socket.

Replaceable bit. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
71371	1/16	38	.05	
71370	5/64	38	.05	
71372	3/32	38	.05	
71374	7/64	38	.05	
71376	1/8	38	.05	
71378	9/64	38	.05	
71380	5/32	38	.05	
71382	3/16	38	.05	
71384	7/32	38	.05	
71386	1/4	38	.05	

Wiha Sockets



[SHOP](#)

713 Hex Sockets 3/8" Square drive socket.

Replaceable bit. 1/4" bits CVM tool steel.

Item	No.	Inch	mm	lbs.
71375	1/8	42	.09	
71377	9/64	42	.09	
71379	5/32	42	.09	
71381	3/16	42	.09	
71383	7/32	42	.09	
71385	1/4	42	.09	
71388	5/16	42	.10	
71390	3/8	42	.10	



[SHOP](#)

713 Hex Metric Sockets 1/4" Square drive

socket. Replaceable bit. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
71301	1.5	38	.04	
71302	2.0	38	.04	
71305	2.5	38	.04	
71313	3.0	38	.04	
71314	4.0	38	.04	
71317	5.0	38	.05	
71319	6.0	38	.05	
71327	8.0	38	.05	
71340	10.0	38	.05	



[SHOP](#)

713 Hex Metric Sockets 3/8" Square drive socket.

Replaceable bit. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
71300	2.0	42	.09	
71316	2.5	42	.09	
71341	3.0	42	.09	
71331	4.0	42	.09	
71323	5.0	42	.09	
71325	6.0	42	.09	
71320	8.0	42	.10	
71322	10.0	42	.11	



[SHOP](#)

713 Hex Metric Sockets 3/8" Square drive socket.

Replaceable bit. 5/16" bits CVM steel.

Item	No.	mm	mm	lbs.
71332	12.0	75	.22	



Replaceable bit

[SHOP](#)

761 Security Hex Inch Sockets

3/8" Square drive socket. 1/4" bits CVM steel.

Item	No.	Inch	mm	lbs.
76164	5/64	42	.09	
76165	3/32	42	.09	
76166	7/64	42	.09	
76167	1/8	42	.09	
76168	9/64	42	.09	
76169	5/32	42	.09	
76170	3/16	42	.09	
76171	7/32	42	.09	
76172	1/4	42	.09	

761 Security Hex Metric Sockets

3/8" Square drive socket. 1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
76132	2.0	42	.09	
76133	2.5	42	.09	
76134	3.0	42	.09	
76135	4.0	42	.09	
76136	5.0	42	.09	
76137	6.0	42	.09	
76138	8.0	42	.09	



[SHOP](#)

717 Ball End Hex Sockets 1/4" Square drive socket. Replaceable bit.

1/4" bits CVM steel.

Item	No.	Inch	mm	lbs.
71761	3/32	38	.09	
71762	7/64	38	.09	
71763	1/8	38	.09	
71764	9/64	38	.09	
71765	5/32	38	.09	
71766	3/16	38	.09	
71767	7/32	38	.09	
71768	1/4	38	.09	



[SHOP](#)


717 Ball End Hex Metric Sockets

1/4" Square drive socket. Replaceable bit.

1/4" bits CVM steel.

Item	No.	mm	mm	lbs.
71771	1.5	51	.11	
71772	2.0	51	.11	
71773	2.5	51	.11	
71774	3.0	51	.11	
71775	4.0	51	.11	
71776	5.0	51	.12	
71777	6.0	51	.12	

Wiha Socket Sets On Molded Rails



Bits CVM
tool steel




71391 10 Piece Hex Inch Socket Set

1/4" Square drive replaceable bit socket.

Item No. 

71391 lbs. Set includes the following:

.48 1/16, 5/64, 3/32, 7/64, 1/8
9/64, 5/32, 3/16, 7/32, 1/4"



Bits CVM
tool steel




71798 8 Pc. Ball End Hex Inch Socket Set

1/4" Square Drive Replaceable Bit Socket.

Item No. 

71798 lbs. Set includes the following:

.72 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



Bits CVM
tool steel




71398 7 Pc. Ball End Hex Inch Socket Set

1/4" Square Drive Replaceable Bit Socket.

Item No. 

71398 lbs. Set includes the following:

.48 3/16, 7/32, 1/4"



Bits CVM
tool steel



71797 7 Pc. Ball End Hex Metric Sockets

1/4" Square Drive Replaceable Bit Socket.

Item No. 

71797 lbs. Set includes the following:

.72 3.0, 4.0, 5.0, 6.0mm



Bits CVM
tool steel



71392 8 Piece Hex Inch Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71392 lbs. Set includes the following:

.78 1/4, 5/16, 3/8"

Bits CVM
tool steel



71393 5 Piece Hex Inch Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71393 lbs. Set includes the following:

.54 1/4, 5/16, 3/8"

Bits CVM
tool steel



71394 5 Piece Hex Metric Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71394 lbs. Set includes the following:

.56 8.0, 10.0mm

Bits CVM
tool steel



71996 9 Piece Hex Metric Socket Set


1/4" & 3/8" Sq. Dr. Replaceable Bit Socket

Item No. 

71996 lbs. Set includes the following:

.66 1/4": 1.5, 2.0, 2.5, 3.0, 4.0mm

3/8": 5.0, 6.0, 8.0, 10.0mm



Bits CVM
tool steel



71999 9 Pc. Security Hex Inch Socket Set

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71999 lbs. Set includes the following:

.86 5/64, 3/32, 7/64, 1/8,

9/64, 5/32, 3/16, 7/32, 1/4"



Bits CVM
tool steel



71989 7 Pc. Security Hex Metric Sockets

3/8" Square Drive Replaceable Bit Socket.

Item No. 

71989 lbs. Set includes the following:

.74 2.0, 2.5, 3.0, 4.0, 5.0,

6.0, 8.0mm

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
13650	22	26427	29	27545	26	28547	24	33417	13	35104	19
13651	22	26430	28	27547	26	28548	24	33418	12	35108	19
13652	22	26431	29	27549	26	28549	24	33419	13	35112	19
13653	22	26436	29	27590	26	28550	24	33420	12	35116	19
13654	22	26439	29	27591	26	28551	24	33421	13	35120	19
13655	22	26440	28	28000	30	28552	24	33422	12	35124	19
13656	22	26441	27	28001	30	28553	24	33423	13	35128	19
13657	22	26443	27	28003	29	28554	24	33424	12	35132	19
13658	22	26445	27	28004	29	28555	24	33425	13	35136	19
13659	22	26447	27	28005	29	28556	24	33426	12	35140	19
13662	22	26449	27	28006	29	28557	24	33427	13	35143	19
13663	22	26455	27	28007	29	28558	24	33428	12	35144	19
13664	22	26457	27	28008	29	28559	24	33429	13	35145	19
13665	22	26459	27	28021	30	28560	24	33430	12	35146	19
13666	22	26461	27	28023	30	28587	24	33432	12	35147	19
13667	22	26463	27	28024	30	28588	24	33433	12	35150	19
13668	22	26465	27	28025	30	28916	25	33434	13	35152	19
13669	22	26467	27	28026	30	28917	25	33435	13	35153	19
13670	22	26490	29	28027	30	28918	25	33436	13	35155	19
13671	22	26491	28	28028	30	28919	25	33437	13	35156	19
13672	22	26493	27	28029	30	28920	25	33438	13	35159	19
13673	22	26499	29	28033	30	28921	25	33439	12	35162	19
13690	22	26900	30	28034	30	28922	25	33440	12	35165	19
13691	22	26901	30	28035	30	28923	25	33441	21	35168	19
13693	22	26913	30	28036	30	28924	25	33442	12	35171	19
13694	22	26914	30	28037	30	28931	25	33443	21	35174	19
26307	28	26915	30	28116	23	28933	25	33444	12	35175	19
26309	28	26916	30	28117	23	28935	25	33445	21	35176	19
26313	28	26917	30	28118	23	28937	25	33446	12	35177	19
26315	28	26918	30	28119	23	28938	25	33447	21	35178	19
26316	28	26919	30	28120	23	28939	25	33448	12	35179	19
26320	28	26920	30	28122	23	28940	25	33449	21	35180	19
26323	28	26921	30	28123	23	31805	22	33450	12	35191	19
26325	28	26923	30	28124	23	31807	22	33452	12	35192	19
26327	28	26924	30	28149	23	31809	22	33453	13	35193	19
26330	28	26925	30	28150	23	31811	22	33454	12	35194	19
26331	28	26926	30	28151	23	31813	22	33456	13	35195	17
26333	28	26927	30	28189	23	31815	22	33458	12	35196	17
26336	28	26928	30	28298	32	31817	22	33459	13	35197	17
26340	28	26929	30	28299	32	31890	22	33462	13	35198	17
26341	27	26932	30	28486	23	32302	21	33465	13	35200	18
26343	27	26933	30	28487	23	32303	21	33468	13	35201	18
26345	27	26934	30	28488	23	32304	21	33471	13	35202	18
26347	27	26935	30	28501	24	32305	21	33474	13	35203	18
26349	27	26936	30	28502	24	32306	21	33477	13	35204	18
26351	27	26937	30	28503	24	32308	21	33478	21	35205	18
26353	27	26961	29	28504	24	32366	21	33480	13	35206	18
26363	27	26989	30	28505	24	33401	13	33481	21	35208	18
26367	27	26999	30	28506	24	33402	13	33482	21	35210	18
26369	27	27505	26	28507	24	33403	13	33483	21	35211	18
26371	27	27507	26	28508	24	33404	13	33484	13	35212	18
26390	28	27509	26	28509	24	33405	13	33485	21	35213	18
26391	28	27510	26	28511	24	33406	13	33486	21	35214	18
26392	27	27513	26	28513	24	33407	13	33487	21	35215	18
26393	27	27515	26	28515	24	33408	13	33488	13	35216	18
26399	28	27520	26	28517	24	33409	13	33489	12	35217	18
26413	28	27525	26	28518	24	33410	13	33490	21	35218	18
26415	28	27530	26	28519	24	33411	13	33492	13	35219	18
26416	29	27535	26	28521	24	33412	13	33493	13	35220	18
26419	29	27537	26	28523	24	33413	13	33494	12	35221	18
26420	28	27539	26	28525	24	33414	13	33496	12	35222	18
26423	29	27541	26	28545	24	33415	13	33498	12	35223	18
26425	28	27543	26	28546	24	33416	13	33499	12	35224	18




Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
35225 18	35318 20	36909 9	36990 8	54002 11	66920 4
35226 18	35319 20	36910 9	36991 8	54003 11	66922 6
35227 18	35320 20	36911 7	36992 8	54004 11	66924 4
35228 18	35321 20	36912 8	36993 8	54005 11	66926 6
35230 18	35330 20	36913 7	36995 7	54006 11	66928 4
35231 18	35331 20	36914 7	36996 17	54007 11	66930 6
35232 18	35332 20	36915 7	36997 17	54008 11	66936 4
35233 18	35333 20	36916 8	36998 6	54009 11	66937 6
35234 18	35334 20	36917 7	36999 9	54010 11	66938 6
35235 18	35335 20	36918 7	38014 34	54012 10	66944 4
35236 18	35336 20	36919 7	38056 32	54014 10	66945 4
35237 18	35337 20	36920 8	38057 32	54016 10	66946 4
35238 18	35338 20	36921 7	38058 32	54018 10	66947 4
35239 18	35339 20	36922 7	46701 9	54020 11	66950 4
35240 18	35340 20	36923 9	46702 16	54022 10	66952 4
35241 18	35341 20	36924 8	46703 9	54024 10	66953 4
35242 18	35342 20	36925 9	46704 16	54025 11	66955 4
35243 18	35343 20	36926 9	46705 9	54030 11	66956 4
35244 18	35345 20	36927 9	46706 16	54040 10	66959 4
35245 18	35346 20	36928 8	46707 9	54042 11	66962 4
35246 18	35347 20	36929 9	46708 16	54050 10	66965 4
35247 18	35348 20	36930 9	46709 9	54052 11	66968 4
35248 18	35390 20	36931 9	46710 16	54060 10	66971 4
35249 18	35391 20	36932 9	46711 9	54062 11	66982 7
35250 18	35392 20	36933 9	46712 16	54080 10	66988 7
35251 18	35393 20	36934 9	46713 9	54082 11	66990 4
35252 18	36696 7	36935 9	46714 16	54086 10	66991 4
35253 18	36710 14	36936 8	46715 16	54088 11	66992 4
35254 18	36713 14	36937 9	46716 16	54090 10	66993 6
35255 18	36715 15	36938 9	46717 9	54091 10	66994 6
35256 18	36716 14	36939 9	46718 16	54092 11	66995 6
35257 18	36719 14	36940 6	46719 9	54094 11	66996 7
35258 18	36720 15	36941 6	46720 16	54095 11	66997 17
35259 18	36723 14	36942 6	46721 9	54097 11	66998 6
35260 18	36725 15	36943 6	46722 16	56901 5	70170 36
35261 18	36726 14	36944 8	46723 9	56902 5	70171 36
35270 18	36728 14	36945 8	46724 16	56903 5	70172 36
35280 18	36730 15	36946 8	46725 16	56904 5	70173 36
35282 18	36732 14	36947 8	46726 16	56905 5	70174 36
35284 18	36734 14	36948 6	46727 9	56906 5	70175 36
35285 18	36736 14	36949 6	46728 16	56907 5	70176 36
35286 18	36738 14	36950 8	46730 16	56908 5	71300 39
35288 18	36740 15	36951 6	46731 9	56909 5	71301 39
35290 18	36742 14	36952 8	46732 9	56910 5	71302 39
35291 18	36744 14	36953 8	46733 9	56911 5	71303 35
35295 18	36750 15	36954 6	46734 9	56912 5	71304 33
35297 18	36760 15	36955 8	46735 9	56913 5	71305 39
35301 20	36780 15	36956 8	46736 9	56914 5	71306 35
35302 20	36786 15	36957 6	46737 9	56915 5	71307 33
35303 20	36790 15	36958 6	46738 9	56916 5	71308 35
35304 20	36791 14	36959 8	46739 9	56917 5	71309 35
35305 20	36792 15	36960 6	46740 16	56918 5	71310 33
35306 20	36793 14	36961 6	46741 9	56919 5	71311 33
35307 20	36794 14	36962 8	46750 16	56920 5	71312 35
35308 20	36900 9	36963 6	46760 16	56921 5	71313 39
35309 20	36901 9	36965 8	46780 16	56922 5	71314 39
35310 20	36902 9	36966 9	46786 16	62994 29	71315 35
35311 20	36903 9	36968 8	46793 16	62995 29	71316 39
35312 20	36904 8	36971 8	46794 16	66904 4,6	71317 39
35313 20	36905 9	36986 5	46796 16	66908 4,6	71318 35
35314 20	36906 9	36987 5	46797 16	66912 4,6	71319 39
35316 20	36907 9	36988 7	46799 16	66916 4	71320 39
35317 20	36908 8	36989 9	54001 11	66918 6	71321 35

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
71322 39	71396 35	71970 35	74348 36	75900 31	77132 38
71323 39	71397 35	71971 35	74349 36	75901 31	77134 38
71324 35	71398 40	71972 35	74350 36	75983 31	77136 38
71325 39	71399 33	71973 35	74351 36	76132 39	77138 38
71326 35	71480 38	71974 35	74352 36	76133 39	77139 38
71327 39	71490 38	71975 35	74353 36	76134 39	77140 38
71328 35	71491 38	71976 35	74354 36	76135 39	77141 38
71329 35	71701 36	71977 35	74355 36	76136 39	77142 38
71330 35	71702 36	71978 35	74356 36	76137 39	77144 38
71331 39	71703 36	71979 35	74357 36	76138 39	77146 38
71332 39	71704 36	71980 35	74360 36	76164 39	77148 38
71333 35	71705 36	71981 35	74361 36	76165 39	77165 38
71336 35	71706 36	71982 35	74362 36	76166 39	77167 38
71339 35	71707 36	71983 35	74363 36	76167 39	77169 38
71340 39	71708 36	71984 35	74364 36	76168 39	77171 38
71341 39	71711 36	71985 35	74365 36	76169 39	77173 38
71342 35	71712 36	71989 40	74366 36	76170 39	77175 38
71343 33	71713 36	71995 34	74369 33	76171 39	77177 38
71345 35	71714 36	71996 40	74371 33	76172 39	77179 38
71346 33	71715 36	71998 34	74373 33	76523 37	77191 38
71348 35	71716 36	71999 40	74375 33	76524 37	77192 38
71349 33	71717 36	72001 38	74377 33	76525 37	77198 38
71351 35	71718 36	72002 38	74379 33	76526 37	79246 33
71352 33	71719 36	72003 38	74380 36	76530 37	79256 33
71353 35	71720 36	72090 38	74381 36	76531 37	79266 33
71354 33	71721 36	72388 36	74382 36	76532 37	79276 33
71356 35	71722 36	72582 35	74383 36	76533 37	79446 34
71358 33	71723 36	72583 35	74384 36	76534 37	91118 26
71359 35	71724 36	72584 35	74385 36	76535 37	91247 37
71360 35	71725 36	72585 35	74386 36	76563 37	91313 37
71361 35	71761 39	72586 35	74387 36	76564 37	
71362 35	71762 39	72587 35	74388 36	76565 37	
71363 35	71763 39	73301 35	74986 34	76566 37	
71364 35	71764 39	73302 35	74989 34	76570 37	
71365 35	71765 39	73303 35	74999 34	76571 37	
71366 35	71766 39	73304 35	75096 31	76572 37	
71367 35	71767 39	73305 35	75307 31	76573 37	
71368 35	71768 39	73306 35	75309 31	76574 37	
71369 35	71771 39	73307 35	75313 31	76575 37	
71370 38	71772 39	73308 35	75315 31	76823 37	
71371 38	71773 39	73309 35	75320 31	76824 37	
71372 38	71774 39	74301 33	75322 31	76825 37	
71373 35	71775 39	74305 33	75325 31	76826 37	
71374 38	71776 39	74307 33	75327 31	76830 37	
71375 39	71777 39	74311 36	75330 31	76831 37	
71376 38	71797 40	74312 36	75332 31	76832 37	
71377 39	71798 40	74313 36	75340 31	76833 37	
71378 38	71930 35	74314 36	75342 31	76834 37	
71379 39	71932 35	74315 36	75350 31	76835 37	
71380 38	71934 35	74316 36	75352 31	76863 37	
71381 39	71936 35	74317 36	75354 31	76864 37	
71382 38	71938 35	74318 36	75356 31	76865 37	
71383 39	71939 35	74319 33	75358 31	76866 37	
71384 38	71940 35	74325 36	75360 31	76870 37	
71385 39	71941 35	74330 36	75362 31	76871 37	
71386 38	71942 35	74340 36	75364 31	76872 37	
71387 35	71943 35	74341 36	75366 31	76873 37	
71388 39	71944 35	74342 36	75368 31	76874 37	
71390 39	71945 35	74343 36	75370 31	76875 37	
71391 40	71946 35	74344 36	75372 31	76893 37	
71392 40	71955 35	74345 36	75395 31	76894 37	
71393 40	71956 35	74346 36	75800 31	77128 38	
71394 40	71960 35	74347 36	75801 31	77130 38	

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wihatools.com
 www.wihatools.com

**SEE OUR GREAT
 WEB SPECIALS!**



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:


Catalog Item No. 99934.wo
 version - 5/15/14

Subject to change
 without notice

©2014 Willi Hahn Corporation




91330.wo - Tooling Catalog



99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99002.wo - Screwdrivers Catalog



99919.wo - Insulated Catalog



99001.wo - TorqueControl Catalog



99945.wo - ESD Safe Catalog



99951.wo - Bits Catalog



99977.wo - Pliers/Crimpers Catalog



99006.wo - Tech Tools Catalog