



13			12		11		10		9		8		7		6		5		4		3		2		1					
PACKAGING SEE NOTE 4 SHT 1			4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK			
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES			
			DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)			
			PLATING				150 TIN				15 GOLD				30 GOLD				30 GOLD				15 GOLD				30 GOLD			
			DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)			
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS			
	MM	IN	MM	IN																										
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A		015-91-0048	015-91-5049	04													
06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A		015-91-0068	015-91-5069	06													
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088		015-91-0088	015-91-5089	08													
10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108		015-91-0108	015-91-5109	10													
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128		015-91-0128	015-91-5129	12													
14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148		015-91-0148	015-91-5149	14													
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168		015-91-0168	015-91-5169	16													
18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188		015-91-0188	015-91-5189	18													
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208		015-91-0208	015-91-5209	20													
22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228		015-91-0228	015-91-5229	22													
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248		015-91-0248	015-91-5249	24													
26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268		015-91-0268	015-91-5269	26													
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288		015-91-0288	015-91-5289	28													
30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308		015-91-0308	015-91-5309	30													
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328		015-91-0328	015-91-5329	32													
34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348		015-91-0348	015-91-5349	34													
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368		015-91-0368	015-91-5369	36													
38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388		015-91-0388	015-91-5389	38													
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408		015-91-0408	015-91-5409	40													
42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428		015-91-0428	015-91-5429	42													
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448		015-91-0448	015-91-5449	44													
46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468		015-91-0468	015-91-5469	46													
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488		015-91-0488	015-91-5489	48													
50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508		015-91-0508	015-91-5509	50													
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528		015-91-0528	015-91-5529	52													
54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548		015-91-0548	015-91-5549	54													
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568		015-91-0568	015-91-5569	56													
58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588		015-91-0588	015-91-5589	58													
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608		015-91-0608	015-91-5609	60													
62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620		015-91-3626	015-91-3620		015-91-3628		015-91-0628	015-91-5629	62													
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648		015-91-0648	015-91-5649	64													
66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660		015-91-3666	015-91-3660		015-91-3668		015-91-0668	015-91-5669	66													
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688		015-91-0688	015-91-5689	68													
70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700		015-91-3706	015-91-3700		015-91-3708		015-91-0708	015-91-5709	70													
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728		015-91-0728	015-91-5729	72													
74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740		015-91-3746	015-91-3740		015-91-3748		015-91-0748	015-91-5749	74													
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768		015-91-0768	015-91-5769	76													
78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780		015-91-3786	015-91-3780		015-91-3788		015-91-0788	015-91-5789	78													
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808		015-91-0808	015-91-5809	80													
82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182		71308-0582	71308-0282		71308-0682		71308-1182	71308-1282	82													
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684		71308-1184	71308-1284	84													
86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186		71308-0586	71308-0286		71308-0686		71308-1186	71308-1286	86													
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688		71308-1188	71308-1288	88													
90	114.30	4.500	11																											

13		12		11				10		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE												BULK / IN TUBES										J	
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK					
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES					
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)					
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN					
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)					
I		CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER					EDP NUMBER	EDP NUMBER	CKTS										
			MM	IN	MM	IN																			
		04	5.08	.200	2.54	.100									04										
		06	7.62	.300	5.08	.200		015-91-6068							06										
		08	10.16	.400	7.62	.300		015-91-6088							08										
		10	12.70	.500	10.16	.400		015-91-6108					713088010	71308-8210	10										
		12	15.24	.600	12.70	.500									12										
H		14	17.78	.700	15.24	.600	015-91-6148								14										
		16	20.32	.800	17.78	.700							713088016		16										
		18	22.86	.900	20.32	.800									18										
		20	25.40	1.000	22.86	.900									20										
		22	27.94	1.100	25.40	1.000									22										
		24	30.48	1.200	27.94	1.100									24										
		26	33.02	1.300	30.48	1.200									26										
G		28	35.56	1.400	33.02	1.300									28										
		30	38.10	1.500	35.56	1.400									30										
		32	40.64	1.600	38.10	1.500									32										
		34	43.18	1.700	40.64	1.600									34										
		36	45.72	1.800	43.18	1.700									36										
		38	48.26	1.900	45.72	1.800									38										
		40	50.80	2.000	48.26	1.900									40										
		42	53.34	2.100	50.80	2.000									42										
F		44	55.88	2.200	53.34	2.100									44										
		46	58.42	2.300	55.88	2.200									46										
		48	60.96	2.400	58.42	2.300									48										
		50	63.50	2.500	60.96	2.400									50										
		52	66.04	2.600	63.50	2.500									52										
		54	68.58	2.700	66.04	2.600									54										
		56	71.12	2.800	68.58	2.700									56										
E		58	73.66	2.900	71.12	2.800									58										
		60	76.20	3.000	73.66	2.900									60										
		62	78.74	3.100	76.20	3.000									62										
		64	81.28	3.200	78.74	3.100									64										
		66	83.82	3.300	81.28	3.200									66										
		68	86.36	3.400	83.82	3.300									68										
		70	88.90	3.500	86.36	3.400									70										
		72	91.44	3.600	88.90	3.500									72										
D		74	93.98	3.700	91.44	3.600									74										
		76	96.52	3.800	93.98	3.700									76										
		78	99.06	3.900	96.52	3.800									78										
		80	101.60	4.000	99.06	3.900									80										
		82	104.14	4.100	101.60	4.000									82										
		84	106.68	4.200	104.14	4.100									84										
		86	109.22	4.300	106.68	4.200									86										
C		88	111.76	4.400	109.22	4.300									88										
		90	114.30	4.500	111.76	4.400									90										
		92	116.84	4.600	114.30	4.500									92										
		94	119.38	4.700	116.84	4.600									94										
		96	121.92	4.800	119.38	4.700									96										
		98	124.46	4.900	121.92	4.800									98										
		100	127.00	5.000	124.46	4.900									100										
B		NO PEG VERSION										QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION			
																MM/IN				INCH					
A		(ALSO SEE SHEET 2)										REV		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO.		SHEET NO.					
														C		SEE TABLE		SD-71308-001		3 OF 6					
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1	

13			12		11		10		9		8		7		6		5		4		3		2		1				
			PACKAGING SEE NOTE 4 SHT 1			4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK					
						10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES					
						DIM. M ±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)		8.13 (.320)		8.13 (.320)			
						PLATING				150 TIN				15 GOLD				30 GOLD				150 TIN		15 GOLD		30 GOLD			
						DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)		4.57 (.180)		4.57 (.180)			
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS				
	MM	IN	MM	IN	MM	IN																							
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040			04											
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060			06											
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080			08											
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100			10											
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120			12											
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140			14											
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160			16											
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180			18											
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200			20											
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220			22											
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240			24											
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260			26											
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280			28											
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300			30											
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320			32											
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340			34											
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360			36											
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380			38											
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400			40											
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420			42											
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440			44											
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460			46											
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480			48											
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500			50											
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520			52											
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540			54											
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560			56											
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580			58											
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600			60											
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620			62											
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640			64											
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660			66											
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680			68											
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700			70											
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720			72											
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740			74											
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760			76											
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780			78											
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800			80											
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282			82											
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284			84											
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286			86											
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288			88											
90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290			90											
92	116.84	4.600	114.30	4.500	111.76	4.400	71308-4092		71308-4192		71308-4292		71308-5092	71308-5192	71308-5292			92											
94	119.38	4.700	116.84	4.600	114.30	4.500	71308-4094		71308-4194		71308-4294		71308-5094	71308-5194	71308-5294			94											
96	121.92	4.800	119.38	4.700	116.84	4.600	71308-4096		71308-4196		71308-4296		71308-5096	71308-5196	71308-5296			96											
98	124.46	4.900	121.92	4.800	119.38	4.700	71308-4098		71308-4198		71308-4298		71308-5098	71308-5198	71308-5298			98											
100	127.00	5.000	124.46	4.900	121.92	4.800	71308-4100		71308-4200		71308-4300		71308-5100	71308-5200	71308-5300			100											

[illegible]

		13		12		11		10		9		8		7		6		5		4		3		2		1																	
J		PEG OPTION																										J															
		NO PEG VERSION														NO PEG VERSION				LONG PEG VERSION (.130")				SHORT PEG VERSION (.055")																			
		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A				4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		BULK		TAPE-N-REEL W/VAC CAPS		BULK				BULK		TAPE-N-REEL W/ VAC CAPS											
				8-100 CKT		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES				BULK		TAPE-N-REEL W/ VAC CAPS											
		DIM. M±0.25 MM										6.10 (.240)														8.13(.320)				13.59(.535)				6.10(.240)				8.13(.320)				6.10 (.240)	
PLATING										59 TIN														59 TIN				59 TIN				59 TIN				59 TIN							
DIM. H										2.54(.100)														4.57(.180)				4.57(.180)				2.54(.100)				2.54(.100)							
I		CKTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS											
		MM	IN	MM	IN	MM	IN																																				
H		04	5.08	.200	2.54	.100	---	---	71308-5404	71308-5504	N/A																	04															
		06	7.62	.300	5.08	.200	2.54	.100	71308-5406	71308-5506	N/A																	06															
		08	10.16	.400	7.62	.300	5.08	.200	71308-5408	71308-5508	71308-5608																	08															
		10	12.70	.500	10.16	.400	7.62	.300	71308-5410	71308-5510	71308-5610																	10															
		12	15.24	.600	12.70	.500	10.16	.400	71308-5412	71308-5512	71308-5612																	12															
		14	17.78	.700	15.24	.600	12.70	.500	71308-5414	71308-5514	71308-5614																	14															
		16	20.32	.800	17.78	.700	15.24	.600	71308-5416	71308-5516	71308-5616																	16															
		18	22.86	.900	20.32	.800	17.78	.700	71308-5418		71308-5618																	18															
		20	25.40	1.000	22.86	.900	20.32	.800	71308-5420	71308-5520	71308-5620																	20															
		22	27.94	1.100	25.40	1.000	22.86	.900	71308-5422		71308-5622																	22															
G		24	30.48	1.200	27.94	1.100	25.40	1.000	71308-5424		71308-5624	71308-5724	71308-5824	71308-6424	71308-6624																	24											
		26	33.02	1.300	30.48	1.200	27.94	1.100	71308-5426		71308-5626																	26															
		28	35.56	1.400	33.02	1.300	30.48	1.200	71308-5428		71308-5628																	28															
		30	38.10	1.500	35.56	1.400	33.02	1.300	71308-5430		71308-5630																	30															
		32	40.64	1.600	38.10	1.500	35.56	1.400	71308-5432		71308-5632																	32															
		34	43.18	1.700	40.64	1.600	38.10	1.500	71308-5434		71308-5634																	34															
		36	45.72	1.800	43.18	1.700	40.64	1.600	71308-5436		71308-5636																	36															
		38	48.26	1.900	45.72	1.800	43.18	1.700	71308-5438		71308-5638																	38															
		40	50.80	2.000	48.26	1.900	45.72	1.800	71308-5440	71308-5540	71308-5640																	40															
		42	53.34	2.100	50.80	2.000	48.26	1.900	71308-5442		71308-5642																	42															
F		44	55.88	2.200	53.34	2.100	50.80	2.000	71308-5444		71308-5644																	44															
		46	58.42	2.300	55.88	2.200	53.34	2.100	71308-5446		71308-5646																	46															
		48	60.96	2.400	58.42	2.300	55.88	2.200	71308-5448		71308-5648																	48															
		50	63.50	2.500	60.96	2.400	58.42	2.300	71308-5450	71308-5550	71308-5650																	50															
		52	66.04	2.600	63.50	2.500	60.96	2.400	71308-5452		71308-5652																	52															
		54	68.58	2.700	66.04	2.600	63.50	2.500	71308-5454		71308-5654																	54															
		56	71.12	2.800	68.58	2.700	66.04	2.600	71308-5456		71308-5656																	56															
		58	73.66	2.900	71.12	2.800	68.58	2.700	71308-5458		71308-5658																	58															
		60	76.20	3.000	73.66	2.900	71.12	2.800	71308-5460		71308-5660																	60															
		62	78.74	3.100	76.20	3.000	73.66	2.900	71308-5462		71308-5662																	62															
E		64	81.28	3.200	78.74	3.100	76.20	3.000	71308-5464		71308-5664																	64															
		66	83.82	3.300	81.28	3.200	78.74	3.100	71308-5466		71308-5666																	66															
		68	86.36	3.400	83.82	3.300	81.28	3.200	71308-5468		71308-5668																	68															
		70	88.90	3.500	86.36	3.400	83.82	3.300	71308-5470		71308-5670																	70															
		72	91.44	3.600	88.90	3.500	86.36	3.400	71308-5472		71308-5672																	72															
		74	93.98	3.700	91.44	3.600	88.90	3.500	71308-5474		71308-5674																	74															
		76	96.52	3.800	93.98	3.700	91.44	3.600	71308-5476		71308-5676																	76															
		78	99.06	3.900	96.52	3.800	93.98	3.700	71308-5478		71308-5678																	78															
		80	101.60	4.000	99.06	3.900	96.52	3.800	71308-5480		71308-5680																	80															
		82	104.14	4.100	101.60	4.000	99.06	3.900	71308-5482		71308-5682																	82															
D		84	106.68	4.200	104.14	4.100	101.60	4.000	71308-5484		71308-5684																	84															
		86	109.22	4.300	106.68	4.200	104.14	4.100	71308-5486		71308-5686																	86															
		88	111.76	4.400	109.22	4.300	106.68	4.200	71308-5488		71308-5688																	88															
		90	114.30	4.500	111.76	4.400	109.22	4.300	71308-5490		71308-5690																	90															
		92	116.84	4.600	114.30	4.500	111.76	4.400	71308-5492		71308-5692																	92															
		94	119.38	4.700	116.84	4.600	114.30	4.500	71308-5494		71308-5694																	94															
		96	121.92	4.800	119.38	4.700	116.84	4.600	71308-5496		71308-5696																	96															
		98	124.46	4.900	121.92	4.800	119.38	4.700	71308-5498		71308-5698																	98															
		100	127.00	5.000	124.46	4.900	121.92	4.800	71308-5500		71308-5700																	100															
		B		59 TIN PLATE ASSEMBLIES										SEE SHEET 1 EC NO: UCP2014-0809 DRWN:MKIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE				SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION													
mm																		INCH		MM/IN				DRAWN BY		DATE		TITLE															
4 PLACES ± ---																		± ---		KMS				1999/10/15		SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100 molex																	
3 PLACES ± ---																		± .005		KMS				DATE																			
2 PLACES ± 0.13																		± .010		KMS				DATE																			
A		1 PLACE ± 0.25		± ---		KMS				DATE		SD-71308-001		SHEET NO.																													
		0 PLACE ± ---		± ---		KMS				DATE		6 OF 6																															
		ANGULAR ±1/2°				MATERIAL NO.				DOCUMENT NO.																																	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																					
		K5		REV																																							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-91-1368