








Dimensions: mm (In.)



101-0162-EV



101-0262-EV



PCB Hole Layout

Electrical Specifications:

- Rating: 50mA/12VDC
- Insulation resistance: >100MΩ 250VDC
- Dielectric Strength: 250VAC 1 minute
- Contact resistance: <100mΩ
- Electrical life: 300,000 cycles

Mechanical Specifications:

- Temperature: -25°C ~ +70°C
- Operating force: 130 ±50gf
- Mechanical life: 500,000 cycles

Material:

- Contact: phosphor bronze plated silver

Note:

- H: 169" (101-0162-EV), .197" (101-0262-EV)
- RoHS Compliant

Tactile Switches (Thru-Hole)
101-0162-EV, 101-0262-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[101-0162-EV](#) [101-0262-EV](#)