




Specification :

Material :

1. Plastic Housing : ABS, UL94V-0.
2. RJ45 Housing : PBT, UL94V-0.
3. RJ45 Contact material & finished :
 - 3-1. Phosphor Bronze with 30-40 micro-inch Nickel plated.
 - 3-2. Contact area : Min. 3mm 50 micro-inch Gold plated.


Performance :

- a. The sticker color codes combine two wirings of T568A & T568B.
- b. Insertion Force : 900 gms for 8 contacts.
- c. Retention Strength : 7.7 kgs between Jack and Plug.
- d. Operation Temperature : -40°C to 80°C.
- e. Durability :
 - e-1. Jack : 750 cycles Plug-Jack mating and unmating test, Insertion cycles at 20 cycles/minute max. Contact resistance test per 100 cycles.

Remark : JE315- / XX
(1)

- (1) XX Plastic Color
 WH=White BK=Black
 GN=Green RD=Red
 OR=Orange

RoHS Compliant

	DSGN	CSQ	21.MAY.2007	ITEM NO: 4261
	CHK	Maer	21.MAY.2007	
UNIT M/M	APPR	Yty	21.MAY.2007	Unshield In-line Coupler
SCALE 1/1				
DWG NO: 4261	Videk Ltd			