


DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

BS,A , 200173,009,03

REV.	DATE	DESCRIPTION	BY	C'K'D'
01	12-02-96	CONVERSION ME10	NIETVELT	
02	29-08-97	B-SYMBOL DELETED	NIETVELT	
03	12.06.98	Material Note corrected	S.V.D.	



MATERIAL :

BODY : POLYAMIDE 6.6 ; COLOUR : BLACK
CONTACTS : BRASS


PERFORMANCE CHARACTERISTICS :

OPERATING TEMPERATURE : -55°C TO +105°C
INSULATING RESISTANCE : 5000M Ω MIN.
TEST POTENTIAL : 2000 VAC
CURRENT RATING : 5 AMPS

NOTES :

CONNECTOR SUPPLIED FULLY LOADED
WITH MACHINED MALE CONTACTS.
MATING PART : SMS10P3
*PLATING INDICATION : SEE SHEET 001.

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90	
INT. ST.	10 11	12 13	14 18 20	31 32	33 34	38 39	40 42	43 44	45 46	48 56	70 72	73 75	76 81	82 83	84 88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR.	DATE	SIGN.	QIKMATE STRAIGHT PINHEADER 10MALE DIPSOLDER CTS.		
	DRAFT	06.06.86	E. CREELLE	CAT. No. SMS10PHGE42*		
	CHECKED			 SOURIAU Connection Technology SOURIAU Route Nationale 23 72470 CHAMPAGNE SCALE 2 / 1		
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	PROD. MGR.					
PR.ENG.MGR.						
PR.MGT.MGR.				BS,A , 200173,009,03 DRAWING NR. CUSTOMER DRAWING		
REFERENCES / REFERENTIES						
ALL DIMENSIONS IN MM 				NOTEXPORT CONTROLLED		
ALLE AFMETINGEN IN MM						