




THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.4	W
MAX INPUT POWER	0.8	W
IMPEDANCE	8±15%	OHM
OUTPUT SPL @ 0.4W/10 cm (AT 10 kHz)	70	dBA
DISTORTION	10%	—
RESONANT FREQUENCY	1,200±200	Hz
FREQUENCY RANGE	1,200 ~ 6,000	Hz
HOUSING MATERIAL	ABS	—
CONE MATERIAL	STAINLESS STEEL	—
MAGNET MATERIAL	FERRITE	—
OPERATING TEMPERATURE	-20 ~ +55	°C
WEIGHT	8	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	5/8/02	
A	REVISED TO NEW TEMPLATE	4/15/04	R. W.



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS,
TOLERANCES ARE ±0.5 AND ANGLES ARE
±3°.



projects®
unlimited

Dayton , Ohio

APPROVALS DATE

DRAWN *RABL* 5/02

APPROVED *S.J.* 5/02

DO NOT SCALE DRAWING

SIZE
A

DYNAMIC SPEAKER
FS-40R-8-OHM

DRAWING NO.
FS-40R-8-OHM

SCALE: N.T.S.

SHEET 1 OF 1

FILE NAME
FS-40R-8-OHM.DWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[FS-40R](#)