

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


E

REV / 0L20-0282-97

13JAN98


ME

SB



1. STAMP AMP 16-14 APPROX AS SHOWN
2. WIRE INSUL DIA, 3.05-4.32 [.120-.170]
3. TONGUE MATL THK, 0.79±0.05 [.031±.002]

1000	LOOSE PIECE	322341
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 649°C [1200°F]	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN L OLMEDA 100CT94	AMP AMP Incorporated Harrisburg, PA 17105-3608					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [in]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M ELLIS 100CT94						
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: - -		0 PLC ±- 1 PLC ±- 2 PLC ±0.20 [.008] 3 PLC ±- 4 PLC ±- ANGLES ±-	APVD S BORTNER 100CT94	NAME TERMINAL, RING TONGUE, STRATOTHERM, DIAMOND GRIP, WIRE SIZE, 16-14 AWG					
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 1.04mm² -2.62mm² [2050-5180]			MATERIAL BODY, NI PER ASTM B162 SLEEVE, NI SIL PER ASTM B122				FINISH -	PRODUCT SPEC -	APPLICATION SPEC -
STRANDED WIRE			CUSTOMER DRAWING			SIZE A3	CAGE CODE 00779	DRAWING NO C-322341	SCALE 4:1	SHEET 1 OF 1	REV E

AMP 1470-19 REV 09MAY94