

Electrical

CONTACT TYPE:

CONTACT RATING:

SWITCHING VOLTAGE, MAX.

SWITCHING CURRENT, MAX.

CARRY CURRENT, MAX.

CONTACT RESISTANCE INCLUDING LEADS, MAX.

BREAKDOWN VOLTAGE, MIN.

FORM C

5 WATTS

175 VDC

0.25 AMPS

1.5 AMPS

220 mΩ (N.O.)

220 mΩ (N.C.)

200 VDC

Physical

CAPSULE:

CHL DYE:
POTTING:
BLACK EPOXY
BLACK EPOXY
BLACK EPOXY

LEADS:
WIRE PVC 24
SERIAL 11001

ACTUATOR:

ACTUATE DISTANCE:

DEACTUATE DISTANCE:

BLACK UL94V-0 POLYESTER



BLACK EPOXY

WIRE PVC 24 AWG 7/32 UL1569

WILLIAM T. VANCE
57030-0000

57030-000
.150" MIN.

MIN. 100" MAX. 800"



Print Detail



BLACK (N.O.)
WHITE (COM.)
BLUE (N.C.)

— NO ORDER

— STRIPPED
— NOT TINNED

- NO ORDER

WHITE (COM.

BLUE (N.C.)

BLUE (N.C.)

STRIPPED
NOT TINNED

✓.245 DIA.
MAX.

* 100-1

DIMENSIONS ARE IN INCHES
TOLERANCES: ±.010 UNLESS NOTED
* KEY ASSEMBLY DIMENSIONS

59030-030 SENSOR										Hamlin Breed Electronics Limited Partnership				DCR No. 1243	
AI	UPDATE/FROMAT		A9433		BJW	2/15/02		BJW	3/13/02		Dwn.	DRR	DATE 5/2/88		D10-59030-030 Page 1 of 1
REV.	DESCRIPTION OF REVISION		DCR No.		BY	DATE		APP.	DATE		App'd	DRR	DATE 5/11/88		