


3.0X2.5mm BI-COLOR SURFACE MOUNT LED



UNIT : MM[INCH]

TOLERANCE : $\pm 0.2[\pm 0.0079]$ UNLESS OTHERWISE NOTED.

Dice	Condition	Peak Emission Wavelength			UNIT
		Min.	Typ.	Max.	
HYPER RED (InGaAlP)	$I_F = 20\text{mA}$	-	640	-	nm
SUPER BRIGHT GREEN (GaP)	$I_F = 20\text{mA}$	-	565	-	nm

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @20mA		Viewing Angle
			Min.	Typ.	2θ 1/2
APB3025SURKSGC	HYPER RED (InGaAlP)	WATER CLEAR	40	100	120°
	SUPER BRIGHT GREEN (GaP)		3	12	

APPROVED:

J. Lu

CHECKED:

J. Chao

DRAWN :

L.N. Sheu

SCALE :

12 : 1

DATA NO. : F7339

V.1

DATE : JUL/26/2000