


## Metal Keypad




## General Specification

|                            |                                                               |
|----------------------------|---------------------------------------------------------------|
| Contact rating             | : 20 mA, 24 V dc                                              |
| LED contact rating         | : $V_{\max} = 4 \text{ V}$ , $V_{\text{nom}} = 3.5 \text{ V}$ |
| Maximum contact resistance | : 200 ohms                                                    |
| Life                       | : 2,000,000 cycles per key                                    |
| Operating temperature      | : -20°C to +60°C                                              |
| Storage temperature        | : -40°C to +65°C                                              |

### Circuit Diagram



Stroke :  $1.4 \pm 0.4$  mm

| Description                                      | Part Number          |
|--------------------------------------------------|----------------------|
| Keypad, Metal, Illum Blue, IP67, 3 × 4           | MCAK304NSSLWPMMBLGKT |
| Keypad, Metal, Illum Yellow / Green, IP67, 3 × 4 | MCAK304NSSLWPMMYLGKT |

**www.element14.com**  
**www.farnell.com**  
**www.newark.com**