



Sample photo

Order symbol: CAB ABS 303018 T3B
Product nbr: 8183042
Description: Cabinet, ABS
Remarks: Lock on the long side

EAN: 6418074020192
El. number:
 Finland 3424361
 Denmark 8212019030
 Italy 7812030
 Sweden 2540039

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			
	L	W	H
mm:	300	300	180
inch:	11.8	11.8	7.1
Materials:			
Material:	ABS		
Base colour:	RAL 7035		
Cover colour:	Smoked grey		
Gasket material:	EPDM		
Temperatures:			
Short term:	-40 ... 80 °C		
Continuous:	-40 ... 60 °C		
Short term:	-40 ... 175 °F		
Continuous:	-40 ... 140 °F		
Accessories:			
EKIV 33	Mounting plate		
EKIV 27	DIN-35 Mounting rail		
FP A 33	Swing-out door, aluminium		
FP 33	Front plate		
FP 12-33	Front Plate		
FP 12x2-33	Front Plate		
DRF 33	DIN rail frame set		

Rating:
Ingress Protection (EN 60529): IP 65
Impact Resistance (EN 50102): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 12, 13
Certificates:
Fimko
Europe EN 50298 1998
Gost R

