

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Spirit Levels
Catalogue number	3494, 3482 & 3493
Date	16/04/2010

Range Description Spirit Levels		 		
Features 3494 • Powder coated aluminium box section construction – strong, light and durable • Virtually unbreakable vials - guaranteed leak proof for three years • Luminous horizontal vial – for low light conditions • High accuracy for overhead and normal measuring positions • Shockproof for rugged conditions • Metric measurement graduations (up to 1000mm) • 2 plumb and 1 level vial on all sizes above 600mm • Hanging hole provided for storage • Display packed 3482 • Robust plastic construction – strong and durable • Vertical and horizontal vials – for convenience • Magnetic base – convenient for steelwork • The removable mini level also has a magnetic base and can be used as a line level • Display packed :				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3494 16	Aluminium Spirit Level 400mm 16"	5013969327502	82055910	30
T3494 24	Aluminium Spirit Level 600mm 24"	5013969327601	82055910	30
T3494 32	Aluminium Spirit Level 800mm 32"	5013969327708	82055910	30
T3494 40	Aluminium Spirit Level 1000mm 40"	5013969327809	82055910	30
T3494 48	Aluminium Spirit Level 1200mm 48"	5013969327908	82055910	10
T3494 70	Aluminium Spirit Level 1800mm 70"	5013969700152	82055910	10
T3482	Pocket Level 210mm 8 1/4"	5013969418637	82055910	5

Technical product information	Accuracy 3494 - (all sizes) +/-0.5mm per Meter 3482 - +/-1mm per Meter
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	3494 – Germany 3482 – UK 3493 – Taiwan

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3494 16	50	22	405	248	50	22	405	252
T3494 24	50	22	605	390	50	22	605	395
T3494 32	50	22	805	530	50	22	805	535
T3494 40	50	22	1005	595	50	22	1005	604
T3494 48	50	22	1205	756	50	22	1205	766
T3494 70	50	22	1805	1001	50	22	1805	1012
T3482	45	13	210	98	75	20	290	115

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3494 16	155	420	240	7752		
T3494 24	155	625	240	12105		
T3494 32	155	820	240	16379		
T3494 40	155	1015	240	18517		
T3494 48	107	1220	125	7938		

T3494 70	100	1810	120	10480		
T3482	150	320	85	649		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3494 16	4	Wrap					195	Box
T3494 24	5	Wrap					255	Box
T3494 32	5	Wrap					329	Box
T3494 40	9	Wrap					397	Box
T3494 48	10	Wrap					278	Box
T3494 70	11	Wrap					380	Box
T3482	9	Blister	8	Backing card			74	Box