


Part Number : PRA 240/30

Proximity Switch - Reed Switch based

Cylindrical - Normally Open Contacts - Suggested Magnet: PRM

Product Data Sheet

PICTURE	DIMENSIONS	Applications Include
		• Position and limit sensing. • Linear actuators . • Security system switch. • Door Switch.
		Options
		• Also available in all Black. • Custom cable lengths, strip lengths, cable types, terminations. • If you do not see what you need, just ask, as there is a strong possibility we can do it !
		Drawings not to scale All dimensions in mm(inches) nominal

SPECIFICATION	
Contact Form / Style	Normally Open
Switching Capacity (Resistive)	10 W/VA Max.
Switching Voltage	400 VAC Max.
Switching Current	0.5 A. Max.
Carry Current	1.0 A. Max.
Breakdown Voltage	600 VDC Min.
Contact Resistance	150 mOhms Max.
Switching Distance	5 mm Min.
Operating Temperature Range	-20°C +85°C
Storage temperature	-25°C +90°C
Case Material	Blue Nylon 66
Cable	2 x Round 0.14mm ² PVC covered Grey and insulated Brown / White

Did you know we also sell?						
						
Float Switches	Magnets	Movement Sensors	Tilt / Tip Switches	Acceleration / Shock Switches	Reed Relays	Solid State Relays

Rev. No.	Revision Note	Date	Signature
2	Datasheet Redesign	28-07-06	LG