

LOC	DIST	REVISIONS				JR/MS		
G	14	P	LTR	DESCRIPTION		DATE	DWN	APVD
		F		REV PER ECR 09-002518		04FEB09	JR	TM

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED	12-10 AWG SOLID OR STRANDED

- 1

STAMP AMP 12-10* APPROX AS SHOWN
- 2

PRELIMINARY - NOT FOR PRODUCTION
- 3


0.00254 [.000100] MIN TIN PLATE PER ASTM B-545
- 4

CLEANED, UNPLATED
- 5

0.00254 [.000100] MIN TIN-LEAD (93-7) PLATE PER ASTM B-545 (3% MIN LEAD CONTENT)
- 6

COPPER PER ASTM B-152, ANNEALED

5	500	LOOSE PIECE	322454-3
4	-	LOOSE PIECE	2 322454-2
3	50	LOOSE PIECE, BOX	8-322454-2
3	2500	ON TAPE, REEL	322454-1
3	----	LOOSE PIECE	322454
FINISH	QTY	PACKAGE TYPE	PART NO.



MAX. RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
			CHK DA PATTERSON 3-17-93						
VOLTAGE RATING: N/A	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD JL MECKLEY 3-17-93	NAME TERMINAL, RING TONGUE, SOLISTRAND -					
			PRODUCT SPEC -						
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED		SEE TABLE	APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
			WEIGHT -	A2	00779	C=322454	-		
				CUSTOMER DRAWING			SCALE	10:1	SHEET