


## MOUNTING CHANNELS




Mounting Channels provide mounting framework for installing DIN rails and grid straps at various positions within the enclosure. Channels can be mounted vertically or horizontally to collar studs or to the slide mechanisms of the adjustable-depth mounting kit. Kit includes two channels.

## BULLETIN: CWY

| Catalog Number | Fits CONCEPT Enclosure            |
|----------------|-----------------------------------|
| CMC12          | when A or B = 12.00 in. (305 mm)  |
| CMC16          | when A or B = 16.00 in. (406 mm)  |
| CMC20          | when A or B = 20.00 in. (508 mm)  |
| CMC24          | when A or B = 24.00 in. (610 mm)  |
| CMC60          | when A or B = 60.00 in. (1524 mm) |

## RACK-MOUNT ANGLES



Rack-Mount Angles are a mounting means for 19-in. rack equipment in 24-in. wide enclosures. L-shaped through-hole angles attach to enclosure flange or the adjustable-depth mounting kit. Holes are .281 in. (7 mm) in diameter. Clear plated 14 gauge steel construction. Mounting hardware included.

Order separately clip nut package catalog number XNM5 and screws XSM5 (metric) or AN1032 and screws AS1032 (English).

## BULLETIN: CWY

| Catalog Number | Fits CONCEPT Enclosure      | Rack Units |
|----------------|-----------------------------|------------|
| CRA12TH        | when A = 24.00 in. (610 mm) | 12         |
| CRA16TH        | when A = 30.00 in. (762 mm) | 16         |

## DIN3 RAIL KITS



DIN3 Rail Kits supply mounting surfaces for DIN mount snap-on devices in either DIN 1, DIN 3 or CENELEC styles. Rails attach vertically or horizontally to rear collar stud or to mounting channels. Kit includes three rails and mounting hardware.

## BULLETIN: CWY


| Catalog Number | Fits CONCEPT Enclosure           |
|----------------|----------------------------------|
| CDR3P12        | when A or B = 12.00 in. (305 mm) |
| CDR3P16        | when A or B = 16.00 in. (406 mm) |
| CDR3P20        | when A or B = 20.00 in. (508 mm) |
| CDR3P24        | when A or B = 24.00 in. (610 mm) |

## CONCEPT™ PANELS

These panels are taller and wider than corresponding NEMA-size panels. Panels are 14 or 12 gauge steel and painted white or have a conductive finish.

Panels have a formed flange along any side that is longer than 22.20 in. (564 mm). CP2420 and CP2424 have a flange on all four sides.

## BULLETIN: CWP, CWY, DWDH2



| Catalog Number | Panel Type    | Panel Size D x E (in.) | Panel Size D x E (mm) | Gauge |
|----------------|---------------|------------------------|-----------------------|-------|
| CP1212         | Painted steel | 10.20 x 10.20          | 259 x 259             | 14    |
| CP1212G        | Conductive    | 10.20 x 10.20          | 259 x 259             | 14    |
| CP1612         | Painted steel | 14.20 x 10.20          | 361 x 259             | 14    |
| CP1612G        | Conductive    | 14.20 x 10.20          | 361 x 259             | 14    |
| CP1616         | Painted steel | 14.20 x 14.20          | 361 x 361             | 12    |
| CP1616G        | Conductive    | 14.20 x 14.20          | 361 x 361             | 12    |
| CP2016         | Painted steel | 18.20 x 14.20          | 462 x 361             | 12    |
| CP2016G        | Conductive    | 18.20 x 14.20          | 462 x 361             | 12    |
| CP2014         | Painted steel | 18.20 x 12.20          | 462 x 310             | 14    |
| CP2014G        | Conductive    | 18.20 x 14.20          | 462 x 310             | 14    |
| CP2416         | Painted steel | 22.20 x 14.20          | 564 x 361             | 12    |
| CP2416G        | Conductive    | 22.20 x 14.20          | 564 x 361             | 12    |
| CP2020         | Painted steel | 18.20 x 18.20          | 462 x 462             | 12    |
| CP2020G        | Conductive    | 18.20 x 18.20          | 462 x 462             | 12    |
| CP2420         | Painted steel | 22.20 x 18.20          | 564 x 462             | 12    |
| CP2420G        | Conductive    | 22.20 x 18.20          | 564 x 462             | 12    |
| CP3020         | Painted steel | 28.20 x 18.20          | 716 x 462             | 12    |

| Catalog Number | Panel Type    | Panel Size D x E (in.) | Panel Size D x E (mm) | Gauge |
|----------------|---------------|------------------------|-----------------------|-------|
| CP3020G        | Conductive    | 28.20 x 18.20          | 716 x 462             | 12    |
| CP3220         | Painted steel | 30.20 x 18.20          | 762 x 462             | 12    |
| CP4420         | Painted steel | 42.20 x 18.20          | 1072 x 462            | 12    |
| CP5620         | Painted steel | 53.20 x 18.20          | 1351 x 462            | 12    |
| CP2424         | Painted steel | 22.20 x 22.20          | 564 x 564             | 12    |
| CP2424G        | Conductive    | 22.20 x 22.20          | 564 x 564             | 12    |
| CP3024         | Painted steel | 28.20 x 22.20          | 716 x 564             | 12    |
| CP3024G        | Conductive    | 28.20 x 22.20          | 716 x 564             | 12    |
| CP3624         | Painted steel | 34.20 x 22.20          | 869 x 564             | 12    |
| CP3624G        | Conductive    | 34.20 x 22.20          | 869 x 564             | 12    |
| CP4824         | Painted steel | 46.20 x 22.20          | 1173 x 564            | 12    |
| CP4824G        | Conductive    | 46.20 x 22.20          | 1173 x 564            | 12    |
| CP3030         | Painted steel | 28.20 x 28.20          | 716 x 716             | 12    |
| CP3030G        | Conductive    | 28.20 x 28.20          | 716 x 716             | 12    |
| CP3630         | Painted steel | 34.20 x 28.20          | 869 x 716             | 12    |
| CP3630G        | Conductive    | 34.20 x 28.20          | 869 x 716             | 12    |
| CP4230         | Painted steel | 40.20 x 28.20          | 1021 x 716            | 12    |
| CP4230G        | Conductive    | 40.20 x 28.20          | 1021 x 716            | 12    |
| CP3636         | Painted steel | 34.20 x 34.20          | 869 x 869             | 12    |
| CP3636G        | Conductive    | 34.20 x 34.20          | 869 x 869             | 12    |
| CP4236         | Painted steel | 40.20 x 34.20          | 1021 x 869            | 12    |
| CP4236G        | Conductive    | 40.20 x 34.20          | 1021 x 869            | 12    |
| CP4836         | Painted steel | 46.20 x 34.20          | 1173 x 869            | 12    |
| CP4836G        | Conductive    | 46.20 x 34.20          | 1173 x 869            | 12    |
| CP6036         | Painted steel | 58.20 x 34.20          | 1478 x 869            | 12    |
| CP6036G        | Conductive    | 58.20 x 34.20          | 1478 x 869            | 12    |
| CP2442         | Painted steel | 22.20 x 40.20          | 564 x 1021            | 12    |
| CP2442G        | Conductive    | 22.20 x 40.20          | 564 x 1021            | 12    |
| CP3048         | Painted steel | 28.20 x 46.20          | 716 x 1173            | 12    |
| CP3048G        | Conductive    | 28.20 x 46.20          | 716 x 1173            | 12    |
| CP3060         | Painted steel | 28.20 x 58.20          | 716 x 1478            | 12    |
| CP3060G        | Conductive    | 28.20 x 58.20          | 716 x 1478            | 12    |
| CP7236         | Painted steel | 70.20 x 34.20          | 1783 x 869            | 12    |

Catalog number CP4230 is used on CONCEPT disconnect enclosures.