

Datasheet

Item No. 96.232.5033.1

Cable assembly RST20I3K1B- 15 50SW

Connection cable, female - free end, length 5m, RST20i3, 3 pole, 250V/20A, cable type H07RN-F, cross section 1,5 mm², color of coding: black



Item No.	96.232.5033.1
EAN	4015573761780
order unit	10 Piece(s)

Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP66/IP68
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H07RN-F
Cable colour	Black
Cable diameter	9.8 mm
Version of cable	Female - free end

Material

Surface finish	Silver-plated
Halogen free	No
Continuous temperature of cable	60 °C

Insulation components continuous temperature	100 °C
Dimensions	
Total length	5 m

Drawings

☐ Drawings made by: Drawing department special
☐ Approved by: Drawing
☐ Date of production: 2007-02-22 for drawing design 96.232

.F	Farbe colour	Codierung U	Buchse female
.0	lichtgrau light grey	N	PE
.1	schwarz black		

PE
grün/gelb
green/yellow

L
braun
brown

PE
grün/gelb
green/yellow

L
braun
brown

Farbe/color		.F
schwarz/black		.1
lichtgrau/light grey		.0

Weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-no.	L	Beispiel (Farbe: schwarz, lichtgrau) example (colour: black, grey)	Typ type
96.232.XX33.1	XX in dm-Schritten	96.232.1033.1 = 10dm/L= 1000mm	RST2013K1B- 15 10SW
96.232.XX33.0		96.232.1033.0	RST2013K1B- 15 10GL
U6.232.XX33.1	XX in m-Schritten	U6.232.1233.1 = 12 m/L=12000mm	RST2013K1B- 15 X12SW
U6.232.XX33.0		U6.232.1233.0	RST2013K1B- 15 X12GL

Fertigung nach DIN 7167/Environnement system etc. to DIN 7167. (This DIN standard describes the envelope principle. According to the envelope principle the deviations of form and position are limited by the size tolerances).
 Typen: GD: Stoffbahn- und Gussrohrsysteme nach DIN EN 60511 (List of prohibited / disallowed characters, subsequent to be declared)

Früher/Nach General tolerance		GD - Zeichnung, keine modifizierenden Änderungen GD - drawing, no modifying modifications allowed	1. Verwendung: First Use:	Druck: 1 mm Sheet: 11
Werkstoff/Material: 2007 12.01. Schritt 1. 12.01. Schritt 1. 12.01. Schritt 1.		2007 12.01. Schritt 1. 12.01. Schritt 1.		Zeichnung Nr.: Drawing No. T 96.232.0433.0 01K

Made in mm/Dimensions are in mm

		KONFEKT_LEITUNG Buchse-freies Ende Crimpausführung/female-free end pre-assembled cable crimp design K1 250V	
Index: 22.02.2007/ 2007 / sheet 1		Änderung/Revision: 1	

2204033000_4 CAD0019 from: 2017-02-22 10:50 1000