


REV	ECN	APP'D
-	5137	

ELFK SERIES PART NUMBERING SCHEME



COLOR/PLATING
 0=BLACK, TIN-LEAD (STANDARD)
 1=BLACK, SELECTIVE GOLD
 G=GREEN, TIN-LEAD
 IG=GREEN, SELECTIVE GOLD

MOUNTING EARS
 0E=BLACK, TIN-LEAD
 1E=BLACK, SELECTIVE GOLD
 GE=GREEN, TIN-LEAD
 EG=GREEN, SELECTIVE GOLD

CONSULT PCD FOR PART NO. AND
 AVAILABILITY OF FOLLOWING OPTIONS:
 *CUSTOM COLORS
 *CUSTOM MARKING
 *CUSTOM KEYING
 *SELECTIVE CONTACT LOADING

INSTALLATION RECOMMENDATIONS:
 WIRE RANGE: AWG #12-26, STRANDED OR SOLID
 WIRE STRIP LENGTH: .310"
 TIGHTENING TORQUE: 7 LB-IN.





MATERIALS:
 HOUSING: PPO, UL 94 V-0
 CONTACT: COPPER ALLOY, OPTIONAL FINISH
 SCREW: STEEL, NICKEL FINISH
 WIRE CLAMP: COPPER ALLOY, NICKEL FINISH

MAX OPERATING TEMPERATURE:
 105°C



 RATINGS CURRENT - 15A VOLTAGE - 300V U.L. FILE NO. PENDING
 RATINGS CURRENT - 15 A VOLTAGE - 450 V CSA FILE NO. PENDING
DIN VDE 0627:1986 DIN VDE 0110-1:1989 EN 60947-1:1991 EN 60947-7-1:1992 CURRENT - 15 A VOLTAGE - 450 V TUV FILE NO. PENDING

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°	PROJECTION 	SPECIFICATION DRAWING ENGR I. QUINN 12/27/02			TITLE ELFK SERIES 45 DEGREE PLUG .300 PITCH		
ORIGINAL STAMPED IN RED	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA	CHKD	SIZE A	DWG NO. ELFK02410		REV -		
		APPD	CODE: 58982		SCALE: NONE	SHEET 1 OF 2		

$$L = (\text{NUM OF POS} \times .300) - .1$$



MOUNTING EAR
CONFIGURATION



SIZE	DWG NO.	REV
A	ELFK02410	-
CODE: 58982	SCALE: NONE	SHEET 2 OF 2