

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0523961090](#)
Status: **Obsolete**
Description: 0.625mm (.0246") SMT, Right Angle, ZIF, Bottom Contact Style Receptacle, 10 Circuits

Documents:

General

Product Family FFC/FPC Connectors
Series [52396](#)
Product Name N/A

Physical

Circuits (Loaded) 10
Contact Position Bottom
Entry Angle 90° Angle
Mated Height 2.70mm (.106")
Material - Metal Phosphor Bronze
Material - Plating Mating Tin-Lead
Material - Plating Termination Tin-Lead
Number of Rows 1
Orientation Right Angle
PCB Locator No
PCB Retention None
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.62mm (.024")
Plating min - Mating 2.032µm (80µ")
Plating min - Termination 2.032µm (80µ")
Polarized to PCB No
Stackable No
Temperature Range - Operating -20°C to +85°C
Termination Interface: Style Surface Mount
Wire/Cable Type FPC only

Electrical

Current - Maximum per Contact 0.2A
Voltage - Maximum 50V

Material Info

Reference - Drawing Numbers

Product Specification PS-52396-001, PS-52396-002, RPS-52396-001
Sales Drawing SD-52396-**17, SD-52396-**90

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[52396Series](#)