






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-		A	ECR-11-018633	13SEP2011	PW	AL
			AI	ECR-11-020935	13OCT2011	JvH	AL



SECTION Z - Z



NOTES:

- PN AS SHOWN: 2173227-2.
- SHARP EDGES ON PLASTIC WILL BE BROKEN.
- PACKAGING: BULK PACKAGING. 2500PCS/BAG.
- FOR PERFORMANCE REQUIREMENTS SEE PRODUCT SPECIFICATION 108-19426.
- GATE POSTITION. MAX 0.10mm CUT OFF BURR.
- 6 = Cpk DIMENSION.

Contact Force vs Deflection		
	Working Height [mm]	Force [N]
MAX.	2,50	2,0 MAX.
MIN.	3,20	0,5 MIN.

3	I	POGO PIN PLUNGER	C36000 or equal	0,3µm MIN. Au over 1,0µm MIN. Ni
2	I	POGO PIN BODY	C36000 or equal	0,3µm MIN. Au over 1,0µm MIN. Ni
1	I	HOUSING	PC	GREY
ITEM No.	Qty.	DESCRIPTION	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22JUL2011 J. van Hoek	 TE Connectivity	
DIMENSIONS: mm		CHK 22JUL2011 P. Willems		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 22JUL2011 A. Ligthart	NAME DUAL FLOATING POGO PIN ASSEMBLY 3,40mm HEIGHT	
0 PLC ±- 1 PLC ±0,10 2 PLC ±0,05 3 PLC ±0,05 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-19426	SIZE A3	
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779	
FINISH -		WEIGHT -	DRAWING NO C-2173227	
CUSTOMER DRAWING		SCALE 15:1		RESTRICTED TO -
		SHEET 1 OF 1		REV AI