



- ① CABLE USED WITHOUT SPACER
- ② CABLE USED WITH SPACER
- ③ SEE INSTRUCTION SHEET 408-2798
- ④ PARTS PACKAGED UNASSEMBLED
- ⑤ USE WITH HAND TOOL FRAME 354940-1
- ⑥ USE WITH HANDTOOL 69710-1, OR PNEUMATIC TOOL 69365 & 69365-3
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED STRIP LENGTH

	OBSOLETE	H.P. RED TRIAXIAL	-	58330-1	69477-4	C	1.090	1-938013-3	-	-	9-329461-0	9-227322-0	413530-6	4-227079-0
	OBSOLETE	RG-180/U,180A/U,180B/U & 195/U	-	58330-1	69477-4	A	1.090	-	-	-	9-329461-0	9-221607-4	413530-5	3-227079-7
SUPERSEDED BY 8-227079-2		RG-188/U DOUBLE BRAIDED	-	58330-1	69477-4	A	1.090	-	227194-1	-	9-329049-0	9-227322-0	413530-6	3-227079-3
	OBSOLETE	BELDEN 9248	-	220244-1	220247-1	A	1.090	-	-	-	9-50427-0	1-221607-7	413530-3	3-227079-2
	OBSOLETE	BELDEN 9248	-	220244-1	220247-1	A	1.090	-	-	-	9-50427-0	1-221607-8	413530-3	3-227079-1
	OBSOLETE	BELDEN 9248 & 9114	-	220244-1	220247-1	A	1.090	-	-	-	9-50427-0	1-221607-6	413530-3	3-227079-0
		RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	-	227194-1	-	9-328666-0	227322-4	227074-2	2-227079-2
SUPERSEDED BY 2-227079-2		RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	-	227194-1	-	9-328666-0	227322-3	413530-6	2-227079-1
SUPERSEDED BY 2-5227079-0		RG-179/U & 187/U	220217-3	220210-1	220009-5	A	1.090	-	227194-1	-	9-328666-0	9-227322-1	413530-6	2-227079-0
		BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	-	58330-1	69477-4	A	1.090	-	-	-	9-329461-0	2-221607-2	413530-5	1-227079-9
SUPERSEDED BY 1-227079-9		BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	-	58330-1	69477-4	A	1.090	-	-	-	9-329461-0	2-221607-1	413530-5	1-227079-8
	OBSOLETE	BELDEN 8218,AMPHENOL 21-597 & BELDEN NH SPECIAL	-	58330-1	69477-4	A	1.090	-	-	-	9-329461-0	9-221607-3	413530-5	1-227079-7
		RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	-	227194-1	-	9-328666-0	227322-8	227074-2	1-227079-6
SUPERSEDED BY 1-227079-6		RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	-	227194-1	-	9-328666-0	227322-7	413530-6	1-227079-5
	OBSOLETE	RG-174/U & 188/U	220217-3	220210-1	220009-5	A	1.090	-	227194-1	-	9-328666-0	9-227322-0	413530-6	1-227079-4
	OBSOLETE	BELDEN 9266	-	220189-5	-	A	1.090	-	-	-	9-50428-0	221607-5	413530-2	1-227079-3
	OBSOLETE	RG-71/U & 71A/U	220217-2	220189-2	220187-2	B	1.090	-	-	227423-1	1-329460-1	221607-8	413530-2	1-227079-2
		RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	-	-	227423-1	9-50428-0	221607-8	413530-2	1-227079-1
		RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	-	-	227423-1	9-50428-0	221607-8	413530-2	1-227079-1
SUPERSEDED BY 227079-6		RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	-	-	-	9-225382-0	221607-7	227074-1	1-227079-0
		RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	221607-7	227074-1	227079-9
		RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	-	-	-	9-50427-1	221607-7	227074-1	227079-9
		RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	-	-	227423-1	9-50428-0	221607-6	227080-1	227079-7
		RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	-	-	-	9-225382-0	221607-5	227074-1	227079-6
		RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	221607-5	227074-1	227079-5
	OBSOLETE	RG-71/U & 71A/U	220217-2	220189-2	220187-2	B	1.090	-	-	227423-1	1-329460-1	9-221607-1	413530-2	227079-4
	OBSOLETE	RG-59/U,59A/U & 59B/U	220217-2	220189-2	220187-2	A	1.090	-	-	227423-1	9-50428-0	9-221607-1	413530-2	227079-3
	OBSOLETE	RG-62/U,62A/U & 62B/U	220217-2	220189-2	220187-2	B	1.090	-	-	227423-1	9-50428-0	9-221607-1	413530-2	227079-3
SUPERSEDED BY 227079-6		RG-55/U,55A/U,55B/U, & 223/U	220217-1	220189-1	220187-1	A	1.280	-	-	-	9-225382-0	9-221607-0	227074-1	227079-2
	OBSOLETE	RG-58/U,58A/U,58B/U,58C/U & 141/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	9-221607-0	227074-1	227079-1

CABLE SIZE	DIE SET ①	DIE SET ②	CRIMP TOOL	VIEW	A	⑥ TUBING, HEAT SHRINK QTY=1	⑤ TUBING QTY=1	④ SPACER QTY=1	③ FERRULE QTY=1	② CONTACT, PLUG QTY=1	① PLUG ASSY, COML BNC QTY=1	PART NUMBER
------------	-----------	-----------	------------	------	---	-----------------------------	----------------	----------------	-----------------	-----------------------	-----------------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN D. LAMAN 10-9-89	TE Connectivity
0 PLC ± -	1 PLC ± -	10/27/89	
2 PLC ± -	3 PLC ± .016	R. E. RUTH	
4 PLC ± -	ANGLES ± -	J. GIBBS 11/06/89	
MATERIAL	FINISH	NAME	PLUG, COMMERCIAL, BNC
		PRODUCT SPEC	108-12044
		APPLICATION SPEC	
		SIZE	A1
		WEIGHT	00779
		DRAWING NO	227079
		SCALE	4:1
		SHEET	1 OF 2
		REV	AV3

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
AJ	16	REV	DATE	BY	APPROV
		1	SEE SHEET 1		

DESCRIPTION	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	1-221607-6	227074-1	9-227079-4
OBSOLETE BELDON 9907				A	1.090	-	-	-	9-50427-1	1-221607-6	227074-1	9-227079-4
OBSOLETE HI-TEMP RG62A/U, TIMES PL62, BERK-TEK BTDC 62 & BELDEN 89269 BELDEN 88241, BERK-TEK BTDC 59	220217-2	220189-2	220187-2	B B	1.312	-	-	227423-1	9-228784-0	221607-6	413530-2	9-227079-3
OBSOLETE BELDEN 8218, AMPHENOL 21-597 AND BELDEN NH SPECIAL	-	58330-1	69477-4	A	1.090	-	-	-	9-329461-0	2-221607-2	413530-5	9-227079-2
OBSOLETE BELDEN YR40862	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	2-221607-8	227074-1	9-227079-1
OBSOLETE C&M 17189	220217-3	220210-1	220009-5	A	1.090	-	414932-2	-	9-328666-0	227322-8	227074-2	9-227079-0
OBSOLETE BELDEN 9907 AND RG-141A/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	1-221607-6	227074-1	8-227079-9
OBSOLETE CUSTOM CABLE: C/C=Ø.014, DIELECTRIC=Ø.062, JACKET=Ø.103	-	220210-1	-	A	1.090	-	227194-1	-	9-328666-0	1-227322-4	413530-6	8-227079-8
OBSOLETE BELDEN 9266	-	220189-5	-	A	1.090	-	-	-	9-50428-0	221607-5	413530-2	8-227079-7
OBSOLETE BELDEN 89907	-	318452-2	-	A	1.312	-	-	-	9-228783-0	1-221607-6	227074-1	8-227079-6
OBSOLETE RG-59/U, 59A/U, 59B/U RG-62/U, 62A/U, 62B/U	220217-2	220189-2	220187-2	A B	1.090	-	-	227423-1	9-50428-0	9-221607-1	413530-2	8-227079-5
OBSOLETE RG-58/U, 58A/U, 58B/U, 58C/U AND 141/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	221607-5	227074-1	8-227079-4
OBSOLETE BELDEN 9555	-	220189-2	220187-2	A	1.090	-	-	-	9-50428-0	221607-6	413530-2	8-227079-3
OBSOLETE RG-188 DOUBLE BRAID AND RG-316 DOUBLE BRAID RG-59/U, 59A/U AND 59B/U	-	58330-1	69477-4	A	-	-	227194-1	-	9-329049-0	227322-8	413530-6	8-227079-2
OBSOLETE RG-62/U, 62A/U AND 62B/U	220217-2	220189-2	220187-2	A B	1.090	-	-	227423-1	9-50428-0	221607-6	413530-2	8-227079-1
OBSOLETE RG-58/U, 58A/U, 58B/U, 58C/U, AND 141/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	221607-5	227074-1	8-227079-0
OBSOLETE GORE CXN1426A	-	58330-2	-	A	1.090	-	-	-	9-329049-0	1-221607-6	413530-5	7-227079-9
OBSOLETE SPECIAL CUSTOMER CABLE-110 OHM LOW NOISE	-	58086-1	-	A	1.090	-	-	-	9-50427-0	2-221607-6	413530-3	7-227079-7
OBSOLETE BELDEN 88241, TIMES PL62, BERK-TEK BTDC 59 AND BTDC 62 BELDEN 88240 AND BERK-TEK BTDC-58	220217-2 220217-1	220189-2 220189-1	220187-2 220187-1	A A	1.312 1.312	-	-	227423-1	9-228784-0 9-228783-0	221607-8 221607-5	413530-2 227074-1	7-227079-6 7-227079-5
OBSOLETE RG-62/U, 62A/U AND 62B/U RG-59/U, 59A/U AND 59B/U	220217-2 220217-1	220189-2 220189-1	220187-2 220187-1	B A	1.090 1.090	-	-	227423-1	9-50428-0 9-50427-1	9-221607-1 9-221607-0	413530-2 227074-1	7-227079-4 7-227079-3
OBSOLETE RG-58/U, 58A/U, 58B/U, 58C/U AND 141/U	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	221607-8	413530-2	7-227079-2
OBSOLETE RG-62/U, 62A/U AND 62B/U RG-59/U, 59A/U AND 59B/U	220217-2 220217-1	220189-2 220189-1	220187-2 220187-1	B A	1.090 1.090	-	-	227423-1	9-50428-0 9-50427-1	221607-8 221607-7	413530-2 227074-1	7-227079-1 7-227079-0
OBSOLETE BELDEN 9275	-	220189-5	-	A	1.090	-	-	-	9-50428-1	9-221607-0	413530-2	7-227079-0
OBSOLETE C & M COAXIAL Q-81-13059	-	58330-1	69477-4	A	1.090	-	227194-1	-	9-329461-0	227322-8	413530-6	6-227079-9
SUPERSEDED BY 6-5227079-8	-	318452-2	-	A	1.312	-	-	-	9-228783-0	1-221607-6	227074-1	6-227079-8
SUPERSEDED BY 6-5227079-5	220217-1	220189-1	220187-1	A	1.090	-	-	-	9-50427-1	1-221607-6	227074-1	6-227079-7
OBSOLETE BELDEN 9907	-	-	220043-1	A	1.490	-	-	-	9-51713-3	1-221607-6	413530-3	6-227079-5
OBSOLETE RG-180/U, 180A/U, 180B/U AND 195/U RG-142/U, 142A/U, AND 142B/U	220217-1 220217-1	220189-1 220189-1	220187-1 220187-1	A A	1.090 1.280	-	-	-	9-50427-1 9-225382-0	1-221607-6 1-221607-7	227074-1 227074-1	6-227079-4 6-227079-2
SUPERSEDED BY 6-5227079-1	220217-1	220189-1	220187-1	A	1.280	-	-	-	9-225382-0	1-221607-6	227074-1	6-227079-1
OBSOLETE RG-142/U, 142A/U, AND 142B/U	220217-1	220189-1	220187-1	A	1.280	-	-	-	9-225382-0	1-221607-8	227074-1	6-227079-0
OBSOLETE RG-174/U (SPECIAL APPLICATION)	-	-	-	A	1.090	-	227194-1	-	9-50427-1	227322-8	413530-6	5-227079-9
OBSOLETE BELDEN 8281	-	-	220043-1	A	1.250	-	-	-	9-50427-2	221607-5	413530-3	5-227079-8
SUPERSEDED BY 1-227079-1	220217-2	220189-2	220187-2	A	1.090	-	-	-	9-50428-0	221607-8	413530-2	5-227079-7
OBSOLETE C & M COAXIAL 6P267B33TC20PC055520 RC-174/U AND 188/U TYPE (SPECIAL)	- -	- 58330-1	- 69477-4	- -	- -	-	227194-1	-	- 227322-8	- 221607-7	413530-6 413530-3	5-227079-5 5-227079-4
OBSOLETE BELDEN 8281	220088-1	220189-6	220043-1	A	1.250	-	-	-	9-50427-2	221607-7	413530-3	5-227079-4
SUPERSEDED HI TEMP RG-59/U, TIMES PL59 AND PLF59	-	220189-5	-	A	1.312	-	-	-	9-228784-0	221607-5	413530-2	5-227079-3
OBSOLETE HI TEMP RG-59/U, TIMES PL59 AND PLF59	-	220189-5	-	A	1.312	-	-	-	9-228784-0	221607-7	413530-2	5-227079-2
OBSOLETE HI TEMP RG-59/U, TIMES PL59 AND PLF59	-	220189-5	-	A	1.312	-	-	-	9-228784-0	9-221607-0	413530-2	5-227079-1
OBSOLETE TIMES MI-2040 DBL BRAIDED RG-59/U	-	-	59894-1	A	1.187	-	-	-	9-50427-0	1-221607-4	413530-2	5-227079-0
OBSOLETE HI-TEMP RG62A/U, TIMES PL62, BERK-TEK BTDC 62 & BELDEN 89269 BELDEN 88241, BERK-TEK BTDC 59	220217-2	220189-2	220187-2	B B	1.312	-	-	227423-1	9-228784-0	221607-6	413530-2	4-227079-9
OBSOLETE HI TEMP RG-62A/U, TIMES PL62, BERK-TEK BTDC 62 BELDEN 88241, BERK-TEK BTDC 59	220217-2	220189-2	220187-2	A B	1.312	-	-	227423-1	9-228784-0	221607-8	413530-2	4-227079-8
OBSOLETE HI TEMP RG-62A/U, TIMES PL62, BERK-TEK BTDC 62 BELDEN 88241, BERK-TEK BTDC 59	220217-2	220189-2	220187-2	B A	1.312	-	-	227423-1	9-228784-0	9-221607-1	413530-2	4-227079-7
OBSOLETE BELDEN 88240 AND BERK-TEK BTDC-58	220217-1	318452-2	-	A	1.312	-	-	-	9-228783-0	221607-5	227074-1	4-227079-3
OBSOLETE BELDEN 88240 AND BERK-TEK BTDC-58	220217-1	220189-1	220187-1	A	1.312	-	-	-	9-228783-0	221607-7	227074-1	4-227079-2
SUPERSEDED BY 4-227079-3	220217-1	220189-1	220187-1	A	1.312	-	-	-	9-228783-0	9-221607-0	227074-1	4-227079-1

CABLE SIZE	DIE SET	DIE SET	CRIMP TOOL	VIEW	A	TUBING HEAT SHRINK QTY=1	TUBING QTY=1	SPACER QTY=1	FERRULE QTY=1	CONTACT, PLUG QTY=1	PLUG ASSY, COML BNC QTY=1	PART NUMBER
------------	---------	---------	------------	------	---	--------------------------	--------------	--------------	---------------	---------------------	---------------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES	± -

DIN D. LAMAN 10-9-89	REV 10/27/89
CHK R. E. RUTH	APPROV J. GIBBS 11/06/89
NAME	PRODUCT SPEC
APPLICATION SPEC	RESTRICTED TO

TE Connectivity

PLUG, COMMERCIAL, BNC

SIZE: A1 CASE CODE: 00779 DRAWING NO: 227079 WEIGHT: -

CUSTOMER DRAWING SCALE: 4:1 SHEET 2 OF 2 REV: AV3