


## C101 ROUND BAR

Hard Drawn High Conductivity  
4-4.2 metre lengths




| Dia<br>(in) | Weight<br>per metre (Kg) |
|-------------|--------------------------|
| ¼           | 0.28                     |
| ⅜           | 0.44                     |
| ½           | 0.63                     |
| 10mm        | 0.70                     |
| 12mm        | 1.01                     |
| ½           | 1.13                     |
| ¾           | 1.76                     |
| 16mm        | 1.79                     |
| 20mm        | 2.80                     |
| ¾           | 2.54                     |
| 1           | 3.45                     |
| 25mm        | 4.39                     |
| 1           | 4.51                     |
| 1½          | 5.71                     |
| 30mm        | 6.32                     |
| 1½          | 7.05                     |

| Dia<br>(in) | Weight<br>per metre (Kg) |
|-------------|--------------------------|
| 1¾          | 8.53                     |
| 1½          | 10.0                     |
| 40mm        | 11.2                     |
| 1¾          | 11.9                     |
| 1¾          | 13.8                     |
| 45mm        | 14.1                     |
| 50mm        | 17.4                     |
| 2           | 18.0                     |
| 2¼          | 22.8                     |
| 2½          | 28.2                     |
| 2¾          | 34.1                     |
| 3           | 40.6                     |
| 3¼          | 45.3                     |
| 3½          | 55.2                     |
| 4           | 72.2                     |

## C101 SHEET

Half Hard




| Size               | Weight<br>per sheet (Kg) |
|--------------------|--------------------------|
| 2m x 1m x 0.9mm    | 16.0                     |
| 4ft x 2ft x 20 swg | 5.94                     |
| 2m x 1m x 1.2mm    | 21.4                     |
| 4ft x 2ft x 18 swg | 7.94                     |
| 2m x 1m x 1.5mm    | 26.7                     |
| 1200 x 600 x 1.6mm | 10.2                     |

| Size               | Weight<br>per sheet (Kg) |
|--------------------|--------------------------|
| 2m x 1m x 2mm      | 35.6                     |
| 1200 x 600 x 2mm   | 12.8                     |
| 2m x 1m x 3mm      | 53.4                     |
| 4ft x 2ft x 10 swg | 21.5                     |
| 2m x 1m x 6mm      | 106                      |

## C101 PLATE

'M' (As Manufactured)



| Size             | Weight<br>per plate (Kg) |
|------------------|--------------------------|
| 3m x 1m x 6mm    | 128                      |
| 3m x 1m x 10mm   | 213                      |
| 3m x 1m x 12.7mm | 339                      |
| 3m x 1m x 16mm   | 427                      |
| 2m x 1m x 20mm   | 355                      |

| Size             | Weight<br>per plate (Kg) |
|------------------|--------------------------|
| 2m x 1m x 25.4mm | 452                      |
| 2m x 1m x 40mm   | 711                      |
| 2m x 1m x 51mm   | 907                      |
| 2m x 1m x 65mm   | 1157                     |
| 1m x 1m x 102mm  | 907                      |

Can be cut to size on plate saws.

## C106 SHEET

Half Hard




| Size                 | Weight<br>per sheet (Kg) |
|----------------------|--------------------------|
| 2m x 1m x 0.55mm     | 9.79                     |
| 4ft x 2ft x 24 swg   | 3.64                     |
| 2m x 1m x 0.7mm      | 12.5                     |
| 4ft x 2ft x 22 swg   | 4.63                     |
| 2m x 1m x 0.9mm      | 16.0                     |
| 4ft x 2ft x 20 swg   | 5.95                     |
| 2.5m x 1.25m x 1.2mm | 33.3                     |
| 2m x 1m x 1.2mm      | 21.4                     |
| 4ft x 2ft x 18 swg   | 7.94                     |
| 2.5m x 1.25m x 1.5mm | 41.7                     |
| 2m x 1m x 1.6mm      | 28.5                     |
| 4ft x 2ft x 16 swg   | 10.6                     |

| Size               | Weight<br>per sheet (Kg) |
|--------------------|--------------------------|
| 2.5m x 1.25m x 2mm | 55.6                     |
| 2m x 1m x 2mm      | 35.6                     |
| 4ft x 2ft x 14 swg | 13.2                     |
| 2m x 1m x 2.5mm    | 44.5                     |
| 4ft x 2ft x 12 swg | 17.5                     |
| 2.5m x 1.25m x 3mm | 83.4                     |
| 2m x 1m x 3mm      | 53.4                     |
| 4ft x 2ft x 10 swg | 21.5                     |
| 4ft x 2ft x ⅜      | 31.5                     |
| 2m x 1m x 5mm      | 89.0                     |
| 2m x 1m x 6mm      | 106                      |

## C106 TUBE

Half Hard

6 metre lengths




| Size<br>(in)   | Weight<br>per metre (Kg) |
|----------------|--------------------------|
| ¼ o/d x 20 swg | 0.14                     |
| ¼ o/d x 18 swg | 0.17                     |
| ⅜ o/d x 20 swg | 0.22                     |
| ⅜ o/d x 18 swg | 0.29                     |
| ½ o/d x 20 swg | 0.30                     |
| ½ o/d x 18 swg | 0.39                     |
| ½ o/d x 16 swg | 0.50                     |
| ⅝ o/d x 20 swg | 0.38                     |
| ⅝ o/d x 18 swg | 0.50                     |
| ¾ o/d x 20 swg | 0.46                     |
| ¾ o/d x 18 swg | 0.61                     |

| Size<br>(in)    | Weight<br>per metre (Kg) |
|-----------------|--------------------------|
| ¾ o/d x 16 swg  | 0.79                     |
| ⅞ o/d x 20 swg  | 0.54                     |
| ⅞ o/d x 16 swg  | 0.94                     |
| ⅞ o/d x 18 swg  | 0.72                     |
| 1 o/d x 20 swg  | 0.63                     |
| 1 o/d x 18 swg  | 0.83                     |
| 1 o/d x 16 swg  | 1.08                     |
| 1¼ o/d x 16 swg | 1.37                     |
| 1½ o/d x 16 swg | 1.66                     |
| 2 o/d x 16 swg  | 2.24                     |
| 2½ o/d x 16 swg | 2.81                     |

## C106 SHEET

Soft - Spinning Quality



| Size               | Weight<br>per sheet (Kg) |
|--------------------|--------------------------|
| 2m x 1m x 0.55mm   | 9.79                     |
| 4ft x 2ft x 24 swg | 3.64                     |
| 2m x 1m x 0.7mm    | 12.5                     |
| 4ft x 2ft x 22 swg | 4.63                     |
| 2m x 1m x 0.9mm    | 16.0                     |

| Size               | Weight<br>per sheet (Kg) |
|--------------------|--------------------------|
| 4ft x 2ft x 20 swg | 5.95                     |
| 2m x 1m x 1.2mm    | 21.4                     |
| 4ft x 2ft x 18 swg | 7.94                     |
| 2m x 1m x 1.6mm    | 28.5                     |
| 4ft x 2ft x 16 swg | 10.6                     |