



platt
Professional cases for business and industry

Platt Luggage, Inc.

“Quality That Lasts!” Since 1921

Platt Luggage, Inc. * 4051 W. 51st Street * Chicago, IL 60632 * www.plattcases.com * 1.800.222.1555

Contents

FOAM-FILLED CASES

HEAVY-DUTY ATA CASES with recessed hardware and wheels 3
and telescoping handle

HEAVY-DUTY ATA CASES with recessed hardware 3

HEAVY-DUTY POLYETHYLENE CASES with wheels 3
and telescoping handle

HEAVY-DUTY POLYETHYLENE CASES 3

BLOW-MOLDED CASES 4

LIGHT-DUTY ABS CASES 4

MEDIUM-DUTY ABS CASES 4

PARALLEL RIB CASES 4

ATA SHIPPING CASES 5

WATERTIGHT CASES

PELICAN® CASES 6

PELICAN® FLASHLIGHTS 6

MOLDED TOOL CASES

SUPER-SIZE™ TOOL CASES with wheels and telescoping handle 7

SUPER-SIZE™ TOOL CASES 7

MILITARY TYPE SUPER-SIZE™ TOOL CASES 7

ROTATIONAL MOLDED TOOL CASE 7

TRANSPORTER TOOL CASE with wheels and telescoping handle 7

POLYETHYLENE TOOL CASES (ultimate) 8

POLYETHYLENE TOOL CASES (deluxe, premium, standard) 8

POLYPROPYLENE TOOL CASES (deluxe, economy) 9

ATA TOOL CASES

GUARDSMAN ATA TOOL CASES 9

GUARDSMAN ATA TOOL CASES with wheels and telescoping handle 9

ALUMINUM GUARDSMAN ATA TOOL CASES 9

TOOL PALLETS

INJECTION MOLDED TOOL PALLETS 10

SEWN AND RIVETED TOOL PALLETS 10

WINGED TOOL PALLET/BOOK TOOL PALLET 11

SEWN TOOL CASES

ZIPPER TOOL / TECHNICIAN CASES 11-12

TELECOM CASES 13

MECHANIC'S TOOL BAGS 14

TOOL ROLLS 14

CLC TOOL BAGS AND ORGANIZERS 14

BUFFALO CASE COMPANY

SEWN TOOL CASES 15

MOLDED TOOL CASE 15

COMPUTER & ATTACHÉ CASES

COMPUTER/AV CASES 16

ALUMINUM ATTACHÉ 16

DELUXE SOFT-MOLDED ATTACHÉ 16

HIGH-IMPACT POLYPROPYLENE ATTACHÉ 16

SPECIALTY/MISC

CATALOG CASES 17

FABRICATED SOFT-SIDED STATIC-FREE PCB CASES 17

AEROSOL CAN SAMPLE CASE 17

SLIDE CAROUSEL CASE 17

INFINITE DIVIDER BOXES 17

CARTS 18

CASE REPLACEMENT HARDWARE 18

Our Mission

Our mission is to lead our industry by providing quality products, superior customer service, technical innovation and on-time delivery. We realize that we cannot exist without the support of our customers, employees, and suppliers and we will treat them all with integrity and professionalism.

What To Know

Ordering with Platt is easy. Please specify Platt part number, color and quantity. For molded cases and sewn tool cases specify top and bottom pallet option. Use chart below as a reference or call our customer service department at 1-800-99-PLATT (997-5288) or visit our webpage at www.plattcases.com.

To Order Specify:

1. Platt#
2. Color
3. Top pallet (select from page 10-11)
4. Bottom pallet (select from page 10-11)

REFERENCE INFORMATION

Platt #	Platt part number
O.D.	Outside dimension
I.D.	Inside dimension
Color	Available color options
Body Depth	Interior depth of bottom half of case
Ship wt.	Shipping weight, including packaging
Option	Additional info to consider, ie. turnbutton on pallets.
Valance	Aluminum molding around edges of lid and base to ensure snug closure. Also referred to as a rim or frame.
Turnbutton	Knob fastener to hold top pallet in case lid.
ABS	ABS Thermoplastic. A tough high-performance material specified for years in many consumer and commercial applications because of its cost/performance balance, strength and durability.
HMW	(High Molecular Weight) Polyethylene. A superior performing, yet lightweight material providing the best in high-impact strength, durability, environmental stress-crack resistance, economy and superior chemical resistance.
Polypropylene	A tough high-performance material with superior chemical resistance.

Reference Material

BM99-1	Blow Molded Case Product Sheet
ENG03-1	Engineering Custom Case Catalog
MST05-1	Mini Product Catalog

Limited Warranty

All Platt cases are under warranty against manufacturing defects, under normal use, for a period of one year from the date of purchase. Any defect, which is a result of faulty workmanship or materials will be repaired and returned free of charge. When, in our judgement, damage is caused by misuse or the guarantee period has expired, we will repair, if practical, for a reasonable charge. If damage is caused by common carrier abuse or airline mishandling, claim must be made with that carrier. Determination of suitability of product for uses and applications contemplated by Buyer shall be at the sole responsibility of Buyer.

Disclosure

Platt continues product improvements. We reserve the right to deviate from product descriptions as shown in catalog.

**NEW
SIZES**

Heavy-Duty ATA Cases



221609AH



202014AH



261617AH

Heavy-Duty ATA Cases with Wheels and Telescoping Handle

Heavy-duty polyethylene ATA cases with recessed hardware. The exterior shell is tough impact-resistant HMW polyethylene. Foam-filled, heavy-duty aluminum rim and gasket, locking provision, full-length piano hinge and spring-loaded handle.

This durable, rugged transportation case series includes wheels and telescoping handle for convenient transportation.

*Gray in color

+This case also comes in laptop version (see page 16)

Platt#	Inside Dim.			Body Depth
	L	W	D	
201409AH	19 ⁵ / ₈ "	13 ³ / ₄ "	9"	5"
202014AH	20"	20"	14"	10"
221609AH	21 ¹ / ₂ "	15 ¹ / ₂ "	9"	5"
222214AH	22"	22"	14"	10"
231510AHG*	23"	15"	10"	5"
231511AH	23 ³ / ₈ "	15 ³ / ₈ "	11"	6"
241811AH	23 ³ / ₄ "	17 ³ / ₄ "	11"	5 ¹ / ₂ "
NEW 242416AH	24"	24"	16"	12"
NEW 242420AH	24"	24"	20"	15"
252310AHG*	25"	23"	10"	5"
252316AH	25 ¹ / ₄ "	23 ³ / ₈ "	16"	9"
261613AH	26"	16"	13"	10"
261617AH+	26"	16"	17"	12"
282011AH	27 ¹ / ₂ "	19 ¹ / ₂ "	11"	5 ¹ / ₂ "
NEW 301816AH	30"	18"	16"	12"
NEW 301820AH	30"	18"	20"	15"
322211AH	31 ³ / ₄ "	22"	11"	5 ¹ / ₂ "
NEW 460909AH	46"	9"	9"	4 ¹ / ₂ "
NEW 531111AH	53"	11"	11"	5 ¹ / ₂ "



201409A



261611A

Heavy-Duty ATA Cases with Recessed Hardware

Heavy-duty polyethylene ATA cases with recessed hardware. The exterior shell is tough impact-resistant HMW polyethylene. Foam-filled, heavy-duty aluminum rim and gasket, locking provision, full-length piano hinge and spring-loaded handle.

Platt#	Inside Dim.			Body Depth
	L	W	D	
181309A	18 ¹ / ₂ "	12 ¹ / ₂ "	9"	5"
201409A	19 ⁵ / ₈ "	13 ³ / ₄ "	9"	5"
202014A	20"	20"	14"	10"
202020A	20"	20"	20"	14"
221609A	21 ¹ / ₂ "	15 ¹ / ₂ "	9"	5"
222214A	22"	22"	14"	10"
222222A	22"	22"	22"	15 ¹ / ₂ "
241811A	23 ³ / ₄ "	17 ³ / ₄ "	11"	5 ¹ / ₂ "
261611A	26"	16"	11"	7 ¹ / ₂ "
282011A	27 ¹ / ₂ "	19 ¹ / ₂ "	11"	5 ¹ / ₂ "
322211A	31 ³ / ₄ "	22"	11"	5 ¹ / ₂ "

Heavy-Duty Polyethylene Cases



181509H




201407H

Heavy-Duty Polyethylene Cases with Wheels and Telescoping Handle

Tough impact-resistant HMW polyethylene. Foam-filled, heavy-duty aluminum valance with black trim and gasket, full-length piano hinge, cast chrome key locks and golf grip handle.

This series includes wheels and telescoping handle for convenient transportation.

Platt#	Inside Dim.			Body Depth
	L	W	D	
181509H	17 ¹ / ₂ "	14 ⁵ / ₈ "	9"	5"
201407H	19 ⁵ / ₈ "	13 ³ / ₄ "	7"	4"
221609H	21 ¹ / ₂ "	15 ¹ / ₂ "	9"	5"
241811H	23 ³ / ₄ "	17 ³ / ₄ "	11"	5 ¹ / ₂ "
282011H	27 ¹ / ₂ "	19 ¹ / ₂ "	11"	5 ¹ / ₂ "



221609

**NEW
SIZES**

Heavy-Duty Polyethylene Cases

The exterior shell is tough impact-resistant HMW polyethylene. Foam-filled, heavy-duty aluminum rim with black trim and gasket, cast chrome key locks, full-length piano hinge, and deluxe golf grip handle.

Platt#	Inside Dim.			Body Depth
	L	W	D	
181307	18 ¹ / ₂ "	12 ¹ / ₂ "	7"	4"
201407	19 ⁵ / ₈ "	13 ³ / ₄ "	7"	4"
221609	21 ¹ / ₂ "	15 ¹ / ₂ "	9"	5"
241809	23 ³ / ₄ "	17 ³ / ₄ "	9"	5"
282007	27 ¹ / ₂ "	19 ¹ / ₂ "	7"	4"
282009	27 ¹ / ₂ "	19 ¹ / ₂ "	9"	5"
322209	31 ³ / ₄ "	22"	9"	5"
NEW 460909	46"	6"	9"	4 ¹ / ₂ "
NEW 531111	53"	11"	11"	5 ¹ / ₂ "

Custom Foam-Filled Cases



Custom Foam-Filled Cases

Custom foam can be cut to fit almost any application and is perfect for protecting delicate equipment.

"Your Small Quantity Specialist"

FOAM-FILLED CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Blow Molded Cases



Blow Molded Cases

Meet Platt's low cost solution to "Make-Your-Own" case needs.

These cases are foam-filled and manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures.

The hardware features mechanical latches that are field replaceable and a mechanical hinge system that is made to last.

All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack.

Platt#	Inside Dim.			Outside Dim.		
	L	W	D	L	W	D
102	5 ⁵ / ₈ "	3 ⁵ / ₈ "	1 ³ / ₈ "	6 ¹ / ₂ "	4 ¹ / ₂ "	1 ¹¹ / ₁₆ "
103	5 ⁷ / ₈ "	3 ⁷ / ₈ "	1 ⁷ / ₈ "	6 ³ / ₂ "	4 ³ / ₂ "	2 ¹ / ₈ "
104	7 ¹ / ₈ "	4"	1 ⁷ / ₁₆ "	8"	5"	1 ³ / ₄ "
105	7 ¹ / ₈ "	4"	1 ¹⁵ / ₁₆ "	8"	5"	2 ¹ / ₈ "
106	7 ¹ / ₂ "	5"	1 ¹¹ / ₁₆ "	8 ¹ / ₂ "	6"	2"
107	7 ¹ / ₂ "	5"	2 ³ / ₁₆ "	8 ¹ / ₂ "	6"	2 ¹ / ₂ "
108	7 ¹ / ₂ "	5"	2 ¹¹ / ₁₆ "	8 ¹ / ₂ "	6"	3"
202	8 ¹ / ₂ "	5 ¹ / ₂ "	1 ¹¹ / ₁₆ "	9 ¹ / ₂ "	6 ¹ / ₂ "	2"
203	8 ¹ / ₂ "	5 ¹ / ₂ "	2 ¹¹ / ₁₆ "	9 ¹ / ₂ "	6 ¹ / ₂ "	2 ¹ / ₂ "
204	8 ¹ / ₂ "	5 ¹ / ₂ "	2 ¹¹ / ₁₆ "	9 ¹ / ₂ "	6 ¹ / ₂ "	3"
205	8 ¹ / ₂ "	5 ¹ / ₂ "	3 ³ / ₁₆ "	9 ¹ / ₂ "	6 ¹ / ₂ "	3 ¹ / ₂ "
206	9 ¹ / ₂ "	6"	1 ¹⁵ / ₁₆ "	10 ¹ / ₂ "	7"	2 ¹ / ₁₆ "
207	9 ¹ / ₂ "	6"	2 ¹¹ / ₁₆ "	10 ¹ / ₂ "	7"	3"
208	9 ¹ / ₂ "	6"	3 ⁷ / ₁₆ "	9 ¹ / ₂ "	7"	3 ³ / ₄ "
302	10 ³ / ₁₆ "	6 ¹ / ₂ "	1 ¹⁵ / ₁₆ "	11 ³ / ₁₆ "	7 ¹ / ₂ "	2 ¹ / ₄ "
303	10 ³ / ₁₆ "	6 ¹ / ₂ "	2 ¹¹ / ₁₆ "	11 ³ / ₁₆ "	7 ¹ / ₂ "	3"
304	10 ³ / ₁₆ "	6 ¹ / ₂ "	3 ⁷ / ₁₆ "	11 ³ / ₁₆ "	7 ¹ / ₂ "	3 ³ / ₄ "
305	11"	7"	1 ¹⁵ / ₁₆ "	12"	8"	2 ¹ / ₄ "
306	11"	7"	2 ¹¹ / ₁₆ "	12"	8"	3"
307	11"	7"	3 ⁷ / ₁₆ "	12"	8"	3 ³ / ₄ "
308	12 ³ / ₈ "	6 ⁷ / ₈ "	2 ⁷ / ₈ "	13 ¹ / ₂ "	8"	3 ¹ / ₄ "
309	12 ³ / ₈ "	6 ⁷ / ₈ "	4 ¹ / ₁₆ "	13 ¹ / ₂ "	8"	4 ³ / ₈ "
310	12 ³ / ₈ "	6 ⁷ / ₈ "	5 ³ / ₁₆ "	13 ¹ / ₂ "	8"	5 ¹ / ₂ "
402	12 ³ / ₈ "	7 ⁷ / ₈ "	2 ⁷ / ₈ "	13 ¹ / ₂ "	9"	3 ¹ / ₄ "
403	12 ³ / ₈ "	7 ⁷ / ₈ "	4"	13 ¹ / ₂ "	9"	4 ³ / ₈ "
404	12 ³ / ₈ "	7 ⁷ / ₈ "	5 ¹ / ₈ "	13 ¹ / ₂ "	9"	5 ¹ / ₂ "
405	12 ³ / ₈ "	8 ⁷ / ₈ "	2 ⁷ / ₈ "	13 ¹ / ₂ "	10"	3 ¹ / ₄ "
406	12 ³ / ₈ "	8 ⁷ / ₈ "	4"	13 ¹ / ₂ "	10"	4 ³ / ₈ "
407	12 ³ / ₈ "	8 ⁷ / ₈ "	5 ¹ / ₈ "	13 ¹ / ₂ "	10"	5 ¹ / ₂ "
503	13 ⁷ / ₈ "	8 ⁷ / ₈ "	2 ⁷ / ₈ "	15"	10"	3 ¹ / ₄ "
504	13 ⁷ / ₈ "	8 ⁷ / ₈ "	4"	15"	10"	4 ³ / ₈ "
505	13 ⁷ / ₈ "	8 ⁷ / ₈ "	5 ¹ / ₈ "	15"	10"	5 ¹ / ₂ "
506	13 ⁷ / ₈ "	9 ⁷ / ₈ "	2 ⁷ / ₈ "	15"	11"	3 ¹ / ₄ "
507	13 ⁷ / ₈ "	9 ⁷ / ₈ "	4"	15"	11"	4 ³ / ₈ "
508	13 ⁷ / ₈ "	9 ⁷ / ₈ "	5 ¹ / ₈ "	15"	11"	5 ¹ / ₂ "
604	14 ⁷ / ₈ "	10 ³ / ₈ "	2 ⁷ / ₈ "	16"	11 ¹ / ₂ "	3 ¹ / ₄ "
605	14 ⁷ / ₈ "	10 ³ / ₈ "	4"	16"	11 ¹ / ₂ "	4 ³ / ₈ "
606	14 ⁷ / ₈ "	10 ³ / ₈ "	5 ¹ / ₈ "	16"	11 ¹ / ₂ "	5 ¹ / ₂ "
607	15 ⁷ / ₈ "	10 ⁷ / ₈ "	2 ⁷ / ₈ "	17"	12"	3 ¹ / ₄ "
608	15 ⁷ / ₈ "	10 ⁷ / ₈ "	4"	17"	12"	4 ³ / ₈ "
609	15 ⁷ / ₈ "	10 ⁷ / ₈ "	5 ¹ / ₈ "	17"	12"	5 ¹ / ₂ "
610	16 ⁷ / ₈ "	11 ¹¹ / ₁₆ "	3 ⁷ / ₈ "	18"	13"	4 ¹ / ₄ "
611	16 ⁷ / ₈ "	11 ¹¹ / ₁₆ "	5"	18"	13"	5 ³ / ₈ "
612	16 ⁷ / ₈ "	11 ¹¹ / ₁₆ "	6 ¹ / ₈ "	18"	13"	6 ¹ / ₂ "
705	17 ⁷ / ₈ "	12 ¹¹ / ₁₆ "	4 ³ / ₈ "	19"	14"	4 ³ / ₄ "
706	17 ⁷ / ₈ "	12 ³ / ₄ "	5 ³ / ₄ "	19"	14"	6 ¹ / ₄ "
707	17 ⁷ / ₈ "	12 ³ / ₄ "	7 ¹ / ₈ "	19"	14"	7 ¹ / ₂ "
802*	21 ⁵ / ₁₆ "	14 ⁵ / ₁₆ "	6 ⁵ / ₈ "	23"	16"	7"
803*	21 ⁵ / ₁₆ "	14 ⁵ / ₁₆ "	9 ⁵ / ₈ "	23"	16"	10"
902*	25 ¹³ / ₁₆ "	14 ⁵ / ₁₆ "	6 ⁵ / ₈ "	27 ¹ / ₂ "	16"	7"
903*	25 ¹³ / ₁₆ "	14 ⁵ / ₁₆ "	9 ⁵ / ₈ "	27 ¹ / ₂ "	16"	10"

* Molded-in handle reduces "W" dimension usable space.
Please contact Platt Engineering for info

Light-Duty ABS Cases



Light-Duty ABS Cases

This series has been a mainstay of Platt's rugged case line for over 25 years. Light-duty, black, scuff resistant molded ABS thermoplastic forms the tough shell of these cases. Foam-filled, extruded aluminum rim, drawbolt key locks and strong molded handle.

* 1425 has a medium-duty valance

Platt#	Inside Dim.			Body Depth
	L	W	D	
1410	10"	7"	5"	3"
1412	12"	8"	5"	3"
1414	12"	11"	5"	3"
1416	16"	12"	5"	3"
1426	16"	12"	7"	4"
1705	17"	11"	5"	3"
1419	18"	13"	5"	3"
1425*	18"	13"	7"	4"

Medium-Duty ABS Cases



Medium-Duty ABS Cases

Modern look of heavy-duty grained ABS with extruded aluminum frame, these foam-filled cases have a deluxe golf grip handle, cast chrome key locks and piano hinge.

* 2005 has a light-duty valance.

Platt#	Inside Dim.			Body Depth
	L	W	D	
2005*	20"	14"	5"	3"
2007	20"	14"	7"	4"
2207	22"	16"	7"	4"
2407	24"	18"	7"	4"
2807	28"	20"	7"	4"

Parallel Rib Cases



Heavy-Duty Polyethylene Cases With Stylish Parallel Rib Pattern Without Foam

The exterior shell is tough impact-resistant HMW polyethylene. Heavy-duty aluminum rim with gasket, black trim, molded handle, full-length piano hinge and cast chrome key locks.

ALL PARALLEL RIB CASES FURNISHED WITHOUT FOAM.


Platt#	Inside Dim.			Body Depth
	L	W	D	
141106PR	14 ¹ / ₈ "	10 ¹ / ₂ "	6"	3 ¹ / ₂ "
171206PR	17 ¹ / ₄ "	12 ¹ / ₂ "	6"	3 ¹ / ₂ "
201675PR	19 ³ / ₄ "	15 ³ / ₄ "	7 ¹ / ₂ "	4 ¹ / ₂ "
221006PR	22"	10"	6"	3 ¹ / ₂ "
241609PR	23 ³ / ₄ "	15 ³ / ₄ "	9"	4 ¹ / ₂ "
251709PR	25"	16 ³ / ₄ "	9"	4 ³ / ₄ "

Guardsman ATA 300 Cases



1116CPU case has foam cavity 6-1/2"x16"x17" with keyboard cavity 2"x7"x19".

1114M Monitor case is lined with 1" high density foam. Included in case are 4 pieces of 1" and 4 pieces of 1/2" Polyethylene Foam. Case will fit monitors 19"x19"x19" or smaller.



1016HW & 1018HW come with four ball bearing wheels and telescoping handle.



1118LAP holds 5 laptops and contains 2 cavities for projector, cords and cables.

Platt Guardsman cases can be made to hold any quantity of laptops. Contact Platt engineering department for assistance.

Guardsman™ ATA 300 Shipping Cases

Heavy-duty black HMW polyethylene material with unique continuous industrial frame based on Platt's patented Guardsman™ design and construction. All hardware is recessed for wearability and shipping purposes. Cases come with locking provision, spring loaded handle, full-length piano hinge and security type bolts. All top and body interiors of cases are lined with high density foam.

DIMENSIONS SHOWN ARE INSIDE THE FOAM LINING.

Platt#	Inside Dim.			Body Depth
	L	W	D	
1008	12"	8 1/2"	14"	11"
1012	16 1/2"	10"	16"	12 1/2"
1013	17 1/2"	11"	8"	6"
1016	20 1/2"	14 1/2"	14"	10 1/2"
1016HW	20 1/2"	14 1/2"	14"	10 1/2"
1018	25 1/2"	17 1/2"	17 1/2"	14 1/2"
1018HW	25 1/2"	17 1/2"	17 1/2"	14 1/2"
1114M	19"	19"	19"	16"
1116CPU	20"	12 1/2"	24"	20"
1118LAP	25 1/4"	15 1/4"	13"	9 3/4"

Ordering: Cases all available with lining only (add L to end of P/N) or foam filled with layers of foam (add F to end of P/N).
(except 1114M, 1116CPU and 1118LAP)

*1112 This case has been discontinued as a stock item. It is still available as a special.

All cases also available as a Jetalum™ all aluminum construction.
(See page 9 for photo)

NEW

TSA Accepted Locks

- Airport Luggage & Security
- TSA Accepted
- TSA Recognized
- Opened Lock Window
- Patented Security Window
- Prevents Surreptitious Entry
- Red Window - Lock Opened
- Green Window - Lock Not Opened
- 1,000 Re-settable Combinations
- Regular and Heavy Duty Shackles
- Different styles and colors available



TSA6430PSB
NEW



TSA7400PW
NEW



TSA7470PFY
NEW

Custom ATA Guardsman Cases

Multi-Laptop Case



Piggyback Case



Multi-Purpose Shipping Case



Patented Guardsman™ Design & Construction

Platt's Guardsman cases are unique and easily recognizable. Construction features HMW polyethylene thermoplastic sheets bent to size to form strong but lightweight shipping cases ideal for computer, video, audio, medical, electronic instrumentation and industrial equipment. All cases use our UNIQUE CONTINUOUS FRAME CONSTRUCTION for maximum strength and durability. Cases include full-length piano hinge, recessed spring-loaded handle and latches.

Foam interiors can be made to your individual requirements using polyurethane ether or ester foam, polyethylene foam, anti-static, conductive or static dissipative foam.

Options include different colors, stacking studs, combination lock, fixed or removable casters, wheels and telescoping handle, key lock, padlockable latches and conductive polyethylene for protection against ESD discharge damage.

All orders (EVEN ONE CASE) are quoted by Platt depending on size, foam interiors, other options and quantity. Call your local distributor.

Color / Material Options

Platt's Guardsman cases are available in black, safety yellow, safety orange, gray, blue, green, and white. Other special colors are available with minimum order requirements. Also available as a Jetalum™ all aluminum construction. Contact factory for availability.

Telescoping Handle ATA

Platt's Guardsman cases are available with built-in wheels and telescoping handle. Not only are the Guardsman cases able to take the rigors of shipping, but now, when you get the case, it is easy to move. Convenient for display cases or product cases.

"Your Small Quantity Specialist"

Pelican Watertight Cases



New & Improved Latches.



1120 Guard Box®
1150 Case™
1200 Case™
1300 Case™
1400 Case™
1450 Case™
1470 Case™
1470 Case™
1490 Case™
1500 Case™
1520 Case™
1550 Case™
1600 Case™
1620 Case™
1650 Case™
1700 Travel VaultII®
1750 Travel Vault®



Platt#	Inside Dim.			Outside Dim.			Ship Weight
	L	W	D	L	W	D	
0350	20"	20"	18 1/2"	22 1/2"	22 7/16"	21 1/4"	26 lbs.
0370	24 1/4"	24"	23"	25 1/4"	26 1/2"	26 1/2"	30 lbs.
1010	4 5/16"	2 13/16"	1 5/8"	5 7/16"	4 1/16"	2 1/8"	3.2 lbs.
1020	5 1/4"	3 1/2"	1 5/8"	6 3/8"	4 3/4"	2 1/8"	4 lbs.
1030	6 3/8"	2 5/8"	2"	7 1/2"	3 7/8"	2 7/16"	4.24 lbs.
1040	6 7/16"	3 13/16"	1 11/16"	7 1/2"	5 1/16"	2 1/8"	4.85 lbs.
1050	6 7/16"	3 13/16"	2 11/16"	7 1/2"	5 1/16"	3 7/8"	6.4 lbs.
1060	8 5/16"	4 5/16"	2 3/16"	9 3/8"	5 9/16"	2 5/8"	6.88 lbs.
1120WF	7 3/8"	4 7/8"	3 1/16"	8 1/4"	6 9/16"	3 9/16"	11.2 lbs.
1150WF	8 3/8"	5 7/8"	3 9/16"	9 1/4"	7 9/16"	4 3/8"	2.5 lbs.
1200WF	9 3/8"	7 1/4"	4 1/16"	10 5/8"	9 11/16"	4 7/8"	3 lbs.
1300WF	9 3/8"	7 1/4"	6 1/8"	10 5/8"	9 11/16"	6 7/8"	3.5 lbs.
1400WF	12"	9 1/16"	5 3/16"	13 3/8"	11 5/8"	6"	5.5 lbs.
1420WF	13"	5"	10"	15"	8 1/2"	10 1/2"	5.5 lbs.
1450WF	14 13/16"	10 3/8"	6"	16"	13"	6 7/8"	7.5 lbs.
1470WF	15 3/4"	10 9/16"	3 3/4"	16 11/16"	13 1/16"	4 3/8"	7.8 lbs.
1470CC#1	15 3/4"	10 9/16"	3 3/4"	16 11/16"	13 1/16"	4 3/8"	6.8 lbs.
1470CC#2	15 3/4"	10 9/16"	3 3/4"	16 11/16"	13 1/16"	4 3/8"	6.75 lbs.
1470AC	15 3/4"	10 9/16"	3 3/4"	16 11/16"	13 1/16"	4 3/8"	6.75 lbs.
1490WF	17 7/8"	11 1/2"	4 1/8"	19 7/16"	13 15/16"	4 11/16"	6.5 lbs.
1490CC#1	17 7/8"	11 1/2"	4 1/2"	19 7/16"	13 15/16"	4 11/16"	8.3 lbs.
1490CC#2	17 7/8"	11 1/2"	4 1/2"	19 7/16"	13 15/16"	4 11/16"	8.25 lbs.
1490AC	17 7/8"	11 1/2"	4 1/8"	19 7/16"	13 15/16"	4 11/16"	8.25 lbs.
1500WF	17"	11 7/16"	6 1/8"	18 1/2"	14 1/16"	6 7/8"	8.85 lbs.
1504*	17"	11 7/16"	6 1/8"	18 1/2"	14 1/16"	6 7/8"	8.85 lbs.
1510	20 3/16"	11 3/8"	7 1/2"	22"	14"	9"	13.9 lbs.
1520WF	17 7/8"	12 3/4"	6 3/4"	19 7/8"	15 7/16"	7 9/16"	10.75 lbs.
1524*	17 7/8"	12 3/4"	6 3/4"	19 7/8"	15 7/16"	7 9/16"	10.75 lbs.
1526**	17 7/8"	12 3/4"	6 3/4"	19 7/8"	15 7/16"	7 9/16"	10.75 lbs.
1527+	17 3/4"	13 1/2"	7 1/4"	19 7/8"	15 7/16"	7 9/16"	10.75 lbs.
1550WF	18 3/4"	14 3/8"	7 5/8"	20 3/8"	16 7/8"	8 1/8"	13.5 lbs.
1600WF	21 3/4"	16 13/16"	7 7/8"	24 1/4"	19 7/16"	8 11/16"	16 lbs.
1610WF	22 3/16"	17 1/8"	10 9/16"	24 9/16"	19 5/16"	11 15/16"	25.5 lbs.
1620WF	22 1/16"	17"	12 3/16"	24 3/16"	19 3/8"	13 7/8"	27 lbs.
1650WF	29"	17 7/8"	10 1/2"	32 3/4"	20 1/2"	11 5/16"	30 lbs.
1660WF	29 7/8"	20 11/16"	17 5/8"	31 1/2"	22 7/8"	18 7/8"	49 lbs.
1700WF	35 3/4"	13 13/16"	5 1/4"	31 1/8"	17 13/16"	6 1/8"	19 lbs.
1720WF	42"	13 1/2"	5 1/4"	44 3/8"	16"	6 1/8"	21.15 lbs.
1750WF	50 1/2"	13 7/16"	5 1/4"	53"	17 7/16"	6 1/16"	25.65 lbs.

*Case With Padded Dividers **Case With Travel Bag +Travel Bag Only

Pelican Flashlights

PELICAN® FLASHLIGHTS

Platt carries a complete line of Pelican® Flashlights. Please call Platt Customer Service at 1-800-299-PLATT (997-5288) for more information.



1900C



2400C

PELICAN® 100% GUARANTEE

Unconditional lifetime guarantee of excellence by Pelican® Products, Inc. Warranty and additional information available through your local dealer or call 1-800-99-PLATT (997-5288) or visit our webpage www.plattcases.com.

Pelican Tool Case



Platt#	Inside Dim.		
	L	W	D
1520T-CB	17 7/8"	12 3/4"	6 3/4"

PELICAN® FEATURES

Pelican protector case is now available as a Platt tool case. This case is constructed of high impact co-polymer resin with a pressure relief valve and padlock loops. Meets MIL-STD 4150 for stacking, drop test and chemical attack.

This case is not watertight.

MOLDED TOOL CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Super-Size Cases



369TH-SGSH

Super-Size™ Tool Cases with Wheels and Telescoping Handle

High-tech rugged HMW polyethylene ribbed case in a large size. Black valance with all black hardware, combination lock, recessed latches, full-length piano hinge, stitched vinyl steel-core handle, ball-bearing wheels, accessory pouch and telescoping handle. Comes standard with Platt's SG and SH super-size pallets. Accepts only a super-size pallet.

Platt#	Inside Dim.			Color
	L	W	D	
369TH-SGSH	17½"	14⅝"	9"	Black
369THG-SGSH	17½"	14⅝"	9"	Gray
369THY-SGSH	17½"	14⅝"	9"	Yellow



359TG-SGSH 359TY-SGSH

359T-SGSH

Super-Size™ Tool Cases

High-tech rugged HMW polyethylene ribbed case in a large size. Black valance with all black hardware, combination lock, full-length piano hinge, stitched vinyl steel-core handle and cast key locks. Comes standard with Platt's super-size pallets SG and SH. Accepts only a super-size pallet.

Platt#	Inside Dim.			Color
	L	W	D	
357T-SGSH	17½"	14⅝"	7"	Black
359T-SGSH	17½"	14⅝"	9"	Black
359TG-SGSH	17½"	14⅝"	9"	Gray
359TY-SGSH	17½"	14⅝"	9"	Yellow

Custom Tool Cases



Ask us about our "Molded-In Logo" option!

"Your Small Quantity Specialist"

Military Type Super-Size Cases



349TG-SGSH

349TY-SGSH

349T-SGSH

Military Type Super-Size™ Tool Cases

High-tech rugged HMW Polyethylene ribbed case in a large size with molded in-corner bumpers to protect the valance and hardware. Black valance with all black hardware, combination lock, full-length piano hinge, spring loaded handle and twist draw latches. Comes standard with Platt's super-size pallets SG and SH. Accepts only a super-size pallet.

Platt#	Inside Dim.			Color
	L	W	D	
349T-SGSH	17½"	14⅝"	9"	Black
349TG-SGSH	17½"	14⅝"	9"	Gray
349TY-SGSH	17½"	14⅝"	9"	Yellow

Rotational Molded Case



Rotational Molded Tool Case with Wheels and Telescoping Handle

Heavy-duty rotational-molded polyethylene shells with 15% thicker corners, unique molded-in bumper system so hardware and valance are "drop-protected". Cases are stackable, rugged with key locking latches, full-length piano hinge, deluxe golf grip handle, combo lock and a provision for padlock or cable tie.

Platt#	Inside Dim.			Color
	L	W	D	
410TH-SGSH	18"	15"	10½"	Black

Transporter Tool Case



Transporter Tool Case with Wheels and Telescoping Handle

This tool case has two over-sized tool pallets which is equivalent to 3 super-size pallets. With full-length piano hinge, recessed hardware, strong rib design, HMW polyethylene, heavy-duty mill valance with black tape inlay and locking provision.

Platt#	Inside Dim.			Body Depth
	L	W	D	
555TH-XGHXEH	26"	16"	13"	10"

Tools Not Included

MOLDED TOOL CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Ultimate Polyethylene



Ultimate Polyethylene Tool Cases with Black Hardware

The "Ultimate" Platt tool case also features the durable molded ribbed HMW polyethylene shell. Constructed with black anodized heavy-duty frame and gasket, black finished cast key locks and combination lock, deluxe golf grip handle and full-length piano hinge. Comes standard with molded adjustable bottom divider, convenient literature pocket and two molded pallets.

Platt#	Inside Dim.			Color
	L	W	D	
976T-CB	18"	13"	7"	Black
978T-CB	18"	13"	8"	Black
978TG-CB	18"	13"	8"	Gray

Deluxe Polyethylene



Deluxe Polyethylene Tool Cases with Chrome Hardware

Molded HMW polyethylene with durable ribbed shell. Features a heavy-duty aluminum frame with black trim and gasket, cast key locks, deluxe golf grip handle, full-length piano hinge and comes in three popular sizes. Comes standard with molded adjustable bottom divider, convenient literature pocket and two molded pallets.

*920TC-CB has combination lock.

Platt#	Inside Dim.			Color
	L	W	D	
926T-CB	18"	13"	6"	Black
928T-CB	18"	13"	8"	Black
928TG-CB	18"	13"	8"	Gray
928TY-CB	18"	13"	8"	Yellow
920TC-CB*	18"	13"	9"	Black

Premium Polyethylene



Premium Polyethylene Tool Cases with Recessed Hardware

Molded HMW polyethylene with durable ribbed shell. Features attractive black powder coated frame, all black hardware, including recessed key lock, deluxe golf grip handle and full-length piano hinge. This quality case comes standard with molded adjustable bottom divider, convenient literature pocket and two molded pallets.

Platt#	Inside Dim.			Color
	L	W	D	
946T-CB	18"	13"	6"	Black
946TY-CB	18"	13"	6"	Yellow
946TG-CB	18"	13"	6"	Gray

Tools Not Included

Standard Polyethylene



Standard Polyethylene Tool Cases

Molded HMW polyethylene with durable ribbed shell. Features medium-duty valance, cast key locks and molded handle. Interior has molded fixed divider, convenient literature pocket and two molded pallets.

*605T-C comes with single pallet.

Platt#	Inside Dim.			Color
	L	W	D	
600T-CB	18"	13"	6"	Black
605T-C*	18"	13"	5"	Black

Deluxe Polypropylene



Deluxe Polypropylene Tool Cases

Black, chemical resistant with extruded aluminum frame, golf grip handle, cast chrome key locks and full-length piano hinge. Interior has divider system, two molded pallets and deluxe literature pocket.

*805T-C comes with one pallet.

Platt#	Inside Dim.		
	L	W	D
800T-CB	18"	13"	6"
805T-C*	18"	13"	5"

Economy Polypropylene



Platt#	Inside Dim.		
	L	W	D
836T-CB	18"	13"	6"

Economy Polypropylene Tool Case

Black injection molded polypropylene shells, heavy-duty valance with gasket, cast key locks, stitched vinyl steel-core handle, full-length piano hinge and literature pocket.

Deluxe Soft-Molded



Platt#	Inside Dim.			Color
	L	W	D	
610T-C	18"	13"	5"	Oxford

Deluxe Soft-Molded Tool Case

Features patented construction utilizing ABS thermoplastic shell interior, quality leather-like vinyl exterior, black anodized extruded aluminum frame for maximum strength, combination lock, cast bolts, and golf grip handle. Interior has one molded pallet, bottom divider and deluxe literature pocket. Oxford Brown. Rugged tool case with the appearance of an attache - this professional looking case will get you in the front door.

ATA TOOL CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Guardsman ATA 300 Cases



Guardsman™ ATA Tool Cases

Heavy-duty HMW polyethylene material with unique continuous industrial frame both on the exterior and interior of case for maximum strength (ATA 300). Recessed hardware, locking provision, full-length piano hinge, spring loaded handle and security type bolts. Deluxe literature pocket in lid and two molded pallets. Foam in bottom of case for meters.

Platt#	Inside Dim.			Outside Dim.			Color
	L	W	D	L	W	D	
747T-CB	17½"	11"	9"	19"	13"	10"	Black
747TY-CB	17½"	11"	9"	19"	13"	10"	Yellow
747TG-CB	17½"	11"	9"	19"	13"	10"	Gray
747TO-CB	17½"	11"	9"	19"	13"	10"	Orange
747TBLU-CB	17½"	11"	9"	19"	13"	10"	Blue
747TGREEN-CB	17½"	11"	9"	19"	13"	10"	Green



777TH-SGSH

757TH-CB

788TH-XGHXEH

Guardsman™ ATA Tool Cases with Wheels and Telescoping Handle

Platt's rugged Guardsman™ ATA Case has now been designed and is available with a telescoping handle and built-in wheels. The case has all recessed hardware, locking provision, full-length piano hinge, literature pocket, two molded pallets and foam in bottom for meters. 777TH comes with super-size pallets and the 788TH-XGHXEH has over-sized pallets that are equivalent to three super-size pallets.

Platt#	Inside Dim.			Outside Dim.			Color
	L	W	D	L	W	D	
757TH-CB	18½"	13"	9¾"	19½"	14"	12½"	Black
777TH-SGSH	18½"	14½"	9¾"	19½"	15½"	12½"	Black
777THY-SGSH	18½"	14½"	9¾"	19½"	15½"	12½"	Yellow
777THG-SGSH	18½"	14½"	9¾"	19½"	15½"	12½"	Gray
777THO-SGSH	18½"	14½"	9¾"	19½"	15½"	12½"	Orange
777THBLU-SGSH	18½"	14½"	9¾"	19½"	15½"	12½"	Blue
777THGREEN-SGSH	18½"	14½"	9¾"	19½"	15½"	12½"	Green
788TH-XGHXEH	25¼"	15¼"	13"	26¼"	16¼"	16"	Black

(757 and 788 Series also available in yellow, gray, orange, blue, white, and green.)

Aluminum Guardsman ATA 300 Cases

Aluminum Guardsman™ ATA Tool Cases

Heavy-duty textured aluminum material with unique continuous industrial frame both on the exterior and interior of case for maximum strength (ATA 300). Recessed hardware, locking provision, full-length piano hinge, spring loaded handle and security type bolts. Literature pocket and two molded pallets. Foam in bottom of case for meters.



747TALUM-CB

757THALUM-CB

*Wheel & Handle Cases

Platt#	Inside Dim.			Color
	L	W	D	
747TALUM-CB	17½"	11"	9"	Aluminum
757THALUM-CB*	18½"	13"	9¾"	Aluminum
777THALUM-SGSH*	18½"	14½"	9¾"	Aluminum
788THALUM-XGHXEH*	25¼"	15¼"	13"	Aluminum

Custom Guardsman Tool Cases



Platt's Patented Guardsman ATA Tool Cases are built to exceed the exacting ATA shipping requirements. They have been tested and approved to ATA 300 specs.

They're constructed from an **ultra-durable (yet light-weight) HMW polyethylene material** with your choice of seven standard colors. They're **line bent to assure uniform thickness and unsurpassed strength**. By using polyethylene, these cases are **up to 50% lighter** than traditional wood transit cases, and because they are bent instead of formed, all corners and edges are the same thickness as the rest of the case, thereby eliminating the traditional weak spots associated with other materials.

Polyethylene can be stored in any environment from -40° to 140° and is unaffected by all common industrial solvents. Plus, our bent aluminum continuous framing system provides the ultimate in strength, and attractive appearance. Our valance system has a gasket for water/dust resistance. Platt uses completely recessed hardware which further resists damage in transit and can be furnished with combination locks or key locks in the latches.

These cases are also available as a Jetalum™ all aluminum construction.

Platt's Engineering Department will assist you in the design of your Guardsman ATA case. Pallets and interiors can be customized to hold your selection of tools.

"Your Small Quantity Specialist"

Tools Not Included

TOOL PALLETS

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

All Platt standard size stock tool cases come with molded pallets. The top pallet is always pallet C. The bottom pallet is always B. If these pallets are not appropriate for the user's tools, Platt will substitute the molded pallets of user's preference at no charge, or sewn pallets for a small additional cost.

If you wish to change the pallet(s) in a stock case, simply change the pallet

letter(s) after the case letter, i.e. 600T-KL. (First letter is top pallet, second letter is bottom pallet).

Pallets can be ordered separately by ordering the individual pallet letter. All of our sewn pallets can be furnished as top or bottom pallets. Our urethane pallets are molded with just the right amount of give, but also toughness to be a pleasure to work with. Our sewn pallets have strong

pockets and pouches to hold a wide range of tools and parts.

All outer edges of our pallets are sewn through our heavy backing material to prevent the separation you might have experienced in pallets of lesser quality.

Platt can custom design sewn pallets in a broad range of configurations. Contact Platt for further details,

specific capabilities, and minimum order quantity.

All Platt super-size stock cases come with SGSH pallets. (357T, 349T, 369T, 410TH, 777TH) Super-size pallets are designated with S, in front of the pallet letter, i.e. SE

Clean room pallets available upon request.

Injection Molded



A/B

All-purpose pallets with 27 pockets each. (A) Pallet, if specified as top, includes turnbutton. Bottom pallet (B) comes without turnbutton.

Platt#	Dim.		Options
	L	W	
A	17 1/4"	12 1/4"	Turnbutton
B	17 1/4"	12 1/4"	-



C/D

All purpose pallets with 22 pockets each. (C) Pallet, if specified as top, includes turnbutton. Bottom pallet (D) comes without turnbutton.

Platt#	Dim.		Options
	L	W	
C	17 1/4"	12 1/4"	Turnbutton
D	17 1/4"	12 1/4"	-

Sewn & Riveted



E/SE



G/SG



I/SI



K/SK



F/SF



H/SH



J/SJ



L/SL

Field service pallet designed primarily for automotive material handling and major appliance installation and maintenance.

Field service pallets designed primarily for the installation and maintenance of office copiers and office machines.

Field service pallets designed primarily for computer and high technology installation and maintenance.

Field service pallets designed primarily for electronic installation and maintenance.



M/SM



O/SO



Q/SQ

Field service pallet designed primarily for telecommunication installation and maintenance.

Platt's padded notebook computer pocket mounted to a pallet allows a protective compartment for your computer.



N/SN

Field service pallets designed primarily for HVAC installation and maintenance



P/SP

Platt's quality attaché pockets mounted to a pallet allows you to carry paperwork in your tool case.



R/SR

A clipboard on a pallet allows you an area to hold papers and documentation.

Platt#	Dim.		Options
	L	W	
Standard	17 1/4"	12 1/4"	Standard
"S"	17 1/4"	14 1/2"	Super-size

Additional Pallet Information

The outer edges of Platt sewn pallets are sewn all the way through the heavy backing material and reinforced with rivets to prevent the separation and tearing common in pallets of lesser quality.

Pallets may be ordered without cases. Simply specify the pallet letter.

Platt will custom design pallets for your specific needs. Please contact your local Platt representative or call our customer service department for details. A minimum quantity may apply.

Custom Pallets



All pallets can be ordered as top pallet or bottom pallet. Turnbutton comes on top pallet.

Winged Pallets



Winged Pallets

Allows for full display of your tools, and for easy access to any item. The center pallet is a G pallet and the wings are modified H pallets.

Platt#	Dim.			Size
	L	W	D	
WGH	17 1/4"	12 1/4"	2"	Standard size
WSGSH	17"	14"	2"	Super-size

Book Pallet



Book Pallet

Side-hinged set of pallets allows loading of additional tools in lid of case. The main pallet is an H pallet and the side pallet is a G pallet.

Platt#	Dim.			Size
	L	W	D	
BSGSH	17 1/4"	14 1/2"	2"	Super-size

Nylon Zipper Tool Cases



Nylon Zipper Tool Cases

Black nylon zipper tool cases designed to hold all of the standard size tool pallets shown on page 10. The 651ZT single zipper holds two pallets. The 652ZT double zipper holds four pallets. Now you can have a zipper tool case in the configuration you want by selecting your choice of pallets. i.e. 651ZT-GH or 652ZT-GHPQ.

IF NO PALLET ARE SPECIFIED, 651ZT AND 652ZT ARE SHIPPED EMPTY WITHOUT PALLET.

Shoulder strap included.

Platt#	Outside Dim.		
	L	W	D
651ZT	18"	13"	3"
652ZT	18"	13"	6"

Soft Rolling Tool Case



Soft Rolling Tool Case

Heavy-duty tool case holds two standard tool pallets and comes complete with wheels and telescoping handle for easy transportation of your tools. G and H pallets are supplied unless otherwise specified. Additional pockets for notebook computer, cords, accessories, etc.

Platt#	Outside Dim.		
	L	W	D
191308ZTH-GH	19"	13"	8"

Trouble Shooter



Trouble Shooter

Consistently a best seller, the 660ZT series "Trouble Shooter" carrying case is designed for versatility. With 29 sewn tool pockets and a meter pouch on the inside, 2 additional meter pouches and a document pocket on the outside, this case will carry a wide variety of tools. Constructed of heavy-duty nylon with industrial strength zipper for durability.

Platt#	Outside Dim.			Colors
	L	W	D	
660ZT	13"	10"	2"	Black
660ZTBLU	13"	10"	2"	Blue
660ZTBURG	13"	10"	2"	Burgundy
660ZTGREEN	13"	10"	2"	Green

Master Technician



Master Technician

For additional capacity, the larger 669ZT series "Master Technician" carrying case contains 47 sewn tool pockets and a meter pouch inside, as well as 2 meter pouches and document pocket on the outside. Constructed of heavy-duty nylon with industrial strength zipper for durability. **Shoulder strap included.**

Platt#	Outside Dim.			Colors
	L	W	D	
669ZT	15 1/2"	11"	2"	Black
669ZTBLU	15 1/2"	11"	2"	Blue
669ZTBURG	15 1/2"	11"	2"	Burgundy
669ZTGREEN	15 1/2"	11"	2"	Green

Tools Not Included

"Quality That Lasts"

SEWN TOOL CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Combo Tool & Attaché/Notebook



679ZT



689ZT

Combo Tool and Attaché/Notebook Computer

Keep your files, manuals and misc. paperwork organized and readily available with the 689ZT "Combo Tool and Computer Attaché" case from Platt. This case contains the same interior 47 tool pocket and meter pouch configuration as our popular 669ZT, plus a padded pocket for your computer (689ZT) or a built-in clipboard (679ZT).

Shoulder strap included.

Platt#	Outside Dim.		
	L	W	D
679ZT	17½"	10¼"	6"
689ZT	18"	13"	6"

Mini Tech



601ZT



602ZT



602ZT

Mini Tech

The compact "Mini Tech" may be used alone or stowed inside one of our larger cases. With 14 interior sewn tool pockets and one inside pouch, it is ideal when only a limited number of tools are needed. The 602ZT contains an additional 3 exterior pockets and wrapped handles.

Platt#	Outside Dim.		
	L	W	D
601ZT	10½"	7⅜"	2"
602ZT	10½"	7⅜"	2"

Technician



Platt#	Outside Dim.		
	L	W	D
665ZT	13¾"	13"	2"

Technician

For users who prefer molded tool pallets, Platt offers the 665ZT "Technician" case as an alternative to the popular 660ZT series with sewn pockets. The 665ZT features 27 molded pockets and 2 hook and loop pockets inside the case. Outside, 2 pockets with hook and loop flaps and a full-length document pocket provide additional storage capacity.

Machine/Copier Repair Field Service



Platt#	Outside Dim.		
	L	W	D
641ZT	18½"	13"	3"

Machine/Copier Repair Field Service

The 641ZT "Machine/Copier Repair Field Service" carrying case with sewn in pockets features the same inside pocket configuration as our popular G & H pallet set (see pg. 10). This configuration was specifically designed for the unique needs of the office machine and copier field technician. Outside, 2 pockets with hook and loop flaps and a full-length document pocket provide additional storage capacity.

Computer Field Service



Platt#	Outside Dim.		
	L	W	D
642ZT	18½"	13"	3"

Computer Field Service

The 642ZT "Computer Field Service Case" is the same as the 641ZT with the exception that the inside sewn pocket configuration is the same as our pallet set I & J (see pg.10), specifically designed for the unique needs of computer and computer based equipment repair and maintenance.

Field Service Supervisor



Platt#	Outside Dim.		
	L	W	D
691ZT	18½"	13"	3"

Field Service Supervisor

Carry a full complement of tools plus all your paperwork in this attractive attaché style 691ZT "Field Supervisor Case". With a slim 3" width profile, this cleverly designed carrying case still has room for 22 sewn in tool pockets, a snap pouch and hook and loop straps (for a flashlight or larger tools) on one side and a deluxe 3-pocket attaché interior on the other side. Outside, 2 pockets with hook and loop flaps and a full-length document pocket offer additional storage capacity.

YOU'LL FIND QUALITY FEATURES IN ALL PLATT SEWN TOOL CASES

Heavy-duty nylon construction with industrial strength memory zippers. Outside pockets with hook & loop flaps provide additional storage capacity. Additional features include poly web straps with wrapped handles, and water and stain resistant exteriors. Platt is known for its superior workmanship.

Tools Not Included

SEWN TOOL CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Field Service Tech



Platt#	Outside Dim.		
	L	W	D
695ZT	17 1/2"	10 1/4"	6"

Field Service Tech

Need to carry multiple tools and parts to the job? Store them all in the double-sided 695ZT "Field Service Tech" case. One side features 39 sewn in tool pockets and one large pouch with 3 more storage pouches and a full-length literature holder in the other side. Outside, 2 pockets with hook and loop flaps and a full-length document pocket provide additional storage capacity. **Shoulder strap included.**

Telecom



Platt#	Outside Dim.		
	L	W	D
630ZT	14"	10"	3"

Telecom

Compact and economical, the 630ZT Telecom case still includes the hook and loop strap "buttset" holder along with 20 sewn tool pockets and 1 parts pouch.

Vacuum Pack



Platt#	Outside Dim.		
	L	W	D
VP511	18"	7 1/2"	6"

Vacuum Pack

Use the VP511 "Vacuum Pack" to securely store and carry your portable vacuum system and accessories. This sturdy nylon carrying case will accommodate most portable vac systems including 3M#496, Atrix's AAA Toner vac, etc. Lid compartment has sewn pockets to hold tools and accessories. **Shoulder strap included.**

Pro Telecom



Platt#	Outside Dim.		
	L	W	D
680ZT	18"	13"	4"

Pro Telecom

Many new tools, testers and accessories are now being used by telecom installers. The 680ZT has been designed by telecom professionals. It is designed to hold all of the standard tools such as screwdrivers, hex keys, retrievers, marks, probes, punch tools, scissors, wrenches, pliers, wire strippers, solder gun, test adapters, lamp puller, polarity tester, cable tester, flashlight and much more. Now you have a case "designed by professionals for professionals". **Shoulder strap included.**

Master Telecom



Platt#	Outside Dim.		
	L	W	D
685ZT	15 1/2"	13"	3"

Master Telecom

Custom designed for Platt by professional telecom installers, the deluxe 685ZT "Master Telecom" carrying case efficiently and securely stores the specialized tools used by telecom installers. Stay organized with 24 sewn interior pockets, 5 small parts pouches, special pockets for tone generator and probe set, and hook and loop strap "buttset" holder. Unique clip-on "stay straps" allow case to function as a handy shelf when hung by the carrying handle on a ladder or wall hook. **Shoulder strap included.**

LAN



Platt#	Outside Dim.		
	L	W	D
688ZT	17"	12 1/4"	5"

LAN

The 688ZT LAN case is designed to hold a multitude of tools and testers for installation and trouble-shooting. This double-sided carrying case features 40 sewn in tool pockets and 4 pouches in one side and 11 sewn in tool pockets with 4 additional pouches in the second side. Outside, 2 pockets with hook and loop flaps and a full-length document pocket provide additional storage capacity. **Shoulder strap included.**

Basic Telecom



Platt#	Outside Dim.		
	L	W	D
675ZT	13 3/4"	12 7/8"	3"

Basic Telecom

Slightly smaller than the Master Telecom case, the 675ZT Basic Telecom carrying case features 14 sewn tool pockets and 6 small parts pouches. Includes the same unique clip-on "stay straps" to allow case to function as a handy shelf. **Shoulder strap included.**

Custom Sewn Tool Cases



Tools Not Included

"Quality That Lasts"

SEWN TOOL CASES

PLATT STANDARD PRODUCT CATALOG STD05-1
www.plattcases.com

Tool Bags



Mechanic's Tool Bag

This handy "Mechanic's Tool Bag" is similar to the GI tool bag used for decades by the U.S. Military. Our water-repellent nylon fabric makes it much more durable and with 8 sewn-in pockets on the inside and 2 divided snap pouches on the outside, this compact utility bag will keep your smaller tools and parts organized.

Platt#	Outside Dim.			Colors
	L	W	D	
MTB	12"	6"	6 1/2"	Black
MTB-BLU	12"	6"	6 1/2"	Blue
MTB-BURG	12"	6"	6 1/2"	Burgundy
MTB-GREEN	12"	6"	6 1/2"	Green

NEW

Tool Rolls



Tool Rolls

Durable material that allows you to organize your tools and store them in small places.

Platt#	Outside Dim.	
	L	W
NEW TR01	21"	12"
NEW TR02	37"	14"

CLC Tool Bags, Organizers & Gloves

CLC Tool Bags & Bucket Organizers

Platt carries the complete CLC product line. For additional info, please call for CLC's full line catalog.

Platt#	Description
CLC1101	3 Zippered Bags
CLC1119	48 Pocket Bucket Organizer
CLC1139	14 Pocket Large Traytote Bag
CLC1141	37 Pocket Double Traytote Bag
CLC1148	22 Pocket Drawstring Bucket Bag
CLC1161	23 Pocket Standard BigMouth Bag
CLC1162	29 Pocket MegaMouth Bag
CLC1165	22 Pocket Large BigMouth Bag
CLC1167	30 Pocket Roller Tote Bag
CLC1168	42 Pocket Sideglide Roller Bag
CLC1526	28 Pocket Tool Pouch
CLC4122	61 Pocket Bucket Organizer



CLC1101



CLC1119



CLC1139



CLC1141



CLC1148



CLC1161



CLC1162



CLC1165



CLC1167



CLC1168



CLC1526



CLC4122

CLC Gloves

Handyman

General purpose glove designed for uses like: Carpentry, Automotive, Basic Utility, Plumbing, Assembly Use, etc.

Platt#	Size
CLC125S	Small
CLC125M	Medium
CLC125L	Large
CLC125XL	X Large
CLC125XXL	XX Large



Boxer

Box Handler gloves designed for professional uses like: Warehouse, Transportation, Material/Box Handling, Parcel Delivery, Low Abrasive Applications, etc.

Platt#	Size
CLC135S	Small
CLC135M	Medium
CLC135L	Large
CLC135XL	X Large
CLC135XXL	XX Large



Tradesman

Heavy utility gloves designed for professional uses like: Carpentry, Framing, Roofing, Material Handling, Demolition, Electrical/HVAC, etc.

Platt#	Size
CLC145S	Small
CLC145M	Medium
CLC145L	Large
CLC145XL	X Large
CLC145XXL	XX Large



Tools Not Included

"Quality That Lasts"



Buffalo Case Company Sewn Tool Cases

Designed In U.S.A. - Made Off-Shore



Platt#	Outside Dim.		
	L	W	D
BCC-06	13"	10"	2"

This rugged case has 29 sewn tool pockets and a meter pouch on the inside, plus 2 additional meter pouches and document pocket on the outside. This case is not only attractive, but is very versatile and holds a variety of tools. Constructed of durable 600d polyester with an industrial strength zipper.



Platt#	Outside Dim.		
	L	W	D
BCC-20	10 1/2"	7 3/8"	2"

This durable bag has 14 sewn tool pockets and a parts pouch. This case can be used alone when only a limited number of tools are needed or it can be carried in one of our larger cases.



Platt#	Outside Dim.		
	L	W	D
BCC-58	15 1/2"	13"	3"

This case efficiently stores the specialized tools used by telecom installers. Contains 24 sewn interior pockets, 5 small parts pouches, special pockets for tone generator and probe set and hook and loop strap "butts" holder. Case also comes with side straps to hold the case open as a work platform. Constructed of durable 600d polyester, with industrial strength zipper, this carrying case comes complete with an adjustable and removable shoulder strap.



Platt#	Outside Dim.		
	L	W	D
BCC-59	17 1/2"	10 1/4"	6"

This large capacity tool carrying case is double-sided and has 39 sewn tool pockets, one large snap pouch on one side and 3 additional pouches with a full-length document pocket on the other side. Adjustable and removable shoulder strap also included.



Platt#	Outside Dim.		
	L	W	D
BCC-96	15 1/2"	11"	2"

For additional capacity, this carrying case contains 47 sewn tool pockets and a meter pouch inside, as well as 2 meter pouches and document pocket on the outside. Constructed of durable 600d polyester, with industrial strength zipper, this carrying case comes complete with an adjustable and removable shoulder strap.



Platt#	Outside Dim.		
	L	W	D
BCC-98	18"	13"	6"

This case contains the same interior 47 tool pocket and meter pouch configuration as our BCC-96, plus a padded pocket for your laptop computer. The 2 outside meter pouches and outside document pocket are also standard on this case. Constructed of durable 600d polyester, with industrial strength zipper, this carrying case comes complete with an adjustable and removable shoulder strap.

Buffalo Case Company Molded Tool Case

Case Made in U.S.A.
Pallets Made Off-Shore

This sturdy molded polyethylene tool case has a medium-duty aluminum valance, chrome cast key locks, molded handle and comes complete with 2 sewn tool pallets.

Platt#	Inside Dim.		
	L	W	D
BCC-00T-GH	18"	13"	6"



Computer / AV Cases



Platt#	Inside Dim.		
	L	W	D
AVEXE191308	19"	13"	8"

This case is both rugged and lightweight. Designed for double-duty, it carries both your notebook computer and other equipment such as video projectors, printers and extra hard-drives. Complete with telescoping handle and wheels for convenient transportation.



Platt#	Inside Dim.		
	L	W	D
AVPC020	20"	14"	6 1/2"

The AVPC020 has a main compartment that opens very wide for easy access to your computer equipment. The case has zippered pockets and its telescoping handle and wheel system allows for easy transport of your equipment while keeping your equipment safe in padded compartments.



Platt#	Inside Dim.		
	L	W	D
AVEXE141208	14"	11 1/2"	7"

This case comes with adjustable divider to accommodate your projector and notebook computer. Side pocket has built-in organizer for cell-phone, pens, business cards, etc. **Shoulder strap included.**



Platt#	Inside Dim.		
	L	W	D
LN-777	17 1/2"	10"	5"

Exterior has two storage pockets and one large document pocket. Interior features large literature lid pocket plus storage for disks. Bottom comes with adjustable dividers to accommodate laptop and accessories. **Shoulder strap included.**



Platt#	Inside Dim.			Body Depth
	L	W	D	
261617AHLAP	26"	16"	17"	12"

This durable, rugged transportation case series includes wheels and telescoping handle for convenient transportation. Molded from high molecular weight polyethylene, with rib design for strength, this case is quality that lasts. Interior is set up to hold 5 notebook computers, video projector and accessories.

Aluminum Attaché Cases



Platt#	Inside Dim.		
	L	W	D
06488	17 3/4"	12 3/4"	4 1/2"

Drawn Aluminum Attaché

Sleek and stylish, this satin finish anodized aluminum shell briefcase is lined with tweed fabric and features deluxe interior vinyl pockets for literature, pens, diskettes, etc. Complete with padded handle, combination lock and durable full-length piano hinge.



Platt#	Inside Dim.		
	L	W	D
06448	17 1/4"	12 1/4"	4 1/2"

Fabricated Aluminum Attaché

Attractive ribbed aluminum finish with contrasting black corner assemblies, this lightweight rigid body attaché case features an ergonomic cushion-grip handle, same deluxe tweed/vinyl interior plus 2 combination locks.

Deluxe Soft Molded Attaché Cases



Shown Open
06273

Deluxe Soft Molded Attaché Cases

Patented leather-like vinyl construction sewn over and through molded ABS thermoplastic shell. Black anodized aluminum frame, recessed combination lock and golf grip handle. Interior has 3 pocket soft-touch vinyl folder.

* 06273 and 06373 have recessed combination lock and latches.

** 06283 and 06288 have 2 flip down combination locks.

Platt#	Inside Dim.			Colors
	L	W	D	
06273*	18"	12 1/2"	3 1/2"	Oxford
06373*	18"	12 1/2"	3 1/2"	Black
06283**	18"	12 1/2"	3 1/2"	Oxford
06288**	18"	12 1/2"	4 1/2"	Oxford

High Impact Polypropylene Attaché



Platt#	Inside Dim.		
	L	W	D
06385	18"	13"	5"

High-Impact Polypropylene Attaché

High-impact black polypropylene shells with extruded aluminum frame, cast chrome key locks, full-length piano hinge and golf grip handle. Interior has 3 pocket soft-touch vinyl file folder.

Catalog Cases



Catalog Cases

Patented construction features nylon-backed vinyl top, bottom and sides. Thermoplastic end shells and clear anodized aluminum frames give superior support, making it the best and longest lasting catalog case available. Concealed metal rods running length of case interconnected and riveted to end shells form a lightweight yet flexible frame. With large bottom glides for maximum wearability, outside pocket for convenience, chrome plated combination locks and unique golf grip handle.

Platt#	Inside Dim.			Colors
	L	W	D	
HT219I	17"	12"	8"	Oxford
HT319I	17"	12"	8"	Black
HT221I	19"	12"	8"	Oxford
HT321I	19"	12"	8"	Black

Fabricated Static-Free PCB Cases



Static-Free PCB Cases

Exterior is static-free black cotton duck and anti-static blue poly end shells inter-locked and riveted to an aluminum frame for maximum strength. Two combination locks, golf grip handle, and giant studs for wearability. Interior features our unique adjustable static-free environment with cushioned separators. Platt cases incorporate Dry Stat/Cryovac EPG 112 humidity independent, amine free static dissipative material and Cancel amine free open cell cushion materials that meet or exceed Military specifications MIL-B-81705, Type II and PPP-C-1842A, Type III. With grounding snap. The number of slots determines the amount of board space available in each case. All but the 12-PCB have two dividers for enhanced board storage.

Platt#	Inside Dim.			Slots
	L	W	D	
12-PCB	12"	12"	8"	7
21-PCB	21"	12"	8"	7
24-PCB	17"	14"	13"	11
29-PCB	23"	18"	8"	9



Aerosol Can Sample Case



Detail of inside bottom molded insert for 639.

Aerosol Can Sample Cases

Molded of black ABS thermoplastic exterior with extruded aluminum frame, drawbolt key locks, and molded handle. Interior is custom molded to hold 8 cans.

Platt#	Inside Dim.		
	L	W	D
639	19"	13"	4"

Slide Carousel Projector Case



Slide Carousel Projector Case

ABS thermoplastic exterior with extruded aluminum frame, drawbolt key locks and molded handle. Interior custom formed to fit Ektagraphics series 4000 and 5000 series.

Platt#	Inside Dim.		
	L	W	D
1913	19"	13"	7"

Divider Boxes



Infinite Divider Boxes

The ultimate storage container for small parts. Dividers are moveable in 1/16" increments providing flexibility in organized space. Resistant to oil, solvents and most common chemicals. Sold in master pack quantity only.

Platt#	Dim.			#Dividers
	L	W	D	
PB300	6 ⁵ / ₈ "	3 ⁷ / ₈ "	1 ¹ / ₄ "	6
PB600	10 ¹ / ₂ "	6 ¹ / ₂ "	1 ¹ / ₂ "	6
PB900	13 ³ / ₈ "	8 ³ / ₄ "	1 ⁷ / ₈ "	16

"Quality That Lasts"

Carts



CART01-B

Constructed of 16 gauge steel tubing .625 dia. and 3/8" dia. solid steel rod. Patented safety hook.

CART07

Glides up and down steps and curbs, yet telescopes closed in a single motion to fit airline overheads. When open: 52"x16 1/2"x19"

CART08

Glides up and down steps and curbs, yet telescopes closed in a single motion to fit airline overheads. When open: 52"x16 1/2"x19". Cart has unique rear wheel assembly that supports larger loads.

CART13

For business, home, recreation or travel. Folds to 2 1/2" flat. Large 7 1/4" shock absorbent tires.

CART14

For business, home, recreation or travel. Folds to 2 1/2" flat. Large 7 1/4" shock absorbent tires.

CART15

This durable and lightweight cart fits in the airline overhead compartment and easily stores in a closet or car trunk. Folds to 2" flat.

Platt #	Load Cap.	Load Tray		Height	Ship Weight	Fold Height			Wheel Dia.	Color
		L	W			L	W	D		
CART01-B	275 lbs.	14"	13"	46"	10.3 lbs.	27"	17"	8"	7"	Black
CART07	400 lbs.	16"	12 3/4"	52"	15 lbs	25 1/2"	16 1/2"	5 3/4"	6"	Chrome
CART08	400 lbs.	16"	12 3/4"	52"	19 lbs.	25 1/2"	16 1/2"	5 3/4"	6"	Chrome
CART13	275 lbs.	9 1/2"	19"	40"	11.5 lbs.	25 3/4"	19"	2 1/2"	7 1/2"	Aluminum
CART14	275 lbs.	16"	15 1/2"	44"	16 lbs.	27 3/4"	19"	2 1/2"	7 1/4"	Aluminum
CART15	200 lbs.	15 1/4"	9 1/4"	35 1/2" & 39 1/2"	7 1/4 lbs.	25 1/4"	15 1/4"	2"	5"	Aluminum

* Warranty provided through cart manufacturer.*

Case Replacement Hardware

Handles, Locks & Wheels

Please contact our customer service department at 1-800-99-PLATT if you should ever need to order replacement handles, locks or wheels. Additional hardware available, view our Engineering Catalog on our web site for a full listing.



HAN011

Die-cast chrome
Golf grip handle



HAN011B

Die-cast black
Golf grip handle



HAN006

Black plastic with
cushioned grip,
screw-on handle



LOC005

Die-cast chrome
key-lock



LOC024

Black
key-lock

LOC019

Die-cast chrome
key-lock



LOC011

Combo lock
Black



HDW007

Polyurethane wheel



TSA6430PSB

TSA7400PW

TSA7470PFY

Padlock for cases
with padlock
provision

Custom Sewn Cases



The design options are almost unlimited. In addition to soft-sewn cases, we produce pouches, pockets, padded cases, foam-filled soft cases, plus numerous other workplace styles.

We work primarily with nylon, 600d polyester, and coated vinyl, but other materials are available in a wide range of colors, depending on your application and your preference.

Contact Platt's Engineering Department at (800) 222-1555 to discuss your particular application.

Custom Molded Cases



The design options are almost unlimited. Platt can do standard cases with custom foam, custom molded cases with your choice of hardware, custom logos, doors, handles, wheels, etc. Platt can also do custom tooling to make your case totally unique.

Contact Platt's Engineering Department at (800) 222-1555 to discuss your particular needs and details.

"Your Small Quantity & Custom Case Specialist"

If you don't see a case that fits your needs,
then our custom case department will build it for you.

Custom Colors

Nameplates

In-House Foam Capability

Digital Artwork Capability

Custom Foam

Molded-In Logo

In-House CAD Design Capability

In-House Digital Photo Capability



CUSTOM DIE-CUT FOAM



CUSTOM SOFT-SEWN



INSERTS

Quality that Lasts.

84 years of experience and innovation in the custom case industry has positioned Platt as the industry leader.

It's no wonder when you consider that Platt was the first to introduce: combination locks on luggage, cushioned handles, custom hardware, plastic molded bowling bags, and urethane pallets. Our product development team and experienced engineers have the knowledge to make your dream case a reality.

From soft-sewn zipper tool bags to foam-filled cases, we will work with you to create a case for any use.

Contact our engineering department or your local distributor for additional information.

Platt Luggage, Inc.
4051 W. 51st Street, Chicago, IL 60632
1-800-997-5288, fax 1-773-838-2010
or visit us at www.plattcases.com.