

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202330011

Status:


Active

Overview:

Brad M23 Signal and Power Connectors

Description:

Brad M23 Power Connector, 90° Female, without Contacts, 6 (5+PE) Poles, Cable Diameter 7.00-12.00mm



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                      |
|-------------------------------|--------------------------------------|
| General                       |                                      |
| Product Family                | Field Attachable / Accessories       |
| Series                        | 120233                               |
| Application                   | Power                                |
| IP Rating                     | IP67                                 |
| Material - Contact            | Brass                                |
| Overview                      | Brad M23 Signal and Power Connectors |
| Product Name                  | Brad M23                             |
| Type                          | Field Attachable Connector           |
| UPC                           | 883906301415                         |
| Physical                      |                                      |
| Cable Diameter                | 7.00-12.00mm (.276-.472")            |
| Coupling Type                 | N/A                                  |
| Diagnostics / LEDs            | No                                   |
| Diagnostics Port              | No                                   |
| Gender                        | Female                               |
| Keyway                        | None                                 |
| Material - Connector Body     | Nylon                                |
| Material - Coupling Nut       | N/A                                  |
| Material - Plating Mating     | Gold                                 |
| Orientation                   | 90° Angle                            |
| Poles                         | 6 (5+PE)                             |
| Temperature Range - Operating | -40°C to +125°C                      |
| Wire Size AWG                 | N/A                                  |
| Electrical                    |                                      |
| Current - Maximum per Contact | 28.0A                                |
| Voltage - Maximum             | 600V                                 |
| Material Info                 |                                      |
| Engineering Number            | KAP6S01-005                          |
| Reference - Drawing Numbers   |                                      |
| Sales Drawing                 | SD-120233-002                        |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Reviewed                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Reviewed |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

120233 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION