



# Ring Tongues – Non-Insulated Butted Seam 16-14 AWG




| Product Number† | UPC (054007-) | Wire Range (AWG) | Stud Size | W    | C    | L    | E    | Thickness | Barrel Length | Barrel I.D. | Terminals per Case |
|-----------------|---------------|------------------|-----------|------|------|------|------|-----------|---------------|-------------|--------------------|
| MU14-4R/SK      | 01364         | 16-14            | 4         | 0.25 | 0.22 | 0.60 | 0.47 | 0.030     | 0.25          | 0.090       | 1000               |
| MU14-6R/SK      | 01366         | 16-14            | 6         | 0.25 | 0.22 | 0.60 | 0.47 | 0.030     | 0.25          | 0.090       | 1000               |
| MU14-8R/LK      | 01371         | 16-14            | 8         | 0.31 | 0.33 | 0.74 | 0.58 | 0.030     | 0.25          | 0.090       | 1000               |
| MU14-10RK       | 01372         | 16-14            | 10        | 0.33 | 0.29 | 0.70 | 0.54 | 0.030     | 0.25          | 0.090       | 1000               |
| MU14-10R/LK     | 01373         | 16-14            | 10        | 0.31 | 0.33 | 0.74 | 0.58 | 0.030     | 0.25          | 0.090       | 1000               |
| MU14-14R/SK     | 01374         | 16-14            | 1/4       | 0.47 | 0.40 | 0.89 | 0.65 | 0.030     | 0.25          | 0.090       | 1000               |




MU14-4R/S  
4  
16-14




MU14-6R/S  
6  
16-14




MU14-8R/L  
8  
16-14



MU14-10R  
10  
16-14



MU14-10R/L  
10  
16-14



MU14-14R/S  
1/4  
16-14

Stud Size  
Wire Range