

NX3215SB

For Mobile Communications

■ Features

Ultra compact, thin, and light weight tuning fork crystal unit.

- Excellent heat resistance and environmental characteristics.
- Excellent electric performance optimum for mobile communications, OA (office automation), AV (audiovisual) and Automotive applications are exhibited.
- RoHS compliant. These can meet the requirements of re-flow profiling using lead-free solder.
- Use a metal lid: Excellent shock resistance during chip mounting process comparing to a glass lid.



Pb
Free

RoHS Compliant
Directive 2002/95/EC

■ Specifications

Item	Model	NX3215SB
Nominal Frequency		32.768kHz
Operating temperature (°C)		-40 to +85°C
Storage temperature (°C)		-40 to +85°C
Recommended drive level		0.1μW (0.5μW Max.)
Frequency Tolerance (25 ±3 °C)		±20 × 10 ⁻⁶
Turning point		+25°C ± 5°C
Temperature coefficient		-0.04 × 10 ⁻⁶ / °C ² Max.
Load capacitance		9.0pF, 12.5pF
Series resistance		80kΩ Max.
Shunt capacitance		1pF typ./ 1.5pF Max.
Insulation resistance		500MΩ Min.

■ List of Ordering Codes

Load capacitance	Ordering Code
9.0pF	NX3215SB-32.768K-STD-MUA-7
12.5pF	NX3215SB-32.768K-STD-MUA-6

■ Dimensions

