

1	2	3	4	6	7	8	8
3P 180°	4P 210°	5P 180°	5P 240°	6P 240°	7P 270°	8P 270°	8P 262°



SPECIFICATIONS:

1. CONTACT RESISTANCE: 20m OHM MAX.
2. INSULATION REISTANCE: 300M OHM MIN. AT DC 500V.
3. VOLTAGE WITHSTANDING: AC 1000V FOR ONE MIN.
4. INSERTION FORCE: 4.0KG MAX.
5. WITHDRAWAL FORCE: 1-3.5KG.
6. RATING: 100V A.C. AT 2A

JIN RUH CO., LTD			
TOLERANCES .X $\pm$ / .XXX $\pm$ / .XX $\pm$ / ANGLES /		PART NUMBER JR 2712	
DRAFT W.RAY 052303		DESCRIPTION DIN SOCKET	
CHECK JANNE HUNG		REV. A	
APPROVAL DANNY HSU		SHEET 1/1	