




FEATURES:

- Half pitch 1.27mm(.050") series
- Centronic female connector solder type for cable
- Panel mount receptacle assemblies bracket with latch block and without latch block
- Die-cast body provide EMI/RFI shielded

MATERIALS:

- Housing: Thermoplastic P.B.T UL94V-0 black
- Contacts: Phosphor bronze mating end selective gold plated
- Shell: Steel nickel plated over copper

ELECTRICAL:

- Current Rating: 1 Amp
- Insulation Resistance: 500M Ω /Min
- Withstanding Voltage: AC 500V/Min
- Contact Resistance: 35m Ω MAX
- Temperature Range: -55°C ~ +105°C



SERIES

Solder termination

NUMBER OF CONTACT:

CONTACT TYPES:

F = female

CONTACT PLATING:

- 0 = selective flash gold
- 1 = selective 15u" gold
- 2 = selective 30u" gold

FIXING DEVICE:

L : Latching + Jackscrews
S : jackscrews only

THREADED HOLES:

- 1 : UNC # 2-56
- 2 : UNC #4-40
- 3 : M2.6

Amphenol Socapex
Usine de Dole

ECH.1,5 ENS.

N SERIE

DATE DU TIRAGE

DESIGNATION

MINI D SERIES

TOL. GEN.

VOLUME PIECE

SURFACE PIECE

PROTECTION

TRAITEMENT

MATIERE

CLIENT

MODIFICATIONS

EXEC.

DATE

Approb

IND.

N INTERNE

MD5 SC 68F

COMMUNICATION ET UTILISATION INTERDITES SAUF AUTORISATION