

LED BA 9s (MBC/MCC) superbright, red, 24 V**1.90.690.341/0000****Electrical characteristics of LED**

Forward voltage typ. U_F at I_F	24 V
LED type	---
LED breakdown voltage U_R bei I_F	24
Light current typ. f_v/I_F	---
Light intensity	250 mcd
Max. current, I_F	15 mA
Current reduction from $T_0 = 50\text{ °C}$	---
Wavelength typ.	621 nm

Other specifications

Ambient temp. operating max.	+65 °C
Ambient temp. operating min.	-30 °C
Colour	red
Storage temperature max.	---
Storage temperature min.	---
Operating life	---
Socket	BA 9 s