

HC-B 16-KML-80/O1M32

Order No.: 1687626

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1687626>

HEAVYCON coupling housing B16, with single locking latch, height 80 mm, with support M32

Commercial data

GTIN (EAN)	 4 017918 882655
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 489 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/03/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Design	B16
Height	80 mm
Width	43 mm
Length	94 mm

Housing type	Coupling housings
Locking type	With single locking latch
Type of the screw connection	1x M32
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	High-grade steel, handle: PA-GF
Material grip body interlock	PA-GF

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;