



LOC		DIST		ZONE		LTR		REVISIONS		DESCRIPTION		DATE	APPD
G	14	P				H				REVISED PER 0720-0020-94		2/10/94	W DAP

METRIC
DIMENSIONS LISTED IN mm [INCHES]



1 STAMP AMP 12-10* APPROX AS SHOWN

AMP WIRE RANGE		UL E13288 Listed	
12-10 AWG SOLID OR STRANDED		12-10 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
12-10 AWG SOLID OR STRANDED		MS20659-128 CLASS 1 & 2 P/N 33220 ONLY	



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² (5,180-13,100) CIR MILS SOLID OR STRANDED

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLG DEC ± . 3 PLG DEC ± . ANGLES MATERIAL COPPER PER ASTM B-152 ANNEALED	DR 3-17-93 TA BRINKMAN CHK 3-17-93 DA PATTERSON APPD 3-17-93 DE MILLER APPD 3-17-93 JL HECKLEY PRODUCT SPEC	FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727
--	---	--

APPLICATION SPEC	WEIGHT
-	-

50	LOOSE PIECE, SPCL BOX	8-33220-5
50	LOOSE PIECE, BOX	8-33220-2
1000	TAPE MOUNTED	1-33220-2
-	-	33220
QTY	PACKAGE TYPE	PART NO

AMP AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
SOLISTRAND™

SIZE	CAGE CODE	DRAWING NO
8:1	00779	33220
SCALE	8:1	SHEET 1 OF 1