




4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2004.

© COPYRIGHT 2004 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION





DATE

DWN



APVD

- SEE SHEET 1

30,34,50 POS 40,48,60,96 POS



MATCHING FACE



- 1 USE A P.C.B. WHOSE SURFACES ARE TREATED WITH SOLDER RESIST.
 - 2 SHOW P.C.B LAYOUT FROM THE CONNECTOR-MOUNTING SURFACE SIDE.
 - 3 NUMBER THE CONTACTS IN THE P.C.B OR CONNECTOR CONSECUTIVELY FROM THE -BSC- SIDE.
 - 4 WHEN SCREWING THE CONNECTOR TO THE P.C.B, USE M2 SCREW, NUT AND WASHERS.
- HOUSING MATERIAL : GLASS 20% FILLED P.B.T RESIN (UL94-V0). COLOR:BLACK
 CONTACT MATERIAL : PHOSPHOR BRONZE.
 FINISH : NICKEL 0.00127 MIN THK OVERALL SELECTIVE GOLD 0.00076 MIN THK ON CONTACT AREA AND TIN 0.001MIN THK ON TINE AREA.
 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	6	8	96	47	59.61	63.86	67.09	73.09
OBSOLETE	6	6	48	23	29.21	33.38	36.61	42.61
8	6	5	34	16	20.32	24.49	27.72	33.72
	6	4	60	29	36.83	41.00	44.23	50.23
OBSOLETE	6	3	50	24	30.48	34.65	37.88	43.88
	6	2	40	19	24.13	28.30	31.53	37.53
OBSOLETE	6	5173277-1	30	14	17.78	21.95	25.18	31.18
	P/N	POS	n	A	B	C	D	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN COREL WANG 20AUG2004

CHK STEVEN YAO 23AUG2004

APVD I.ENOMOTO 23AUG2004

PRODUCT SPEC 108-10036

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -
 FINISH

MATERIAL

参照 5/6

参照 - 7

GENERAL TOLERANCE

10 ≥ : ±0.2
 30 ≥ > 10: ±0.25
 100 ≥ > 30: ±0.3
 ANGLES: ±3°

LEAD FREE

STE TE Connectivity

PLUG ASSY HORIZONTAL
 AMPLIMITE .050 SERIES I B-TO-B CONN.

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-5173277

SCALE 2:1

SHEET 2 OF 2

REV B