




7908 Series

D-SUB Crimp Type



Features:

Mates with: 7905, 7906, 7926, 7936.

Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.

Contacts: Copper Alloy.

Shell: Metal.

Recommend Wire: 24AWG to 28AWG.

Electrical Characteristics:


Current Rating: 1 A.

Dielectric Withstanding Voltage: AC 1000V.

Insulator Resistance: 1000M Ω min.

Contact Resistance: 30m Ω max.

Operating Temperature: -55°C~+105°C.



Position	Dimension				
	A	B	C	D	E
9	16.92	24.99	30.81	19.28	16.33
15	25.25	33.32	39.14	27.51	24.66
25	38.96	47.04	53.04	41.30	38.38
37	55.42	63.50	69.32	57.71	54.84

Ordering information

7908-
Series

37
Position

M
M: Male
F: Female

T
T: Tin Shell

N1
Blank: Standard Type
N1 : More Option Pls
See Page A160

A
A: Tray Package

7908-
Series

PIN-
10K Pins Per Reel

M-
M: Male
F: Female

10K