


Banana Jack

164-R105-EX

KOBICONN

Banana Jack



Dimensions: mm (in.)

Specifications

Rating:	10A
Insulation Resistance:	500VDC 100M Ω Min.
Dielectric Strength:	1000VAC 1 Minute
Temperature Range:	-10°C ~ +80°C
RoHS Compliant by Exemption	

Material

Metal:	Nickel Plated Brass
--------	---------------------

Date Last Revised: 03/06/07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301108

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

164-R105-EX