


MODEL 197




T - 3 ¼ MINIATURE BAYONET CLUSTER LED - Dual Polarity AC/DC

Voltages available from 5 - 48VDC and 5 - 120VAC. Please specify color when ordering. Insert 1 - Red, 2 - Green, 3 - Yellow, 4 - Amber, 5 - Ultra Green, 6 - Ultra Blue, 7 - Pure White where "X" appears below. Ultra Bright Blue, Ultra Bright Green and White are configured with a single 5mm LED only. All others are configured with a six T-1 LED cluster.

<u>Voltages</u>	<u>Pos. Ctr.</u>	<u>Neg. Ctr.</u>	<u>Dual Pol.</u>
5vdc/vac	197-PC5X	197-NC5X	197-DP5X
14vdc/vac	197-PC14X	197-NC14X	197-DP14X
24vdc/vac	197-PC24X	197-NC24X	197-DP24X
28vdc/vac	197-PC28X	197-NC28X	197-DP28X
48vdc/vac	197-PC48X	197-NC48X	197-DP48X
120vac			197-DP120

Direct replacement for the following incandescent lamps: 24MB, 28MB, 44, 47, 53, 60RB, 120MB, 194, 256, 313, 356, 363, 756, 757, 1445, 1450, 1495, 1813, 1815, 1816, 1818, 1819, 1820, 1829, 1850, 1855, 1864, 1866, 1891, 1892, 1893.

MODEL 160



T - 4 ½ CANDELABRA LED - Dual Polarity AC/DC


S6 candelabra screw base LED light. Long life, low power replacement for incandescent lamps. Dual polarity works in both AC and DC applications. Comes as a 4 LED cluster. Insert 1 - Red, 2 - Green, 3 - Yellow, 4 - Amber, 5 - Ultra Green, 6 - Ultra Blue, 7 - Pure White where "X" appears.

<u>Voltage</u>	<u>Model No.</u>
12	160-12X
24	160-24X
28	160-28X
48	160-48X
60	160-60X
120	160-120X (AC only)

Direct replacement for 3S6 and 6S6 lamps

How to Order: Model No.-Voltage-Color
 Example: 160-121

MODEL 460



STACK LIGHT - Dual Polarity AC/DC

S8 candelabra bayonet base with dual contacts is designed to replace incandescent lighting in Stack Lights. Reduce your energy and maintenance cost with long life LEDs. Voltages available from 24 to 120. With 360 degree viewing, these lights are available in all colors. Insert 1 - Red, 3 - Yellow, 4 - Amber, 5 - Ultra Green, 6 - Ultra Blue, 7 - Pure White where "X" appears below.

<u>Voltages</u>	<u>Model No.</u>
24	460-24X
28	460-28X
60	460-60X
120	460-120X (AC only)