



CLT SERIES

LOW PROFILE DUAL WIPE SOCKET

UL
FILE NO. E111594

Pass-Thru

Tiger Claw™ contacts

Suitable for pass-through applications

Low profile (2,21 mm) .087"

(2,00 mm) .0787" pitch

ALSO AVAILABLE IN MOQ Reel

- Other platings

Contact Samtec.

CLT	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	OTHER OPTIONS
		02 thru 50	-01 = Through-hole -02 = Surface Mount -03 = Through-hole	-F = Gold flash on contact, Matte Tin on tail -L = 10μ" (0,25 μm) Gold on contact, Matte Tin on tail -G = 10μ" (0,25 μm) Gold on contact, Gold flash on tail	All options require Style -02 -BE = Bottom Entry (Required for bottom entry applications) -A = Alignment Pin (3 positions minimum) Metal or plastic at Samtec's discretion -K = (5,00 mm) .197" DIA Polyimide Film Pick & Place Pad (04 thru 50 only) -P = Pick & Place Pad (4 positions minimum) (Not always necessary for auto placement.) -TR = Tape & Reel Packaging (36 positions max)	

LEAD STYLE	A
-01	(2,16) .085
-03	(2,95) .116

Note: Some lengths, styles and options are non-standard, non-returnable.