



Current refinements (click to remove)

[Search Tips](#)

☐ Region USA ☐ Product FamilyHLM / HLS Hook & Loop Strips and Rolls Text Search: 'HLS3S4'

Your search criteria matched only one product, shown below.

Related Products

[Click here to see ima](#)

- Strip Ties (HLS)Rolls performed in convenient 6", 12 18" strips
- 15' & 75' Rolls (HLM/HLS 15 & 75)- Can be cut to desire length, eliminating waste
- Adjustable, releasable, and reusable hundreds of times for applications requiring frequent moves, adds, or chan
- Hook and loop material maintains network data integrit protecting against overensioning of high performance cop and fiber cables
- Easy to use and operator safe with no sharp edges
- Complementary mounts available

- [Tak-Ty Hook & Loop Cable Ti...](#)
- [Tak-Ty Hook & Loop Cable Ti...](#)
- [4-Way Adhesive Backed Cable Tie Mou...](#)
- [Flat Pan-Post™ Standof...](#)
- [Extra-Heavy Cable Tie Mounts](#)
- [Swivel Mounts](#)
- [More...](#)

Note: Minimum 2" overlap required to achieve loop tensi

Part Number:	HLS3SX4
RoHS Compliancy Status:	Compliant
Part Description:	Hook & Loop Cable Tie, Strips, 12.0", Standard (section
Product Type:	Cable Ties
Material:	Nylon Loop, Polyethylene Hook
Color:	Yellow
CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854)	No
Length (In.):	12.0
Length (mm):	305
Width (In.):	.750
Width (mm):	19.1
CE Compliant:	Yes
Cross Section:	Standard
Locking Style:	Hook & Loop
Max. Bundle Diameter (In.):	3.20
Max. Bundle Diameter (mm):	81
Min. Loop Tensile Strength (L	50
Min. Loop Tensile Strength (N	222
Temperature Range:	0°F to 220°F
Thickness (In.):	.10
Thickness (mm):	2.5
Min. Order UOM:	PC
Min. Order Qty.:	10
BOM Qty. (# of Pkgs.)	0

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' f