

Intel® Server Board S2600CP2

Intel® Server Board S2600CP4

Intel® Server System Family P4000CP4

Spares/Accessories List and Configuration Guide

A reference guide to assist customers in ordering the necessary components to configure the Intel® Server Board S2600CP2, Intel® Server Board S2600CP4, and the P4000CP4 Intel® Server Systems.

~ Preliminary and Subject to Change ~



Revision 1.1

February 2012

Enterprise Platforms and Services Marketing

Revision History

May '11- Rev 0.1 – initial release for Beta Samples

Aug '11 – Rev 0.2 – initial draft for Production

Oct '11 – Rev 0.3 – updated draft for Production

Oct '11 – Rev 0.4 – incorporated feedback

Nov '11 – Rev 0.5 – Posted to CDI

Dec '11 – Rev. 0.6 – updated descriptions

Jan '12 – Rev. 0.7 – added new 6G bundled SKU, added new board SKU with C602J chip, added compatible riser options.

Jan '12 – Rev 1.0 – Final revision prior to “Books Open”. Updated ordering information, descriptions, and included most up-to-date pictures.

Feb '12 – Rev 1.1 – Updated software product codes in sections 2.5 and 2.6.

INFORMATION IN THIS DOCUMENT IS PROVIDED IN CONNECTION WITH INTEL® PRODUCTS. NO LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT. EXCEPT AS PROVIDED IN INTEL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, INTEL ASSUMES NO LIABILITY WHATSOEVER, AND INTEL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY, RELATING TO SALE AND/OR USE OF INTEL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

Intel products are not intended for use in medical, life saving, life sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice.

Intel server boards, server chassis, and processors may contain design defects or errors known as errata, which may cause the product to deviate from published specifications. Current characterized errata are available on request.

Intel, Intel Xeon, Pentium, and the Intel logo are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries.

*Other names and brands may be claimed as the property of others.

Copyright © 2012, Intel Corporation

Table of Contents:

1. SYSTEM PRODUCT ORDER CODES	4
1.1 PRODUCT DESCRIPTIONS – OVERVIEW	4
1.2 SUMMARY TABLE.....	4
1.3 AVAILABLE PRODUCTION BOARD ORDER CODE FOR S2600CP.....	4
1.4 AVAILABLE PRODUCTION SYSTEM ORDER CODES FOR P4000CP4 FAMILY	7
2. SPARES AND ACCESSORIES ORDER CODES	9
2.1 GENERAL SPARES AND ACCESSORIES	9
2.2 DRIVE/STORAGE SUBSYSTEM SPARES AND ACCESSORIES.....	12
2.3 EXPANSION MODULES: RISERS, SAS MODULE, RMM4, TPM	15
2.4 COMPATIBLE RISER OPTIONS	17
2.5 VMWARE VSPHERE* AND VCENTER* SERVER SKUS	18
2.6 SYMANTEC BACKUP EXEC 2010 SKUS	20

1. System Product Order Codes

1.1 Product Descriptions – Overview

The Intel® Server Boards S2600CP2 and S2600CP4 are mainstream server boards supporting up to two Intel® Xeon Processors, E5-2600. These boards are standard SSI EEB (12"x13") designed for the small/medium business and embedded markets. These will be offered as board-only as well as a fully integrated system in a 4U pedestal chassis. For more details, please review the tables in the subsequent sections. Should you have any questions or feedback, please feel free to contact Jeannette Larson at jeannette.h.larson@intel.com.

1.2 Summary Table

For a quick overview, all configuration options described in this document are summarized in the table below. For more details such as MM numbers and product order codes, please refer to the other sections in this document.

Product Code	FF	HDD	# of HDD	Power supply	Rails	RAID	Storage Activation	Expander
P4308CP4MHEN	4U	3.5" HS	8	1x550W Fixed	None	1,0,10+	RKSATA8	No
P4308CP4MHGC	4U	3.5" HS	8	2x750W CRPS	None	1,0,10+	RKSATA8	No
P4208CP4MHGC	4U	2.5" HS	8	2x750W CRPS	None	1,0,10+	RKSAS8	No

1.3 Available Production Board Order Code for S2600CP

Image For illustration only, not to scale.	Product Code MM UPC EAN MOQ	Description
	BBS2600CP2 916039 735858238816 5032037033596 10	Intel® Server Board S2600CP2 OEM 10-pack with Dual NIC • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C600 series chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 8 SCU SATA/SAS ports (4 ports functional w/ no storage keys and 4 ports require storage keys) • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports • Intel® Dual Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRMM4LITE) and dedicated NIC for remote management (AXXRMM4). • Support for Intel® SAS and RAID modules in PCIe form factor. Module sold separately. *Does not include IO shield. IO shield (AXX2IOS) sold separately.

	BBS2600CP2J 921042 735858244800 5032037039376 10	Intel® Server Board S2600CP2 OEM 10-pack with Dual NIC • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C602J chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports (no SCU SATA/SAS ports are supported in this SKU) • Intel® Dual Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRM4LITE) and dedicated NIC for remote management (AXXRM4). • Support for Intel® SAS and RAID modules in PCIe form factor. Module sold separately. *Does not include IO shield. IO shield (AXX2IOS) sold separately. Note: Only available in a 10-pack and only available upon request, build to order.
	DBS2600CP2 916040 735858238823 5032037033602 5	Intel® Server Board S2600CP2 Retail Single pack with Dual NIC • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C600 series chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 8 SCU SATA/SAS ports (4 ports functional w/ no storage keys and 4 ports require storage keys) • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports • Intel® Dual Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRM4LITE) and dedicated NIC for Remote Management (AXXRM4). • Support for Intel® SAS and RAID modules in PCIe form factor. Module sold separately. • IO shield included.
 And 	DBS2600CP2IOC 920971 735858244817 5032037039383 5	Intel® Server Board S2600CP2 Retail Single pack with Dual NIC and 6 Gb/s SAS • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C600 series chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 8 SCU SATA/SAS ports (4 ports functional w/ no storage keys and 4 ports require storage keys) • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports • Intel® Dual Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRM4LITE) and dedicated NIC for Remote Management (AXXRM4). • Intel® 6Gb/s SAS module in PCIe form factor included. • Includes IO shield

	BBS2600CP4 916042 735858238830 5032037033619 10	Intel® Server Board S2600CP4 OEM 10-pack with Quad NIC • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C600 series chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 8 SCU SATA/SAS ports (4 ports functional w/ no storage keys and 4 ports require storage keys) • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports • Intel® Quad Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRM4LITE) and dedicated NIC for Remote Management (AXXRM4). • Support for Intel® SAS and RAID modules in PCIe form factor. *Does not include IO shield. IO shield (AXX4IOS) sold separately.
	DBS2600CP4 916041 735858238847 5032037033626 5	Intel® Server Board S2600CP4 Retail Single pack with Quad NIC • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C600 series chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 8 SCU SATA/SAS ports (4 ports functional w/ no storage key storage keys) • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports • Intel® Quad Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRM4LITE) and dedicated NIC for remote Management (AXXRM4). • Support for Intel® SAS and RAID modules in PCIe form factor. • IO shield is included.
 And 	DBS2600CP4IOC 920972 735858244824 5032037039390 5	Intel® Server Board S2600CP4 Retail Single pack with Quad NIC and 6Gb/s SAS • Supports Dual Intel® Xeon E5-2600 processors 135W max • Intel® C600 series chipset • 16 DDR3/DDR3L DIMM slots • 6 PCIe slots • 8 SCU SATA/SAS ports (4 ports functional w/ no storage key storage keys) • 2 SATA 6G AHCI ports and 4 SATA 3G AHCI ports • Intel® Quad Gigabit Ethernet with Intel® Virtualization Technology • Integrated Baseboard Management Controller with IPMI 2.0 • Option for advanced management functions with KVM (AXXRM4LITE) and dedicated NIC for remote Management (AXXRM4). • Intel® SAS module in PCIe form factor included. • IO shield is included.

1.4 Available Production System Order Codes for P4000CP4 Family



EPSD Romley Chassis and Systems shipped to the US & Canada will contain North American power cords. North American customers no longer need to order skus ending in "NA" to receive power cords on Romley products.


Image For illustration only, not to scale.	Product Code MM UPC EAN MOQ	Description
 Demonstration only. See description for configuration details.	P4308CP4MHEN 916067 735858238809 5032037033589 1	Integrated Intel® Server System P4308CP4MHEN S2600CP4 board in an Intel P4000 pedestal chassis, rackable* • Standard control panel • 8x3.5" Hot-swap backplane • 8x3.5" HDD carriers • Two CPU heat sinks • Non-Redundant system fans • Single 550W PSU, Silver level efficiency • Intel® RAID C600 Upgrade Key RKSATA8 • Processor/Memory air duct • No Power Distribution Board needed. • Bezel supporting Hot Swap drives • IO shield • Quick User Guide *Rails are not included
 Demonstration only. See description for configuration details.	P4308CP4MHGC 918994 735858238755 5032037033534 1	Integrated Intel® Server System P4308CP4MHGC S2600CP4 board in an Intel P4000 pedestal chassis, rackable* • Standard control panel • 8x3.5" Hot-swap backplane • 8x3.5" HDD carriers • Two CPU heat sinks • Redundant system fans • Two 750W CRPS PSU, Platinum level efficiency • Intel® RAID C600 Upgrade Key RKSATA8 • Processor/Memory air duct • Power Distribution Board (High Current) • Bezel supporting Hot Swap drives • IO shield • Quick User Guide *Rails are not included
 Demonstration only. See description for configuration details.	P4208CP4MHGC 918995 735858238779 5032037033558 1	Integrated Intel® Server System P4208CP4MHGC S2600CP4 board in Intel P4000 pedestal chassis, rackable* • Standard control panel • 8x2.5" Hot-swap backplane • 8x2.5" HDD carriers • Two CPU heat sinks • Redundant system fans • Two 750W CRPS PSU, Platinum level efficiency • Intel® RAID C600 Upgrade Key RKSAS8 • Processor/Memory air duct • Power Distribution Board (High Current) • Bezel supporting Hot Swap drives • IO shield • Quick User Guide

		*Rails are not included
--	--	-------------------------

2. Spares and Accessories Order Codes

2.1 General Spares and Accessories

Image (For illustration only, not to scale.)	Product Code MM UPC EAN MOQ	Description
	FXX460GCRPS 915603 735858235846 5032037030595 1	460W Common Redundant Power Supply (CRPS) 80Plus Gold efficiency power supply accessory.
	FUP550SNRPS 915602 735858235839 5032037030588 1	550W Fixed 80Plus Silver efficiency power supply spare.
	FXX750PCRPS 915604 00735858234979 5032037030601 1	750W Common Redundant Power Supply (CRPS) spare 80Plus Platinum efficiency.
	FXX1200PCRPS 915605 735858225137 5032037035071 1	1200W Common Redundant Power Supply spare 80Plus Platinum efficiency.
Image not yet available	FUPNRPSADP 912769 735858219471 5032037016278 1	P4000 Non-Redundant Power Supply adaptor kit Includes; bracket, screws, locker
	FUPCRPSCAGE 915607 00735858235891 5032037030656 1	Common Pedestal CRPS PSU cage assembly (cage, adaptor bracket, screws, supporting bulkhead, 1x blank filler)
	FUPPDBLC 916812 735858238731 5032037033510 1	Power Distribution Board Spare (Low Current) for P4000 server chassis. Recommend to use with FXX460GCRPS or FXX750PCRPS power supplies.
	FUPPDBHC 916813 735858238748 5032037033527 1	Power Distribution Board Spare (High Current) for P4000 server chassis. Recommend to use with FXX750PCRPS, FXX1200PCRPS, or FXX1600PCRPS power supplies.



	AUPSRCBTP 915293 735858238724 5032037033497 2	Spare/Accessory SRC-B tower passive heat sinks, 98mmx100mm. 2 are required with Intel® Server Board S2600CP in P4000 chassis if two processors are installed.
	BXSTS200P 915972	Intel Boxed Thermal Solutions, passive 25.5mm heat sink supports E5-2600 processors. For use with non-Intel chassis.
	BXSTS200C 915970	Intel Boxed Thermal Solutions, heat sink combo with removable fan supports E5-2600 processors. For use with non-Intel chassis.
	FUPMLHSFAN 915620 00735858235969 5032037030724 1	80mm system fan kit for P4000M/P4000L server chassis includes fan, fan holder, for use in redundant cooling configuration
	FUPNHFANCPU 919572 00735858236034 5032037030793 1	Fixed Fan Spare Kit for P4000M (24") for CPU area fan. Includes: (1) 120mm fixed fan
	FUPMNHFANPCI 919575 735858236041 5032037030809 1	Fixed Fan spare kit for P4000M (24") for PCI area fan. Includes: (1) 120mm fixed fan
 AND 	FCPUPMAD 915623 00735858225267 5032037030823 1	Air duct and unique cable kit for Intel® Server Board S2600CP to be used Intel® Server Chassis P4000M Includes: SATA Cable MiniSAS to SATA Cable SGPIO Cable 24pin Power Extend Cable Note: Common cables are remained in P4000M chassis package

	AXXELVRAIL 920970 00735858244367 5032037038980 1	Value Rail Kit, half extension, extended inner slide member Works for 438mm wide Intel 2U/4U Rack Chassis and System families (H2000, R2000LH/R2000LT Swan Peak 2U, P4000M/P4000L/P4000L-WS)
	AXX3U5UPRAIL 915634 00735858236119 5032037030892 1	Advanced rail kit for P4000 Server Chassis used when converting Pedestal chassis to 4U rack chassis, and full extension rails are needed. Includes: (2) rails
	AXX3U5UCMA 915635 00735858236126 5032037030908 1	Rack Cable Management for use with Advanced Rail Kit AXX3U5UPRAIL for Intel® Server Chassis P4000 Family.
	FUPBEZELFIX 911886 00735858219457 5032037016254 1	Bezel spare for P4000 server chassis with fixed drives (no door)
	FUPBEZELHSD 911896 00735858219464 5032037016261 1	Bezel spare for P4000 server chassis with Hot Swap HDDs (w/door for HS bays) Fits P4304, P4308, P4208, and P4216 with HS drive bays installed.
	AUPBEZEL4UF 915636 00735858235976 5032037030731 1	Rack bezel kit for converting P4000 pedestal server chassis to rack chassis Includes: (1) bezel frame; (2) rack handles
	AUPBEZEL4UD 915637 00735858235983 5032037030748 1	Rack bezel accessory for P4000 chassis in rack configuration - security door only
	FXXFPANEL 915982 00735858222419 5032037018968 1	Front Panel board spare for P4000 server chassis
	A4ULCP 921029 00735858244695 5032037039260 1	LCP Module (local control panel) Enables system to display critical errors from SEL for instant diagnostic. Also allows custom message for branding. Available in Q2 2012

Image not yet available	AXX2IOS 919757 735858239264 5032037034036 50	I/O Shield spare/accessory for Intel® Server Board S2600CP2
	AXX4IOS 919758 735858238939 5032037033718 50	I/O Shield spare/accessory for Intel® Server Board S2600CP4
	AUPMGPUBR 920613 00735858244428 5032037039048 1	Bracket for securing full length GPU cards to fan bulkhead, for use in P4000M, includes 1 bracket, 2 GPGPU power cables, and 5 screws for GPGPU fixture.
Image not yet available	FUPMMSK 915638 735858235990 5032037030755 1	Chassis Maintenance kit for UPM – (Mechanical Spares Kit) Including EMI cover, ODD rail, PCI card retainer {4x 3.5" EMI cover, 8x 3.5" EMI cover, ODD rail x4, #6-32 screw x20, M3x12 USB cable screw x2, M2x10 Intrusion cable
	FUPMESK 915653 735858236003 5032037030762 1	Chassis Maintenance kit for UPM – (Electric Spares Kit) Including power cable extension, 1x4 -> 2x2 power adaptor cable accessory (for 2.5" HDD connector)
	FPWRCABLENA 879287 00735858181129 1	North American Power Cord Spare



2.2 Drive/storage subsystem spares and accessories



Image For illustration only, not to scale.	Product Code MM UPC EAN MOQ	Description
	FUP8X35HSBP 916353 735858222792 5032037033480 1	Spare 8x3.5" Hot Swap Backplane for use with P4000 server chassis Includes: (1) 8x3.5" backplane board
	FXX8X25HSBP 917973 735858240987 5032037035736 1	8x2.5" hot swap HSBP spare (for R2200, and P4200 Chassis families)
	FXX8X25DPBP 917974	Spare 8x2.5" Dual Port Hot Swap Backplane for use with P4200 chassis.

	735858240994 5032037035743 1	Availability: post launch.
	FUP4X35HSDK 911885 00735858219440 5032037016230 1	3.5" Hot Swap Drive Kit for P4000 server chassis Includes: Drive Cage, Hot Swap Back Plane, 4 Hot Swap Drive carriers, data cables, I2C cable, and ID filler
	FUP8X35HSDK 915608 00735858235907 5032037030663 1	8x3.5" Hot Swap Drive Cage Kit for P4000 server chassis Includes: Drive Cage, Hot Swap Back Plane, 8 Hot Swap Drive Carriers, data cables, I2C cable, and ID filler panel
	FUP8X25HSDKS 915819 00735858235914 5032037030670 1	8x2.5 Hot Swap Drive Cage Kit for P4000 server chassis Includes: Drive cage, Hot Swap Back Plane, 8 Hot Swap Drive carriers, data cables, I2C cable, ID filler panels, and power adaptor cable accessory
	FXX35HSADPB 912771 00735858219495 5032037016391 8	3.5" HDD Hot Swap Drive Carrier spares for P4300 chassis families
	FXX25HSCAR 918807 00735858241182 5032037035910 1	2.5" HDD Hot Swap Drive Carrier spares for P4200 chassis families
	FUP4X35NHDK 912770 00735858219488 5032037016247 4	Fixed Drive Carrier spare for P4300 server chassis (compatible with 2.5" HDDs/SSDs)
	RKSATA4R5 916346 735858238861 5032037033640 5	Patsburg-A SATA SW LSI RAID 5 Key, Black
	RKSATA8 916347 735858238878 5032037033657 5	8port SATA Key, Blue
	RKSATA8R5 916348 735858238885 5032037033664 5	8port SATA with LSI SW RAID 5 Key, White

	RKSAS4 916349 735858238892 5032037033671 5	4port SAS Key, Green
	RKSAS4R5 916350 735858238908 5032037033688 5	4port SAS with LSI SW RAID 5 Key, Yellow
	RKSAS8 916351 735858238922 5032037033701 5	8port SAS Key, Orange
	RKSAS8R5 916352 735858238915 5032037033695 5	8port SAS with LSI SW RAID 5 Key, Purple

2.3 Expansion modules: Risers, SAS Module, RMM4, TPM

Image For illustration only, not to scale.	Product Code MM UPC EAN MOQ	Description
	RES2CV240 918934 735858241175 5032037035903 1	Integrated 24-port 6G SAS expander, compatible with R2200 family and P4000M/P4000L of chassis (only supported in 2.5" drive 2U or 4U chassis) Includes 3 screws and bumpers, 4 cables and power cable.
	RES2CV360 918935 735858241168 5032037035897 1	Integrated 36-port 6G SAS expander, compatible with R2200 family and P4000M/P4000L family of chassis (only supported in 2.5" drive 2U or 4U chassis) Includes 3 screws and bumpers, 6 Mini-SAS cables and power cable.
	AXXRMM4LITE 911660 00735858219297 5032037014946 1	Intel® Remote Management Module RMM4LITE - Activation key for advanced management features including remote KVM.
	AXXRMM4 911670 00735858219303 5032037014922 1	Intel® Remote Management Module RMM4 – Activation key for advanced management features including remote KVM <u>plus</u> Dedicated NIC Module.
	AXXTPME5 919737 735858240352 5032037035088 1	Trusted Platform Module for server systems
	RMS25KB080 917089 735858239028 5032037033800 5	Intel® Integrated RAID Module RMS25KB080, PCIe Slot, LSI2308 I/O Controller, 8P Internal SAS, LSI IR-based RAID 0,1,1E Requires PCIe x8 slot
	RMS25KB040 917090 735858239035 5032037033817 5	Intel® Integrated RAID Module RMS25KB040, PCIe Slot, LSI2308 I/O Controller, 4P SAS, LSI IR-based RAID 0,1,1E Requires PCIe x8 slot

	RMS25PB080 917056 735858238946 5032037033725 5	Intel® Integrated RAID Module RMS25PB080, PCIe Slot, LSI2208 ROC, 8P Internal SAS/SATA, LSI MegaRAID-based Firmware, 1GB DDR3, RAID 0,1,10,5,50,6,60 Requires PCIe8 slot
	RMS25PB040 917078 735858238953 5032037033732 5	Intel® Integrated RAID Module RMS25PB040, PCIe Slot, LSI2208 ROC, 4P Internal SAS/SATA, LSI MegaRAID-based Firmware, 1GB DDR3, RAID 0,1,10,5,50,6,60 Requires PCIe8 slot
	RMT3PB080 917079 735858238960 5032037033749 5	Intel® Integrated RAID Module RMT3PB080, PCIe Slot, LSI2208 ROC, 8P Internal SATA (only), LSI MegaRAID-based Firmware, 512MB DDR3, Restricted to use only SATA drives, R0,1,10,5,50,6,60 Requires PCIe8 slot
Image not yet available	AXXRMFBU2 919876 735858244541 5032037039116 5	Intel® RAID Maintenance Free Backup Unit
	AXXRSBBU9 914238 735858220286 5032037039567 5	Intel® RAID Smart Battery AXXRSBBU9 provides optional battery backup for mainstream RS25, RMS25, RT3 and RMT3 family RAID products.
	SVCORDPSY 916902 1	Intel® On-site repair for two processor Intel® Server Systems.
	SVCEWDPSY 911295 1	Two year extended warranty for Intel® Server Systems or Intel® Server Knock Down Kits + Intel® Server Boards that support two processors. Intel® RAID controller extended warranty is purchased separately.
	SVCEWDPBD 911294 1	Two year extended warranty for Intel® Server Boards that support two processors.

2.4 Compatible Riser Options

The risers below are compatible with Intel® Server Board S2600CP2 and S2600CP4 when used in PCIe slot 6 and in 3rd party rack chassis. Users may need to develop mounting mechanics to fit their own chassis.

Image	Product Code MM UPC	Description
Image not yet available	AXX2UPCIEX16 919822 00735858244510 5032037039086 1	2U PCIe x 16 riser, 1 slot, x16 electrical/x16 mechanical Available in early Q2'2012
Image not yet available	AXX2UPCIEX8X4 919823 00735858244527 5032037039093 1	2U PCIe x16 riser, 3 slots, one x8 electrical/x16 mechanical + two x4 electrical/x8 mechanical Available in early Q2'2012
Image not yet available	AXX1UPCIEX16 919808 00735858244534 5032037039109 1	1U PCIe x16 riser, 1slot, x16 electrical/x16 mechanical Available in early Q2'2012

2.5 VMware vSphere* and vCenter* Server SKUs

Each VMware vSphere SKU contains a paper certificate with a software product activation code. As directed on the certificate, the end user must register the product activation code with VMware at <http://www.vmware.com/code/intel> to access VMware Software, Support and Subscription Services.

VMware vSphere* and vCenter* Server Editions

All VMware vSphere SKUs (except Essentials) are bundled with either 1 year VMware Basic (12x5) or with 1 year VMware Production (24x7) Support and Subscription. The Essentials SKU is bundled with 1 year VMware Subscription.

Essentials	VMware vSphere 5 Essentials Bundle for 3 hosts (Max 2 processors per host) and 192 GB vRAM entitlement with 1 year VMware Subscription.
Essentials Plus	VMware vSphere 5 Essentials Plus Bundle for 3 hosts (Max 2 processors per host) and 192 GB vRAM entitlement with 1 year VMware Basic (12x5) Support and Subscription with 1 year VMware Production (24x7) Support and Subscription
Standard	VMware vSphere 5 Standard for 1 processor (with 32 GB vRAM entitlement per processor) with 1 year VMware Basic (12x5) Support and Subscription with 1 year VMware Production (24x7) Support and Subscription
Enterprise	VMware vSphere 5 Enterprise for 1 processor (with 64 GB vRAM entitlement per processor) with 1 year VMware Basic (12x5) Support and Subscription with 1 year VMware Production (24x7) Support and Subscription
Enterprise Plus	VMware vSphere 5 Enterprise Plus for 1 processor (with 96 GB vRAM entitlement per processor) with 1 year VMware Basic (12x5) Support and Subscription with 1 year VMware Production (24x7) Support and Subscription
VMware vCenter* Server Standard for vSphere 5	VMware vCenter Server 5 Standard for vSphere 5 (Per Instance) One instance of vCenter Server is required to centrally manage virtual machines and their hosts and to enable all VMware vSphere features on Standard, Enterprise and Enterprise Plus editions. with 1 year VMware Basic (12x5) Support and Subscription with 1 year VMware Production (24x7) Support and Subscription

VMware vSphere* and VMware vCenter* – Order Codes:

Product Code	UPC	MM	Description	Minimum Order Quantity
VMW5ESS	7 35858 22474 1	918769	Paper certificate containing software license activation code for VMware vSphere 5 Essentials Bundle for 3 hosts (Max 2 processors per host) and 192 GB vRAM entitlement with 1 year VMware Subscription.	1
VMW5ESSPLUS	7 35858 22475 8	918774	Paper certificate containing software license activation code VMware vSphere 5 Essentials Plus Bundle for 3 hosts (Max 2 processors per host) and 192 GB vRAM entitlement with 1 year	1

			VMware Basic (12x5) Support and Subscription.	
VMW5ESSPLUSP	7 35858 22476 5	918768	Paper certificate containing software license activation code for VMware vSphere 5 Essentials Plus Bundle for 3 hosts (Max 2 processors per host) and 192 GB vRAM entitlement with 1 year VMware Production (24x7) Support and Subscription.	1
VMW5STD	7 35858 22477 2	918773	Paper certificate containing software license activation code for VMware vSphere 5 Standard for 1 processor (with 32 GB vRAM entitlement per processor) with 1 year VMware Basic (12x5) Support and Subscription.	1
VMW5STDP	7 35858 22478 9	918767	Paper certificate containing software license activation code for VMware vSphere 5 Standard for 1 processor (with 32 GB vRAM entitlement per processor) with 1 year VMware Production (24x7) Support and Subscription.	1
VMW5ENT	7 35858 22479 6	918772	Paper certificate containing software license activation code for VMware vSphere 5 Enterprise for 1 processor (with 64 GB vRAM entitlement per processor) with 1 year VMware Basic (12x5) Support and Subscription.	1
VMW5ENTP	7 35858 22484 0	918770	Paper certificate containing software license activation code for VMware vSphere 5 Enterprise for 1 processor (with 64 GB vRAM entitlement per processor) with 1 year VMware Production (24x7) Support and Subscription.	1
VMW5ENTPLUS	7 35858 22480 2	918771	Paper certificate containing software license activation code for VMware vSphere 5 Enterprise Plus for 1 processor (with 96 GB vRAM entitlement per processor) with 1 year VMware Basic (12x5) Support and Subscription.	1
VMW5ENTPLUSP	7 35858 22481 9	918760	Paper certificate containing software license activation code for VMware vSphere 5 Enterprise Plus for 1 processor (with 96 GB vRAM entitlement per processor) with 1 year VMware Production (24x7) Support and Subscription.	1
VMW5VCSTD	7 35858 22482 6	918742	Paper certificate containing software license activation code for VMware vCenter Server 5 Standard for vSphere	1

			5 (Per Instance) with 1 year VMware Basic (12x5) Support and Subscription.	
VMW5VCSTDP	7 35858 22483 3	918759	Paper certificate containing software license activation code for VMware vCenter Server 5 Standard for vSphere 5 (Per Instance) with 1 year VMware Production (24x7) Support and Subscription.	1

2.6 Symantec Backup Exec 2010 SKUs

Each SKU contains a paper certificate with a Voucher key code. As directed on the certificate under “Frequently Asked Questions”, the end user must go to the Symantec licensing portal at <http://licensing.Symantec.com> to redeem their Voucher key. A Sales Order Number is also on the certificate and required for redemption. Please follow all the steps to obtain serial numbers and register for support.

Symantec Backup Exec 2010 Suites

All SKUs are bundled with 1 year Symantec Essentials (24x7) support.

Symantec Backup Exec 2010	Provides an all-in-one solution for small offices to consolidate and manage many application workloads while reducing hardware and operating costs with a low up-front investment. One Backup Exec Server (per server)
Symantec Backup Exec 2010 for Windows Small Business Server	The perfect data protection solution for Microsoft* Windows Small Business Server Standard and Premium editions. This robust solution provides integrated deduplication, granular restore features, open file protection, disaster recovery and backup protection for Microsoft Exchange, SharePoint Services, SQL and Windows workstations. - One Backup Exec for Windows Small Business Server (per server) - One Agent for Microsoft Exchange server - One Agent for Microsoft SQL Server - One Agent for Microsoft Exchange Server - One Agent for Microsoft Sharepoint Server - Desktop/laptop option (up to 75) - System Recovery for one Windows server - System Recovery for one Windows Small Business server
Symantec Backup Exec 2010 Microsoft Exchange Suite	Provides complete protection for your business-critical email server running Microsoft Exchange. - One Backup Exec Server (per server) - One Agent for Microsoft* Exchange Server (per server)
Symantec Backup Exec 2010 Microsoft SQL Suite	Provides complete protection for a business-critical transactional server running Microsoft SQL - One Backup Exec Server (per server) - One Agent for Microsoft* SQL Server (per server)
Symantec Backup Exec 2010 Multi-Server Suite	Provides a Remote Agent, Continuous Protection Agent capabilities, and also includes the Advanced Open File Option and Intelligent Disaster Recovery Option. - One Backup Exec Server (per server) - Three Agents for Microsoft* Windows Systems (per server)
Symantec Backup Exec 2010 VMware Infrastructure Suite	Backup for an unlimited number of guests running on VMware* virtualization environments on one physical server. - One Backup Exec Server (per server) - One Agent for VMware Virtual Infrastructure* (per server)

Symantec Backup Exec 2010 Microsoft Hyper-V Suite	Backup for an unlimited number of guests running on Microsoft Hyper-V* on one physical server. • One Backup Exec Server (per server) • One Agent for Microsoft Hyper-V (per server)
Symantec Backup Exec 2010 Multi-Server DeDuplication Suite	Backup for four Windows Servers, including deduplication option • One Backup Exec Server (per server) • Three Agents for Microsoft Windows Systems (per server) • One Option for Deduplication (per server)
Symantec Backup Exec 2010 Exchange DeDuplication and Archiving Suite	Backup for one Windows Server with Microsoft Exchange, including deduplication and archiving options: • One Backup Exec Server (per server) • One Agent for Microsoft Exchange Server (per server) • One Option for Deduplication (per server) • One Option for Microsoft Exchange Mailbox Archiving (up to 10 mailboxes)

Symantec System Recovery 2011 Editions

All SKUs are bundled with 1 year Symantec Essentials (24x7) support.

Symantec System Recovery 2011 Server Edition	• Includes 1 license for Symantec System Recovery 2011 Server Edition • Includes 1 license for Symantec System Recovery 2011 Desktop Edition • Includes 1 license for Granular Restore Option
Symantec System Recovery 2011 Small Business Server Edition	• Includes 1 license for Symantec System Recovery 2011 SBS Server Edition • Includes 1 license for Granular Restore Option
Symantec System Recovery 2011 Desktop Edition	• Includes 1 license for Symantec System Recovery 2011 Desktop Edition

Symantec Backup Exec 2010 and System Recovery 2011 – Order Codes:

Product Code	UPC	MM	Description	Minimum Order Quantity
SYMCBE	7 35858 21992 1	911526	Paper certificate containing voucher key for one Backup Exec Media Server license with 1 year Symantec Essentials 24x7 Support.	1
SYMCBESBS	7 35858 21996 9	911532	Paper certificate containing voucher key for one Backup Exec for Windows* Small Business Server (SBS), agent for Microsoft Exchange, agent for Microsoft SQL, agent for Microsoft Sharepoint, agent for Windows systems (1 license), Desktop and Laptop option (up to 75 licenses), and Backup Exec System Recovery 2010 (1 license for server and SBS server) with 1 year Symantec Essentials 24x7 Support.	1
SYMCBE3WIN	7 35858 21993 8	911554	Paper certificate containing voucher key for one Backup Exec Media Server	1

			license and three Agent for Windows Systems with 1 year Symantec Essentials 24x7 Support.	
SYMCBEEXC	7 35858 21994 5	911533	Paper certificate containing voucher key for one Backup Exec Media Server license and agent for Microsoft Exchange Server 2003, 2007 and, 2010 SP1 with 1 year Symantec Essentials 24x7 Support.	1
SYMCBESQL	7 35858 21997 6	911534	Paper certificate containing voucher key for one Backup Exec Media Server license and agent for Microsoft SQL Server 2008 R2, 2005, and 2000 users with granular protection on 32- and 64-bit systems down to the individual database or file group with 1 year Symantec Essentials 24x7 Support.	1
SYMCBEVMW	7 35858 21998 3	911536	Paper certificate containing voucher key for one Backup Exec Media Server license and one Backup Exec 2010 Agent for VMware Virtual Infrastructures with 1 year Symantec Essentials 24x7 Support.	1
SYMCBEHYP	7 35858 21995 2	911543	Paper certificate containing voucher key for one Backup Exec Media Server license and one Backup Exec 2010 Agent for Microsoft Hyper-V license with 1 year Symantec Essentials 24x7 Support.	1
SYMCDEDUP	7 35858 21999 0	911544	Paper certificate containing voucher key for one Backup Exec Media Server license, three Agent for Windows Systems, and one Deduplication Option license which will support your entire media server environment with 1 year Symantec Essentials 24x7 Support.	1
SYMCDEDUPA	7 35858 22000 2	911545	Paper certificate containing voucher key for one Backup Exec Media Server license, one Deduplication Option license, one Exchange Archive option (10 pack), and one Agent for Exchange with 1 year Symantec Essentials 24x7 Support.	1
SYMCSRSE	7 35858 22462 8	918312	Paper certificate containing voucher key for 1 license for Symantec System Recovery 2011 Server Edition, 1 license for Symantec System Recovery 2011 Desktop Edition and 1 license for Granular Restore Option with 1 year Symantec Essentials 24x7 Support.	1

SYMCSRSBS	7 35858 22463 5	918534	Paper certificate containing voucher key for 1 license for Symantec System Recovery 2011 SBS Server Edition and 1 license for Granular Restore Option with 1 year Symantec Essentials 24x7 Support.	
SYMCSRDT	7 35858 22464 2	918535	Paper certificate containing voucher key for 1 license for Symantec System Recovery 2011 Desktop Edition with 1 year Symantec Essentials 24x7 Support.	1