


CERAMIC FILTER FOR COMMUNICATION

通信机用陶瓷滤波器

LT450□U



DIMENSIONS(mm) 外形尺寸





1:Input 1 输入
2:Ground 2 接地
3:Output 3 输出

PRINCIPAL PARAMETERS 主要参数

Model 型 号	6dB Band Width 6分贝带宽 (Khz) min	Selectivity 选择性		Stop Band Att 450 ± 100KHz 阻带衰减 (dB)min	Insertion Loss 插入损耗 (dB)max	In/Output Impedance 输入/输出阻抗 (KΩ)
		Att Band Width 衰减带宽 (KHz)max	Att Specified 保证衰减量 (dB)min			
LT450BU	±15	±30	40	27	4	1.5
LT450CU	±12.5	±24				
LT450DU	±10	±20				
LT450EU	±7.5	±15				
LT450FU	±6	±12.5		25	6	2
LT450GU	±4.5	±10				
LT450HU	±3	±9				
LT450IU	±2	±7.5				
LTW450HT	±3	±9		35		
LTW450IT	±2	±7.5				

TEST CIRCUIT 测量线路



$R_s + R_i = R_o = \text{Input/Output Impedance}$
 $R_s + R_i = R_o = \text{输入/输出阻抗}$

[Click here to enlarge the photo](#)