


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			M1	REVISED PER ECO-11-004917	11MAR11	RK



AMP
WIRE RANGE

24-20 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

NOTE:
1. WIRE INSULATION DIA 1.02[.040] TO 2.54[.100]

M7928/5-2 CLASS 2	2500	ON TAPE	2-323975-3
M7928/5-2 CLASS 1&2	50	LOOSE PIECE	323975
MILITARY PART NUMBER & CLASS PER MIL-T-7928	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105° C

VOLTAGE RATING:
—

CIRCULAR MIL AREA:
0.16 - 0.65mm² [320-1,290]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM[INCHES]

MATERIAL
COPPER PER ASTM B-152
NYLON, COLOR:NATURAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20[.008]

3 PLC ± -

4 PLC ANGLES ± -

FINISH
TIN PLATE
PER MIL-T-10727

DWN
S.S. GOULDEN
9-28-93

CHK
R. HERSEY
9-28-93

APVD
S. BORTNER
9-28-93

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

TE Connectivity

NAME
SPLICE, BUTT, P.I.D.G.,
WIRE SIZE: 24-20 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-323975

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 of 1

REV
M1

1470-19 (3/11)