


ISSUE	CATALOG LISTING	
M	5	PAGE 1 OF 1
REVISIONS	RELEASE NO. PR-1848	
A CO-180820	CHECK	
K D R	.050 MAX PRETRAVEL	
5 JUN 95	.188±.020	
B 0063672	ELASTOMER PLUNGER SEAL	
KNR 20APR10	.43 OPERATING POSITION	
	.27 ELONGATED MTG HOLE 1	
	.33	
	.091 MAX MTG HOLE 1	
	.188 1	
	.214±.010	
	.616±.010	
	.316±.010	
	CORROSION RESISTANT TREATED METAL ENCLOSURE	
	CORROSION RESISTANT STEEL PLUNGER	



NOTES

- 1 MOUNTING HOLES WILL ACCEPT ϕ .087 MAX PINS OR SCREWS ON .188±.002 CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS .16 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS 4.00 OZ MAX

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS		ELECTRICAL DATA	SCALE 2 TO 1	DO NOT SCALE PRINT
OPERATING FORCE	10 OZ MAX	CONTACT ARRANGEMENT S P N C	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE	2 OZ MIN		ONE PLACE (.0) \pm .030	
RELEASE TRAVEL	.004 MIN		TWO PLACE (.00) \pm .015	
DIFFERENTIAL TRAVEL	.005 MAX		THREE PLACE (.000) \pm .005	
OVERTRAVEL	.004 MIN		ANGLES \pm	
			WEIGHT 3	

RASTER

DRAWN

K D R 5 JUN 95

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[6XE27-1](#)