




Back

Selected Cable: 17753

Cord View

| End View | Plug | Cord | Connector | End View |
|---|---|---|---|---|
|  |  |  |  |  |
| C14 | 388A | SVT BELDFOIL SHIELDED | 386A | C13 |



| | |
|-----------------------------------|--|
| Part Number | 17753 |
| Category | 3 conductor plastic detachable |
| Shielding | Beldfoil Shielded |
| Jacket Color | black |
| Length Feet | 3'3" |
| Length Meters | 1 |
| Temperature Rating | 60 C°C |
| Packaging Units Per Carton | H-100,H-25 |
| Color Coding | International |
| AWG Stranding | 18 (41x34) |
| Nominal OD Inch | 0.253 |
| Nominal OD millimeter | 6.43 |
| Rating | 1250 Watts 10A-125V (*) |
| Notes | (*) Dual rated at 10A-250V. See 17624 for SJT version. |

Approvals



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

