






RECOMMENDED P.C.B. LAYOUT


SCALE 4:1



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATINGS: 12VDC, 50mA
5. OPERATING FORCE: 160 ± 50 gf
6. TRAVEL: 0.25 ± 0.1 mm
7. CONTACT RESISTANCE: 100 m Ω Max.
8. DIELECTRIC STRENGTH: 250V RMS min.
9. INSULATION RESISTANCE: 100 Mega Ω min.
10. ELECTRICAL LIFE: 100,000 CYCLES min.
11. DESIGNATE MAJOR FEATURE:
12. HOUSING COLOR: BLACK
13. 2002/95/EC (ROHS) COMPLIANT



E	18742	LEG TOLERANCE WAS +/- 0.1	1/12/10	BLR
D	12357	ADD NOTE 12	8/7/02	CB
C1	12354	ADD NOTCH	8/6/02	CB
REV.	ECN NO.	DESCRIPTION	DATE	CHKD

TITLE		DATE		DR		DWG		REV	
TL1105JA F160 Q		1/12/10		BLR		P010205		E	



THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED