

EvoMaxx XL

Multifunktions Seitenschneider, C60

Multifunctional HD Diagonal Cutter, C60

technische Daten:

technical specifications:

mm		Ø mm			g
mm	"	MH	H	P	
180	7	3,5	2,5	2,0	270



Abisolieren
Stripping
1,5 + 2,5 mm²



Aderendhülsen crümpen
Crimping of ferrules
1,5 - 2,5mm²



Abschneiden von Messingschrauben
Plain shearing of brass screws
M 3,5 + M 4



Ösen biegen
Looping device
Ø 4, 5, 6 mm



Flachschneider
Accurate flat cutter



Seitenschneider
Diagonal cutter
14 mm length

EvoTel

KraftTelefonzange, C60

HD Long Nose Pliers, C 60



technische Daten:
technical specifications:

		Ø mm			
mm	"	MH	H	P	g
220	9	3,0	2,0	1,4	295





Aderendhülsenzange für Aderendhülsen DIN 46 228

Spezifikationen							DIN ISO 5743			
Artikel- nummer	2022						g			
										
49-140	•						145	5 3/4	0,25–2,5mm²	130
49-180	•						180	7	0,25–16mm²	250



Crimping pliers for cable terminals according to DIN 46 228

Specification							DIN ISO 5743	
Ref. No.	2022						g	
								
49-140	•						145	5 3/4
49-180	•						180	7





Aderendhülsen-Set

bestehend aus Artikel 49-180 und
Spannungsprüfer, je 100 Stück isolierten
Aderendhülsen 0,5; 0,75; 1,5; 2,5mm²
sowie 50 Stück 4mm²

Spezifikationen										DIN ISO 5743	
Artikel- nummer	2022								g 		
76-330	•						0,25-16mm²		700		



Crimp assortment

consists of item 49-180, voltage tester
and cable terminals 0,5; 0,75; 1,5;
2,5mm² à 100 pcs. and 50 pcs. 4mm²

Specification							DIN ISO 5743	
Ref. No.	2022						g 	
							mm	"
76-330	•					0,25-16mm²	700	



