



Terminal blocks

to Type 319

-  **ASP045** page 49
-  **Type 313** page 96
-  **Type 314** page 96
-  **Type 349** page 94
-  **Type 350** page 94

Accessories

for Type 319

Coding set
700024 page 206


Type 319

Header, centerline 5 mm / 0.197 inches, vertical mounting, square contact pins 1 mm / 0.039 inches, open ends

Technical Data

 US V / A	300 / 15		
	320 V / 4 kV / 10 A		
Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 4 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	320	800	800
Rated test voltage	4	6	4
Protection category according to IEC 529	IP00		
Solder pin dimension	1.0 x 1.0 mm		
Recommended pc board hole dia.	Ø 1.5 mm		
Solder pin length	3.25 mm		
Pole size	2 - 24		
Color	black		

Dimensions in mm 1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5 \text{ mm} / 0.197 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 319

centerline 5 mm / 0.197 inches

P/N 313191

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

-  Standard pole sizes
-  Available on demand. Minimum order quantity 5000 pieces per item.