

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19075-0021
Status: Active
Overview: Solderless Terminals
Description: InsulKrimp™ Steel Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4)

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series 19075
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Solderless Terminals
Product Name InsulKrimp™
Type Ring
UPC 800753079786

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-0
Insulation PVC
Material - Plating Mating Tin
Net Weight 0.659/g
Packaging Type Bag
Stud Size 8 (M4)
Wire Insulation Diameter 4.45mm
Wire Size AWG 14, 16
Wire Size mm² 1.00 - 2.60

Material Info

Old Part Number SRB-S-229-08X

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing CD2115



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

19075Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051900
Hand Crimp Tool	0640011900

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19075-0021](#)