


THIS DRAWING IS A CONTROLLED DOCUMENT
REV 17579

Restricted to: General Release

USED ON




Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: MM

Housing Color: Red

Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - ——— - Fiber B
Fiber B - ——— - Fiber A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).

Right Side

Connector(s): SC-Duplex

Mode: MM

Housing Color: Beige


Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	B	Rev Per EC#	ECR-06-020123	9/21/2006	-	MK	
P	LTR	REVISION	RECORD	DATE	DN	APVD	



Customer Print

DNI Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK	Michael Kepko			
APVD	Michael Kepko			
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 6754410	SHEET 1 of 3	REV B

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Red		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6754410-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6754410-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6754410-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6754410-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6754410-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6754410-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-6754410-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-6754410-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-6754410-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6754410-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6754410-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-6754410-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6754410-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-6754410-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-6754410-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-6754410-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-6754410-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6754410-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-6754410-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-6754410-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6754410-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-6754410-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-6754410-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-6754410-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-6754410-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-6754410-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-6754410-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-6754410-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-6754410-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-6754410-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-6754410-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-6754410-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-6754410-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-6754410-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-6754410-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-6754410-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-6754410-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-6754410-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-6754410-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-6754410-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
5-6754410-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-

Qty	U of M	Description	Item No.
1	piece	DUST COVER, MT-RJ	1
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	PIN KEEPER, 3.8MM	3
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ Keyed Connector Housing - Red	6
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	8
2	piece	SC Simplex Housing, Beige	9
2	piece	2.5mm ferrule cover	10
AR	meter	2 fiber, XG-50/125, 1.8mm, Twinzip, Aqua, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	SC Duplex Clip	13
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Trace Label	16

B	Rev Per EC#	ECR-06-020123	8/21/2006	-	MK
P	LTR	REVISION RECORD	DATE	DIN	APVD

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ±
1 P.L.C. ±
2 P.L.C. ±
3 P.L.C. ±
4 P.L.C. ±

Customer Print

DIN Cable Assy Configurator

OK Michael Kepko

APVD Michael Kepko

MATERIAL -

HEAT TREAT -

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ
SECURE (No Pins) to SC-Duplex

SCALE NTS

SIZE A2

DRAWING NO C- 6754410

SHEET 2 of 3

REV B

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

CAC Customer Layout Rev: D

This label is used on all lengths on this drawing.

Part: Cable Assy Configurator		Material: -		Heat Treat: -	
QTY: 1		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
App'd: Michael Kepko					
Name: FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex					
Scale: NTS	Size: A2	Drawing No: C- 6754410	Sheet: 3 of 3	Rev: B	