

Home

About Hasco

Our Factory w/ Pictures

Reed Relays

Electromechanical Relays

Reed Switches/Magnets

Proximity Reed Switches

Catalog (PDF Download)

EZ Relay Design Page

Request Quote

Links

Hasco Reps

Hasco Distributors

Quick Products Listings

info@hascorelays.com

Electromechanical Relays

Hasco Component's electromechanical relays range from less than an amp to 80 amps. Hasco's relays are UL and CSA with some TUV ratings. All relays have DC coils and many have an AC coil. They come sealed for wave soldering and washing thereby allowing the relays to be put on any assemble line. There are surface mount low current relays available as well.

KLT MINIATURE POWER RELAYS
SPDT 3, 6, 12, 15 & 20 AMP

FEATURES

- Highly reliable, low cost
- Miniature size & large switch capacity up to 20A
- High dielectric strength type
- Fully Sealed
- Inexpensive



File E75887

File LR49291



Also Available As Surface Mount Device. Call for Availability.

ELECTRICAL RATINGS

3 Amp:	3A at 120VAC or 28VDC resistive
6 Amp:	6A at 120VAC or 28VDC; 6A at 240VAC general purpose; 1/4 hp at 120VAC
12 & 15 Amp:	12A at 120VAC or 28VDC; 12A at 240VAC general purpose; 7A at 277VAC general purpose; 1/4 hp at 120VAC; 15A at 120VAC resistive
Pilot duty:	40A in-rush, 4A steady state at 125VAC 10A in-rush, 1A steady state at 240VAC
N.O. only, Single Pole:	10A at 12VDC Tungsten; 15A at 120VAC Tungsten 1/2 hp at 120VAC; 5.4A at 277 VAC Ballast

GENERAL DATA

Contact resistance:	50mOhms Max.
Operate Time:	8ms Max. (at nominal voltage)
Operate Bounce Time:	3 ms Max.
Release Time:	5 ms Max.
Release Bounce Time:	8 ms Max
Max. Switching Voltage:	277VAC & 125VDC
Min. Permissible Load (reference value):	3 Amp: 5VDC at 1mA 6, 12, 15 & 20 Amp: 5VDC at 100mA
Insulation Rating:	Class B & Class F
Insulation Resistance:	more than 100M at 500VDC
Dielectric Strength:	750VAC (50/60Hz), between open contacts 1500VAC (50/60Hz), between coil & contact
Vibration:	1.5mm double amplitude, 10 to 50Hz
Shock:	100 m/sec ² (approx. 10G's)
Operation Frequency:	Mechanical: 18,000 operations/hour Electrical: 1,800 operations/hour (under rated load)
Service Life:	Mechanical: 10 million operations Electrical: 100,000 operations min. at rated resistive load
Temperature Range:	Class B: - 40°C to 85°C Class F: - 40°C to 105°C
Temperature Rise:	Less than 35 degrees
Humidity:	45% - 85% RH
Approximate Weight:	12 grams

COIL RATINGS

Nominal Coil Voltage	Coil Resistance in Ohms, ±10% at 20°C 6, 12, 15 Amp	Coil Resistance in Ohms, ±10% at 20°C 20 Amp	Must Operate Voltage at 20°C	Must Release Voltage at 20°C	Maximum Voltage
3VDC	25	20	75% max. of nominal voltage	10% min. of nominal voltage	130% of nominal voltage
5VDC	70	55			
6VDC	100	80			
9VDC	225	180			
12VDC	400	320			
18VDC	900	1100			
24VDC	1600	1280			
48VDC	6400	5120			


REMARK

- Use alcohol, freon or water for cleaning. (water temperature not to exceed 50°C)

ORDERING INFORMATION

KLT	F	1C	12	DC12	1
Model No.	Class B Class F	Contact Arrangement: A = 1 Form A (SPST-NO) B = 1 Form B (SPST-NC) C = 1 Form C (SPDT)	Contact Material & Rating: 3 Amp = Silver, gold flash 6 Amp = Silver cadmium oxide 12 Amp = silver cadmium oxide 15 Amp = silver tin indium oxide 20 Amp = Silver tin indium oxide	Nominal Voltage: 3 = 3VDC; 5= 5VDC; 6 = 6VDC; 9 = 9VDC; 12 = 12VDC; 24 = 24VDC; 48 = 48VDC	NIL = Sealed 1 = Unsealed

DIMENSIONSmm (inch)



PART NUMBERS

KLT1A6DC5	KLT1B12DC5	KLT1C15DC5
KLT1A6DC6	KLT1B12DC6	KLT1C15DC6
KLT1A6DC9	KLT1B12DC9	KLT1C15DC9
KLT1A6DC12	KLT1B12DC12	KLT1C15DC12
KLT1A6DC18	KLT1B12DC18	KLT1C15DC18
KLT1A6DC24	KLT1B12DC24	KLT1C15DC24
KLT1A6DC48	KLT1B12DC48	KLT1C15DC48
KLT1B6DC5	KLT1C12DC5	KLT1A20DC5
KLT1B6DC6	KLT1C12DC6	KLT1A20DC6
KLT1B6DC9	KLT1C12DC9	KLT1A20DC9
KLT1B6DC12	KLT1C12DC12	KLT1A20DC12
KLT1B6DC18	KLT1C12DC18	KLT1A20DC18
KLT1B6DC24	KLT1C12DC24	KLT1A20DC24
KLT1B6DC48	KLT1C12DC48	KLT1A20DC48
KLT1C6DC5	KLT1A15DC5	KLT1B20DC5
KLT1C6DC6	KLT1A15DC6	KLT1B20DC6
KLT1C6DC9	KLT1A15DC9	KLT1B20DC9
KLT1C6DC12	KLT1A15DC12	KLT1B20DC12
KLT1C6DC18	KLT1A15DC18	KLT1B20DC18
KLT1C6DC24	KLT1A15DC24	KLT1B20DC24
KLT1C6DC48	KLT1A15DC48	KLT1B20DC48
KLT1A12DC5	KLT1B15DC5	KLT1C20DC5
KLT1A12DC6	KLT1B15DC6	KLT1C20DC6
KLT1A12DC9	KLT1B15DC9	KLT1C20DC9
KLT1A12DC12	KLT1B15DC12	KLT1C20DC12
KLT1A12DC18	KLT1B15DC18	KLT1C20DC18
KLT1A12DC24	KLT1B15DC24	KLT1C20DC24
KLT1A12DC48	KLT1B15DC48	KLT1C20DC48

E-mail This Page

Print Preview

[Home](#) | [About Hasco](#) | [Our Factory](#) | [Reed Relays](#) | [ElectromechanicalRelays](#) | [Reed Switches/Magnets](#) | [ProximityReed Switches](#) | [EZ Relay Design Page](#) | [Request Quote](#) | [Hasco Reps](#) | [Hasco Distributors](#) | [Site Map](#)

906 Jericho Turnpike ♦ New Hyde Park, NY 11040 ♦ Phone: 516-328-9292 ♦ Fax: 516-326-9125

Electromechanical Relays- Relay SPDT- Relay 10 amp- Relay 12 amp- Relay SDPT Power- Relay Manufacturers
© 2010 Hasco Relays and Electronics International Corp.