






OBSOLETED	Y	<u>7</u>	<u>2</u> <u>6</u>	1-106014-9
	N		<u>2</u> <u>3</u>	1-106014-1 <u>11</u>
	Y	<u>7</u>	<u>2</u> <u>5</u>	106014-9
	N		<u>2</u> <u>4</u>	106014-4
	N		<u>2</u> <u>3</u>	106014-1
	CONSERVATION TREATMENT		CONTACT FINISH	PARTNUMBER

①	MATERIAL HOUSING : GREY GLASSFILLED POLYESTER UL-RATING V0 CONTACT : PHOSPHORBRONZE
②	GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN-LEAD MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
③	CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
④	CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
⑤	CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
⑥	CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
⑦	CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
⑧	CONNECTOR MARKED WITH PARTNUMBER AND DATECODE
⑨	PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
⑪	CONNECTOR ASSEMBLY WITH LATCH HINGE FOR CABLE CONNECTOR.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.v.d.HEIJDEN CHK D. TRUREN 15DEC97 15DEC97	 TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F.v.KONINGSBRUGGE PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029	NAME Z-PACK 2MM HM TYPE B 125 POS. RIGHT ANGLE MALE CONNECTOR ASSEMBLY	
	0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± _	WEIGHT _	SIZE A2	CAGE CODE 00779
MATERIAL _	FINISH _	DRAWING NO C-106014		RESTRICTED TO _
CUSTOMER DRAWING		SCALE NTS	SHEET 1 of 1	REV 1 3